

# Rod clevis SG-M6

Part number: 3110

FESTO



## Data sheet

Feature	Value
Size	M6
Type code	SG
Conforms to standard	DIN 71752 ISO 8140
Threaded connection	Internal thread M6
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-40 °C ... 150 °C
Product weight	22 g
Note on materials	Free of copper and PTFE RoHS-compliant
Bolt material	Steel Galvanized
Clevis material	Steel Galvanized
Nut material	Steel Galvanized