

Ministrobe MS1X12/1 and MS1X24/1



CE – Certified to EMC Directive 89/336/EEC.

Complies with low voltage directive 2006/95/EC.

High voltage transient and polarity reversal protection fitted.

Operating temperature: -20°C to +50°C.



MS1X12/1 12Vdc	60/min	single flash	115mA	IP67	65gms
MS1X24/1 24Vdc	60/min	single flash	55mA	IP67	65gms

Features:

A compact and reliable Xenon flashing device. It comprises two assemblies; a drive module and a Xenon lamp unit.

- Multivoltage 12Vdc and 24Vdc versions
- Available in five lens colours
- Low power consumption
- 12 months' guarantee
- Weatherproof to IP67

Materials:

Acrylic lens and synthetic rubber base.

Lenses and drive units ordered separately		Drive Unit	Type	Part No.
Lens Colour	Part No.	MS1X12/1	12Vdc	471007
Amber	571002			
Blue	571004			
Red	571003	MS1X24/1	24Vdc	471008
Clear	571001			
Green	571015			

