



Model : MBA42.5002 Series

BGA Heat Sink For 42.5x42.5 Chip set

Specification:

1. Material:


Heat Sink : CU1100

Clip : Plastic (UL94-V0)

2. Heat sink dimension :

Foot print : 42.5x42.5mm

Part no.	Height	Fin shape	Base	Clip	Weight
MBA42.5002-	12	P	/2.6	- Y, BU, O	66.9g
MBA42.5002-	15	P	/2.6	- Y, BU, O	74.2g
MBA42.5002-	20	P	/2.6	- Y, BU, O	86.4g
MBA42.5002-	25	P	/2.6	- Y, BU, O	98.5g



5. Clip available:

Chip set thickness

3.0-3.6mm **Y** - Yellow colored clip


1.4-2.0mm **BU** - Blue colored clip

0.5-1.1mm **O** - Orange colored clip

3. Technology: Precision Forging

4. Finish: Oxygenless Treatment

Performance Data:



Heat Source Size : Uniform



No.5, Min Lung Road, Yang Mei
Taiwan, R.O.C.
Tel : 886-3-4728155
Fax : 886-3-4725979
E-mail : sales@malico.com.tw