

3ft (1m) Side Screw Locking USB C Cable 10Gbps - USB 3.1/3.2 Gen 2 Type-C Cable - 100W (5A) Power Delivery Charging, DP Alt Mode - Dual Screw Lock - USB-C Cord Charge/Sync

**Product ID:** USB31CCSLKV1M



#### High Performance Cable

This side screw locking USB-C 3.2/3.1 Gen 2 10Gbps cable lets you connect your USB Type-C devices for syncing, charging, and powering your devices.

The USB-C cable is also compatible with Thunderbolt 3 ports, allowing you to connect and charge your USB-C devices using your Thunderbolt 3 laptop.

#### Reliable Connection with Screw Locking USB-C

This cable features dual locking screws that can securely connect to your USB-C peripherals and can prevent accidental disconnection from your devices such as external hard drives or docking stations.

The screws are designed to fit all devices that use a standard side screw locking input, such as StarTech.com's DK31C3HPD.

The knurled screws can easily be removed from the cable completely allowing it to be used as a standard USB-C cable if required.

#### Supports up to 100W (5A) with Power Delivery 3.0

With up to 100W (5A) of power delivery, you can power and charge a USB-C laptop, such as your Apple MacBook or Microsoft Surface Book. Simply connect the cable to your USB-C laptop and to a USB-C wall charger.

#### Deliver 8K video with DisplayPort 1.4 Alt Mode

The cable supports 8K 30Hz video with DisplayPort 1.4 and is backward compatible to connect your docking station or laptop to a monitor that supports 4K or 1080p resolutions.

#### Charge your mobile devices

When used with devices that support PD 3.0, this cable charges up to 20V and 5A for a maximum of 100W. It can decrease your charge time and make sure your mobile devices are ready, whenever you need them.

#### Quality Build

This cable is constructed with durable long-lasting, flexible TPE jacket and strain relief. It has been tested to withstand 4000+ bends. It is built with aluminum-mylar foil with 85% braid coverage and EMI shielding for improved signal integrity.

The USB31CCSLKV1M from StarTech.com is backed by a 2-year warranty for guaranteed reliability.

## Certifications, Reports and Compatibility

### Applications

### Features

- **HIGH PERFORMANCE CABLE:** The 3.3ft (1m) Side Screw Locking USB C to C cable complies with USB 3.2 Gen 2 SuperSpeed (10Gbps); USB-C cable supports DisplayPort 1.4 Alt mode up to 8K 30Hz & up to 100W (5A) Power Delivery 3.0; Thunderbolt 3 compatible
- **DURABLE BUILD:** Locking USB C Cable is tested to withstand 10000+ insertions & 4000+ bend cycles at 120 angle; Long lasting flexible TPE jacket & strain relief; TPE is non-toxic, halogen free & RoHS certified for environmental sustainability;
- **QUALITY CONSTRUCTION:** 32 AWG conductors; Al-Mylar foil with 85% Braid coverage EMI Shield for improved signal integrity; M2 screws (1.2"/30.5mm long) with knurled grip for easy installation/removal; Charging USB C Cord works with USB 3.0 & earlier versions
- **APPLICATIONS:** USB Type-C cable for docking stations w/ dual side locking USB C port like StarTech.com's DK31C3HDPD; Removable screw for hard drive enclosures & external storage devices; Charge a TB3/USBC workstation laptop MacBook/Surface Book/ThinkPad
- **SPECS:** 3.3 feet (1 meter) USB 3.2/3.1 Gen 2 10Gbps data transfer PD 3.0, 20V (max), 5A (max) USB C Screw Locking Male to USB C Male 0.19" (4.8 mm) Outer Diameter, 32 AWG Jacket: TPE EMI Shield: Al-Mylar Foil, Braid 2-Year warranty

---

#### Hardware

Warranty	2 Years
Connector Plating	Nickel
Cable Jacket Material	TPE - Thermoplastic Elastomers
Cable Shield Material	Aluminum-Mylar Foil with Braid

---

## Performance

Video Revision	DisplayPort 1.4
Maximum Data Transfer Rate	10Gbps
Maximum Cable Length	39.4 in [100 cm]
Type and Rate	USB 3.2 Gen 2 - 10 Gbit/s

## Connector(s)

Connector A	USB Type-C (24 pin) USB 3.1 (10Gbps)
	USB Type-C (24 pin) USB 3.1 (10Gbps)

## Power

Power Delivery	100W
----------------	------

## Physical Characteristics

Color	Gray and Black
Connector Style	Straight
Wire Gauge	30/32 AWG
Cable Length	39.4 in [100 cm]
Cable OD	0.2 in [4.8 mm]
Product Length	0.0 in [0.0 mm]
Product Width	0.0 in [0.0 mm]
Product Height	0.0 in [0.0 mm]
Weight of Product	0.0 oz [0.0 g]

## Packaging Information

Package Length	5.0 in [12.8 cm]
Package Width	8.7 in [22.0 cm]
Package Height	0.6 in [14.0 mm]
Shipping (Package) Weight	3.2 oz [90.0 g]



**What's in the Box**

Included in Package	1m Certified Side Screw Locking USB-C 10 Gbps Cable
---------------------	---

---

***\*Product appearance and specifications are subject to change without notice.***

