



## Chin straps

Available in two styles: Deluxe with chin cup, Standard elasticated.

Product	Code	Description
Chin Strap	AHV000-500-000	Deluxe Chin Strap with Chin Cup
Chin Strap	AHV001-100-000	Standard Elasticated Chin Strap



## Invincible Slimline Replacement Visors

The slimline range of visors fit the Invincible Browguard. They are designed for improved manoeuvrability of the head in tight spaces and for a more modern look.

- Polycarbonate 15cm/6" or 20cm/8"
- Acetate
- Acetate gas weld grade 5 20cm/8"

Product	Code	Description
Invincible Slimline Replacement Visors	ANA060-610-000	6"/15cm Polycarbonate Bound
Invincible Slimline Replacement Visor	ANA010-630-000	8"/20cm Acetate Bound
Invincible Slimline Replacement Visors	ANA060-630-000	8"/20cm Polycarbonate Bound
Invincible Slimline Replacement Visors	ANA010-610-000	6"/15cm Acetate Bound
Invincible Slimline Replacement Visors	ANA020-630-000	8"/20cm Acetate GW5 Bound



## **Retractaspec Eyeshield**

Retractaspec is an eyeshield designed for use with the Invincible Mark 3, Mark 2 and Mark 1 industrial safety helmets.

A retro-fit eyeshield that fits directly to a Mark 3, Mark 2 and Mark 1 helmet. It is designed to retract into the helmet, so there is less likelihood of scratching than with conventional eyeshields and so that eye protection is always on-hand to the wearer.

- Retro fit
- Slide fitting
- Soft PVC nose bridge
- No vision impairment when fully retracted
- Easy to assemble
- Available in clear or anti-glare green acetate
- Flatpacked or pre-fitted to the Mark 3, Mark 2 and Mark 1 helmet
- Conforms to EN 166 1.F

Product	Code	Description
Retractaspec	ANF030-200-000	Anti-Glare Green
Retractaspec	ANF080-200-000	Anti-Mist Clear Acetate
Retractaspec	ANF010-200-000	Clear Acetate



## **Martcare Wraparound Spectacle**

A wrap around sports style eyeshield for wide vision and complete protection.

- Moulded nose piece for added comfort
- Sideshields and adjustable arms
- Cord attachment point

Product	Code	Description
Martcare Wraparound Spectacle	ASA240-021-100	A wrap around sports style eyeshield for wide vision and complete protection.



## **Stealth 1000**

### Stealth 1000

A modern lightweight frameless single lens spectacle. The wraparound design complete with integral sideshields allows for a wide, clear field of vision.

Frame Grey, Lens Clear.

- Frameless design minimises wearer fatigue
- Sidearms feature adjustable temple length and a cord attachment point
- Conforms to EN 166.1.F

Product	Code	Description
Stealth 1000	ASA260-021-800	Stealth 1000



## **Stealth 2000**

A stylish oval rimmed executive metal framed spectacle with clear side shields.

A popular lightweight up to date choice.

- Extremely comfortable and lightweight
- Robust construction for long lasting use
- Metal frames provide strength and durability while maintaining excellent levels of protection
- Clear scratch resistant polycarbonate, UV or smoke lens
- Available in black or satin finished gun metal frames
- Conforms to EN 166.1.F

Product	Code	Description
Stealth 2101	ASA280-043- 400	Gunmetal frame, Clear UV400 lens
Stealth 2100	ASA270-023- 400	Gunmetal frame, Clear lens
Stealth 2102	ASA290-026- 100	Gunmetal frame, Smoke UV400 lens
Stealth 2200	ASA300-021- 100	Black frame, Clear lens
Stealth 2201	ASA310-041- 100	Black frame, Clear UV400 lens

Stealth 2202	ASA320-025- 800	Black frame, Smoke UV400 lens
-----------------	--------------------	----------------------------------



## **Stealth 3000**

Lightweight safety spectacle offering style and wraparound eye protection.

Black frame, clear lens.

- Curved profile polycarbonate lenses, give perfect vision, whilst maintaining a fashionable look
- Black frames enhance style
- Available with clear scratch resistant polycarbonate, smoke or mirrored lens
- Conforms to EN 166.1.F

Product	Code	Description
Stealth 3000	ASA330-021- 100	Black frame, Clear lens
Stealth 3002	ASA340-025- 800	Black frame, Smoke UV400 lens
Stealth 3003	ASA350-026- 000	Black frame, Smoke/Mirror lens



## Stealth 7000

Clear safety spectacle offering excellent levels of safety. The contour design and flexibility of frame gives a good versatile fit onto both smaller and larger faces. Available in six colours Clear, Purple Mirror, Green, Smoke, Orange, Yellow

- Ultra lightweight at only 26 grams
- Modern styling
- Polycarbonate
- UV400
- One piece
- Scratch Resistant
- Conforms to EN 166.1.F



Product	Code	Description
Stealth 7000	ASA430-021- 300	Clear Frame, Clear lens
Stealth 7000	ASA430-026- 400	Smoke Frame, Smoke UV400 lens Green Frame, Green lens
Stealth 7000	ASA430-020- 300	
Stealth 7000	ASA430-020- 800	Orange Frame, Orange lens
Stealth 7000	ASA430-023- 800	Purple Mirror Frame, Purple Mirror lens
Stealth 7000	ASA430-020- 200	Yellow Frame, Yellow lens