

White Gloss Inverter Systems

Our EASYfit split air conditioners comprises two elements - an internal and an external unit. The internal unit is fitted to a metal mounting plate on a wall in the room to be cooled, whilst the external unit is situated outside the building. The two are connected using copper pipe. The external unit, or condenser, removes the heat from the room and dissipates it outside, along with any condensation that's built-up in the system, whilst the internal unit provides cooling. Our wall split range now come alexa and google home compatible making hand controllers a thing of the past.











SPECIFICATIONS

Model	KFR63IW/AG
Power Rating (Ph-V-Hz)	1 / 220-240V / 50Hz
Capacity BTU/H (cooling) kW	24000 / 7.0 (7.8)
Capacity BTU/H (heating) kW	24000 / 7.0 (8.1)
Power Input (W) Cooling/Heating	2850~2820
Current Input (A) Cooling/Heating	9.8~9.2
SEER (BTU/hr.w)	6.1
SCOP (W/W)	4.0
Dehumidification (L/h)	2.56
Noise Level dB(A) (Hi/M/Lo)	45~56
Outdoor Noise Level dB(A)	69
Indoor Airflow (m3/h) (Hi/M/Lo)	1100 max
Current Rating (A)	10
Net Dimension (mm) indoor (W/D/H)	1055x313x240
Dimension (mm) outdoor (W/D/H)	880x330x650
Net/Gross Weight (kg) indoor	16
Net/Gross Weight (kg) outdoor	44
Max Room Size (m²)	34-60
Max Conservatory Size (m²)	30
Pipe Length (m)	6
Pipe Diameter Liquid/Gas (Inch)	3/8 & 5/8
Selectable Temp Range °C	16-32
Operating Temp (Cooling/Heating)	-15 / -10
Restart after Power Failure	Yes
Refrigerant Leak Detection & Self Diagnosis Systems	Yes



FEATURES

-  Compatible with Amazon and Google home
-  Adjustable fan speeds for rapid cooling or minimum noise
-  Heat-pump model provides heating as well as cooling
-  Oscillating air vanes for dissipation of cold air
-  A timer feature that will turn the unit on and off automatically
-  High efficiency air filters to remove odours and particles
-  Anti-mould coating for hygienic operation
-  Digital display to show operational settings and temperature

All our systems will Heat the room as well when required.

All ACC products are guaranteed for 12 months (unless otherwise stated) from the date of original purchase.

