

Product data sheet

Characteristics

9070T150D1SF41

Transformer, Type T, industrial control, 150 VA, 240/480 VAC primary / 120 VAC secondary, 1 phase, 50/60 Hz, 55 °C rise



Main

Product Type	Industrial Control Transformer
Power Rating	150 VA

Complementary

Number of Phases	1 phase
Power Rating	150 VA

Environment

Enclosure Type	Not rated (open device)
----------------	-------------------------

Ordering and shipping details

Category	16200 - 9070 T (NOT TF) 50-200VA
Discount Schedule	CP8
GTIN	00785901905417
Nbr. of units in pkg.	1
Package weight(Lbs)	5.5 lb(US) (2.49 kg)
Returnability	Yes
Country of origin	US

Packing Units

Package 1 Height	5.50 in (13.970 cm)
Package 1 width	6.30 in (16.002 cm)
Package 1 Length	7.20 in (18.288 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------
