



### Main

Product	Buck and Boost Transformer
Enclosure Code	7A
Enclosure Type	NEMA 3R
Insulation Temperature	356 °F (180 °C)
Primary Voltage	120 x 240 V
Power Rating	1 kVA
Secondary Voltage	16/32 V
Temperature Rise	115 °C

### Ordering and shipping details

Category	16265 - BUCK & BOOST
Discount Schedule	PE2
GTIN	00785901876328
Nbr. of units in pkg.	1
Package weight(Lbs)	24.95 lb(US) (11.32 kg)
Returnability	Yes
Country of origin	MX

### Packing Units

Package 1 Height	9.10 in (23.114 cm)
Package 1 width	10.50 in (26.670 cm)
Package 1 Length	11.60 in (29.464 cm)

### Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
PVC free	Yes

### Contractual warranty

Warranty	18 months
----------	-----------