




Blue Nitrile G25B & Green Nitrile G25G



CE Complex Design



Also in green

APPLICATIONS

Ideal for use in maintenance, assembly, automotive and printing industries, food handling.

FEATURES AND BENEFITS

- Nitrile formula for resistance to many solvents and oil based chemicals
- Flock lined with superior raised grip pattern
- Open cuff allows ventilation to keep hands cool
- High resistance to oil based chemicals
- Good puncture and abrasion resistance
- 21 CFR (USA) and European Directives compliant for food applications.



Blue Nitrile G26B & Green Nitrile G26G



CE Complex Design




APPLICATIONS

Ideal for use in food preparation areas, agrochemical industry, crop spraying.

FEATURES AND BENEFITS

- Nitrile formula for resistance to many solvents and oil based chemicals
- Unlined finish with superior raised grip pattern
- High resistance to oil based chemicals
- Open cuff allows ventilation to keep hands cool
- Good puncture and abrasion resistance
- 21 CFR (USA) compliant for food applications.

Also in blue



G915F & G915B



CE Complex Design



APPLICATIONS

Ideal for use in petrochemical and related industries

Ideal for general janitorial and chemical cleaning applications.

FEATURES AND BENEFITS

- Nitrile formula for resistance to many solvents and oil based chemicals
- High resistance to oil based chemicals
- Sand blasted finish for extra grip
- Flock lined for extra comfort during use
- Loose fitting cuff for added ventilation to the hand
- Generous hand sizing
- Available in green (G915F) and blue (G915B).

Size	Order code
Blue Nitrile G25B	
6.5 (S)	1626
7.5 (M)	1627
8.5 (L)	1628
9.5 (XL)	1629
10.5 (XXL)	5746
Length 330 mm	
Thickness (double wall) 0.76 mm	
Green Nitrile G25B	
6.5 (S)	3271
7.5 (M)	3272
8.5 (L)	3273
9.5 (XL)	3274
10.5 (XXL)	5747
Length 330 mm	
Thickness (double wall) 0.76 mm	

Size	Order code
Blue Nitrile G26B	
6.5 (S)	8054
7.5 (M)	8055
8.5 (L)	8056
9.5 (XL)	8057
10.5 (XXL)	8058
Length 330 mm	
Thickness (double wall) 0.90 mm	
Green Nitrile G26G	
6.5 (S)	8059
7.5 (M)	8060
8.5 (L)	8061
9.5 (XL)	8062
10.5 (XXL)	8063
Length 330 mm	
Thickness (double wall) 0.90 mm	

Size	Order code
G915F	
7 (S)	9307
8 (M)	9308
9 (L)	9309
10 (XL)	9310
11 (XXL)	9311
G915B	
7 (S)	10466
8 (M)	10467
9 (L)	10468
10 (XL)	10469
11 (XXL)	10470
Length 335 mm	
Thickness (double wall) 0.76 mm	