

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0395021009**
Status: **Active**
Overview: Eurostyle Terminal Blocks
Description: 3.50mm Pitch Eurostyle Horizontal PCB Header, 9 Circuits

Documents:

| | |
|--------------------------------|--|
| Drawing (PDF) | Product Specification PS-39500-001-001 (PDF) |
| 3D Model (PDF) | RoHS Certificate of Compliance (PDF) |
| 3D Model | |

Agency Certification

UL E48521

General

| | |
|----------------|---|
| Product Family | Terminal Blocks |
| Series | 39502 |
| Application | N/A |
| Component Type | PCB Header |
| Overview | Eurostyle Terminal Blocks |
| Product Name | ESE, Eurostyle Pluggable |
| Type | Euro Block |
| UPC | 822350435024 |

Physical

| | |
|-------------------------------|----------------|
| Circuits (Loaded) | 9 |
| Entry Angle | N/A |
| Lock to Mating Part | None |
| Number of Rows | 1 |
| Orientation | Horizontal |
| PC Tail Length | 3.50mm |
| PCB Thickness - Recommended | 2.50mm |
| Panel Mount | No |
| Pitch - Mating Interface | 3.50mm |
| Pitch - Termination Interface | 3.50mm |
| Polarized to Mating Part | Yes |
| Shrouded | Fully |
| Stackable | No |
| Temperature Range - Operating | -40° to +105°C |
| Wire Size AWG | N/A |


Electrical

| | |
|-------------------------------|------|
| Current - Maximum per Contact | 8.0A |
| Voltage - Maximum | 300V |

Material Info

Reference - Drawing Numbers

| | |
|-----------------------|------------------------------------|
| Product Specification | PS-39500-001-001 |
| Sales Drawing | SD-39501-002-001, SD-39502-001-001 |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[39502](#) Series

Mates With

Most 3.50mm Pitch Industry Standard Plugs,
[39500](#) Horizontal Plug, [39503](#) Vertical Plug