

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0393800102](#)
Status: **Active**
Overview: [Eurostyle Terminal Blocks](#)
Description: 6.35mm Pitch Beau Eurostyle Fixed Mount PCB Terminal Block, Modular, 2 Circuits

Documents:

[Drawing \(PDF\)](#) [3D Model](#)
[3D Model \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Terminal Blocks
 Series [39380](#)
 Application N/A
 Component Type One Piece
 Overview [Eurostyle Terminal Blocks](#)
 Product Name Eurostyle Fixed Mount
 Type Euro Block
 UPC 822348022977

Physical

Circuits (Loaded) 2
 Color - Resin Black
 Entry Angle Horizontal
 Lock to Mating Part None
 Material - Resin Nylon
 Number of Rows 1
 Orientation Vertical
 PC Tail Length 5.20mm
 PCB Retention None
 PCB Thickness - Recommended 4.00mm
 Panel Mount No
 Pitch - Mating Interface 6.35mm
 Pitch - Termination Interface 6.35mm
 Polarized to Mating Part N/A
 Shrouded Fully
 Stackable Yes
 Surface Mount Compatible (SMC) No
 Temperature Range - Operating 110°C
 Wire Size AWG 10, 12, 14, 16, 18, 20, 22, 24, 26, 28, 30
 Wire Size mm² 0.05-2.50

Electrical


Current - Maximum per Contact 30.0A
 Voltage - Maximum 300V

Material Info

Engineering Number MX-MSP0200S-0N

Reference - Drawing Numbers

Sales Drawing SD-39380-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per -
 D(2021)4569-DC (8
 July 2021)

Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[39380 Series](#)