



## Appliance 15W E14 230-240V T22 CL OV 1CT

Product family description  
Tubular vacuum lamps with clear glass (T-bulb)

### Product Features

- Coiled-coil filament
- Manufactured with heat-resistant solder, getter and lamp-base cement

### Product Benefits

- Reliable operation when used in special lampholders at high oven temperatures (up to 300°C)

### Application


- Electrical and standard ovens, rotisseries and similar places subject to high operating temperatures
- Available for specific oven luminaires fitted in different positions such as downlighter, side-light and backlight

| Product data                            |  |
|---|--|
| Order code                              | 036599 50                                |
| Full product code                       | 871150003659950                          |
| locod                                   |  |
| Full product name                       | Appliance 15W E14 230-240V T22 CL OV 1CT |
| Order product name                      | App 15W E14 230-240V T22 CL OV 1CT       |
| Packing type                            | 1 Lamp in a Folding Carton               |
| Pieces per pack                         | 1  |
| Packing configuration                   | 10X10F                                   |
| Packs per outerbox                      | 100                                      |
| Bar code on pack - EAN1                 | 8711500036599                            |
| Bar code on intermediate packing - EAN2 | 8711500255174                            |
| Bar code on outerbox - EAN3             | 8711500257673                            |
| Logistic code(s) - 12NC                 | 9241 962 44440                           |
| ILCOS code                              | IBT/C-15-230/240-E14-22*                 |
| Net weight per piece                    | 10.500 GR                                |
| Successor order code                    |  |
| Cap-Base                                | SES                                      |
| Bulb                                    | T22 [T 22mm]                             |


| Product data                  |                     |
|-------------------------------|---------------------|
| Bulb Finish                   | Clear               |
| Execution                     | -                   |
| Burning Position              | any [Any/Universal] |
| Main Application              | Oven                |
| Average Lifetime              | 1000 hr             |
| Rated Lamp Wattage            | 15W                 |
| Voltage                       | 230-240V            |
| Energy Efficiency Label (EEL) | F                   |
| Lamp Luminous Flux            | 90 Lm               |




App E14 T22 CL



Cap-Base SES



Burning Position any



App E14 T22

|  | C   | D   |
|--|-----|-----|
| Full product name                              | Max | Nom |
| Appliance 15W E14<br>230-240V T22 CL<br>OV ICT | 49  | 22  |

