

SDIS 0.4X2.5X75

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1.
SoftFinish grip

General ordering data

Version	Screwdriver, Blade width (B): 2.5 mm, Blade length: 75 mm, Blade thickness (A): 0.4 mm
Order No.	2749790000
Type	SDIS 0.4X2.5X75
GTIN (EAN)	4050118896534
Qty.	1 pc(s).

Creation date October 22, 2021 8:35:09 AM CEST

Catalogue status 08.10.2021 / We reserve the right to make technical changes.

SDIS 0.4X2.5X75**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Width	179 mm	Width (inches)	7.047 inch
Net weight	32 g		

Technical data

Description of article	VDE-insulated screwdriver with slotted blade 0.4x2.5x75
------------------------	---

Screwing tools

Blade length	75 mm	Blade thickness (A)	0.4 mm
Blade type	A	Blade width (B)	2.5 mm
Form	Slotted		

Classifications

ETIM 6.0	EC000158	ETIM 7.0	EC000158
ETIM 8.0	EC000158	ECLASS 9.0	21-04-04-07
ECLASS 9.1	21-04-04-07	ECLASS 10.0	21-04-04-07
ECLASS 11.0	21-04-04-07		

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--