

**SDS 0.8X4.0X100****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Slotted screwdriver with rounded blade SD DIN 5265,  
ISO 2380/2, output to DIN 5264, ISO 2380/1.  
ChromTop tip, SoftFinish grip

**General ordering data**

Version	Screwdriver, Blade width (B): 4 mm, Blade length: 100 mm, Blade thickness (A): 0.8 mm
Order No.	<a href="#">2749360000</a>
Type	SDS 0.8X4.0X100
GTIN (EAN)	4050118895582
Qty.	1 pc(s).

Creation date October 22, 2021 8:36:05 AM CEST

Catalogue status 08.10.2021 / We reserve the right to make technical changes.

## SDS 0.8X4.0X100

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

# Technical data

### Dimensions and weights

Width	210 mm	Width (inches)	8.268 inch
Net weight	50 g		

### Technical data

Description of article	Insulated screwdriver with slotted bit 0.8x4
------------------------	--

### Screwing tools

Blade length	100 mm	Blade thickness (A)	0.8 mm
Blade type	A	Blade width (B)	4 mm
Form	Slotted		

### Classifications

ETIM 6.0	EC000158	ETIM 7.0	EC000158
ETIM 8.0	EC000158	ECLASS 9.0	21-04-04-07
ECLASS 9.1	21-04-04-07	ECLASS 10.0	21-04-04-07
ECLASS 11.0	21-04-04-07		

### Downloads

Product Change Notification	<a href="#">Produktänderungsmitteilung</a> <a href="#">Product Change Notification</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>