

SDIS 0.8X4.0X100**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1.
SoftFinish grip

General ordering data

Version	Screwdriver, Blade width (B): 4 mm, Blade length: 100 mm, Blade thickness (A): 0.8 mm
Order No.	2749820000
Type	SDIS 0.8X4.0X100
GTIN (EAN)	4050118897029
Qty.	1 pc(s).

Creation date October 22, 2021 8:35:28 AM CEST

Catalogue status 08.10.2021 / We reserve the right to make technical changes.

Data sheet

SDIS 0.8X4.0X100

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Width	210 mm	Width (inches)	8.268 inch
Net weight	50 g		

Technical data

Description of article	VDE-insulated screwdriver with slotted blade 0.8x4.0x100
------------------------	----------------------------------------------------------------

Screwing tools

Blade length	100 mm	Blade thickness (A)	0.8 mm
Blade type	B	Blade width (B)	4 mm
Form	Slotted		

Classifications

ETIM 6.0	EC000158	ETIM 7.0	EC000158
ETIM 8.0	EC000158	ECLASS 9.0	21-04-04-07
ECLASS 9.1	21-04-04-07	ECLASS 10.0	21-04-04-07
ECLASS 11.0	21-04-04-07		

Downloads

Catalogues	Catalogues in PDF-format
------------	------------------------------------------