

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0638116900](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: Hand Crimp Tool for Right-Angle Board-in Crimp Terminals

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General


Product Family	Application Tooling
Series	207129
Comments	Field Repair, See Tooling Specification (PDF) Above. Type: 2C
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	PremiumGrade
Tool Type	Hand Crimp Tool
UPC	822350856386
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Engineering Number 63811-6975

Reference - Drawing Numbers

Application Tooling Documents
ATS-6381169HM-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/30/2017 (7 July 2017)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[207129 Series](#)

Use With

Loose Piece Terminals

Application Tooling | [FAQ](#)

Description	Product #
-------------	-----------

2.50mm Pitch, Board-in Male Crimp Terminal, Right-Angle, Brass Tin (Sn) Plating, 22-28 AWG, Reel	350211001
--	---------------------------

2.50mm Pitch, Board-in Male Crimp Terminal, Right-Angle, Tin (Sn) Plating, 22-28 AWG, Reel	350211160
--	---------------------------

2.00mm Pitch, Board-in Male Crimp Terminal, Right-Angle, Brass Tin (Sn)	350211201
---	---------------------------

2.00mm Pitch, Board-in Male Crimp Terminal, Right-Angle, Brass Tin (Sn)	
---	--

2.00mm Pitch, Board-in Male Crimp Terminal, Right-Angle, Brass Tin (Sn)	
---	--

2.00mm Pitch, Board-in Male Crimp Terminal, Right-Angle, Brass Tin (Sn)	
---	--

Plating, 24-30 AWG,
Reel
2.00mm Pitch, 350211301
Board-in Male Crimp
Terminal, Right-
Angle, Pre-Plated,
24-30 AWG, Reel
2.00mm Pitch, 350211360
Board-in Male Crimp
Terminal, Right-
Angle, Post-Tin
Plated, 24-30 AWG,
Reel

This document was generated on 11/02/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION