

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0638131700](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: Extraction Tool for Pico-Clasp Wire-to-Board Terminals, 28-32 AWG


Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|--------------------------------|---|
| Product Family | Application Tooling |
| Series | 207121 |
| Comments | <p style=""margin-top: 0; marginbottom: 0">See Tooling Specification (PDF) Above<p style=""margin-top: 0; marginbottom: 0">Extraction Tool for removal of 501193 , and 501189 Series |
| Function | Extraction |
| Geographic Area | Global |
| Level of Automation | Manual |
| More Detailed Tech Information | applicationtooling@molex.com |
| Overview | Application Tooling |
| Product Name | N/A |
| Tool Type | Extraction Hand Tool |
| UPC | 822350359030 |
| Warranty Disclaimer | CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified. |

Material Info

Reference - Drawing Numbers
Application Tooling Documents [ATS-638131700-001](#)



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[207121 Series](#)

Application Tooling Description

FAQ Product #

| | |
|--|----------------------------|
| 1.00mm Pitch, Pico-Clasp Low-Halogen Receptacle Crimp Housing, Dual Row, Inner Positive Lock, 20 Circuits, White | 5011892010 |
| 1.00mm Pitch, Pico-Clasp Low-Halogen Receptacle Crimp Housing, Dual Row, Inner Positive Lock, 30 Circuits, White | 5011893010 |
| 1.00mm Pitch, Pico-Clasp Low-Halogen Receptacle Crimp Housing, Dual Row, Inner Positive Lock, 40 Circuits, White | 5011894010 |
| 1.00mm Pitch, Pico-Clasp Female Crimp Terminal, Gold | 5011937000 |

Plating 0.10µm,
28-32 AWG, Reel
1.00mm Pitch, Pico- [5011938000](#)
Clasp Female Crimp
Terminal, Gold
Plating 0.38µm,
28-32 AWG, Reel
1.00mm Pitch, Pico- [5011939000](#)
Clasp Female Crimp
Terminal, Gold
Plating 0.76µm,
28-32 AWG, Reel
1.00mm Pitch, Pico- [5013300200](#)
Clasp Low-Halogen
Receptacle Crimp
Housing, Single
Row, Friction Lock, 2
Circuits, White
1.00mm Pitch, Pico- [5013300300](#)
Clasp Low-Halogen
Receptacle Crimp
Housing, Single
Row, Friction Lock, 3
Circuits, White
1.00mm Pitch, Pico- [5013300400](#)
Clasp Low-Halogen
Receptacle Crimp
Housing, Single
Row, Friction Lock, 4
Circuits, White
1.00mm Pitch, Pico- [5013300500](#)
Clasp Low-Halogen
Receptacle Crimp
Housing, Single
Row, Friction Lock, 5
Circuits, White
1.00mm Pitch, Pico- [5013300600](#)
Clasp Low-Halogen
Receptacle Crimp
Housing, Single
Row, Inner Positive
Lock, 6 Circuits,
White
1.00mm Pitch, Pico- [5013300700](#)
Clasp Low-Halogen
Receptacle Crimp
Housing, Single
Row, Inner Positive
Lock, 7 Circuits,
White
1.00mm Pitch, Pico- [5013300800](#)
Clasp Low-Halogen
Receptacle Crimp
Housing, Single
Row, Inner Positive
Lock, 8 Circuits,
White
1.00mm Pitch, Pico- [5013300900](#)
Clasp Low-Halogen
Receptacle Crimp
Housing, Single
Row, Inner Positive
Lock, 9 Circuits,
White

1.00mm Pitch, Pico- [5013301000](#)
Clasp Low-Halogen
Receptacle Crimp
Housing, Single
Row, Inner Positive
Lock, 10 Circuits,
White

1.00mm Pitch, Pico- [5013301100](#)
Clasp Low-Halogen
Receptacle Crimp
Housing, Single
Row, Inner Positive
Lock, 11 Circuits,
White

1.00mm Pitch, Pico- [5013301200](#)
Clasp Low-Halogen
Receptacle Crimp
Housing, Single
Row, Inner Positive
Lock, 12 Circuits,
White

1.00mm Pitch, Pico- [5013301300](#)
Clasp Low-Halogen
Receptacle Crimp
Housing, Single
Row, Inner Positive
Lock, 13 Circuits,
White

1.00mm Pitch, Pico- [5013301400](#)
Clasp Low-Halogen
Receptacle Crimp
Housing, Single
Row, Inner Positive
Lock, 14 Circuits,
White

1.00mm Pitch, Pico- [5013301500](#)
Clasp Low-Halogen
Receptacle Crimp
Housing, Single
Row, Inner Positive
Lock, 15 Circuits,
White

1.00mm Pitch, Pico- [5013340000](#)
Clasp Female Crimp
Terminal, Tin Plating,
28-32 AWG, Reel

1.00mm Pitch, Pico- [5013340100](#)
Clasp Female Crimp
Terminal, Tin Plating,
28-32 AWG, Bag

1.00mm Pitch, Pico- [5019390300](#)
Clasp Low-Halogen
Receptacle Crimp
Housing, Single
Row, Outer Positive
Lock, 3 Circuits,
White

1.00mm Pitch, Pico- [5019390400](#)
Clasp Low-Halogen
Receptacle Crimp
Housing, Single
Row, Outer Positive
Lock, 4 Circuits,
White

1.00mm Pitch, Pico- [5019390500](#)
Clasp Low-Halogen
Receptacle Crimp
Housing, Single
Row, Outer Positive
Lock, 5 Circuits,
White

This document was generated on 11/02/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION