

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0638171200](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: Right Angle Hand Wire Stripping Tool for 8-34 AWG Wire with 1.00mm Max Insulation Thickness

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Application Tooling
Series	207129
Application Tooling Video	www.youtube.com/watch?v=w-EFhMmpg_E
Comments	The 638171200 tool comes with 638170071 VBlade Stripping Cassette for Teflon and PVC insulation 12 to 28 AWG.
Function	Wire Stripping
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	N/A
Tool Type	Hand Wire Stripper
UPC	191128862196
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers

Application Tooling Documents 638171200-000



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[207129 Series](#)

Use With

[638170070](#) Straight Blade Stripping Cassette for PVC from 8-34 AWG, [638170071](#) "V" Blade Stripping Cassette for PTFE from 12-28 AWG, [638170072](#) Straight Blade Stripping Cassette for PVC from 5-10 AWG