



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASED	03/10/2021	DGUTTADAUR



WIRING MAP

"J1"	"CUTOFF"
WHITE 1	_____
BROWN 2	_____
GREEN 3	_____
YELLOW 4	_____
GRAY 5	_____
PINK 6	_____
BLUE 7	_____
RED 8	_____

PART NUMBER	LENGTH	
	FEET	METERS
TRG887-C4G-2M	6.56	2.0
TRG887-C4G-5M	16.41	5.0

**NOTES**



**MATERIAL:**  
MOLDED HOOD:PVC,BLACK,UL94 V-0,UV RESISTANCE  
INSULATOR:TPU, BLACK  
SCREW NUT:BRASS, NICKEL PLATE  
CONTACTS:PHOSPHOR BRONZE,15µ" MIN. GOLD PLATE

**ELECTRICAL:**  
NOMINAL VOLTAGE RATING:30 V AC/DC  
MAX CURRENT:2A

**APPLICATION:**  
INGRESS PROTECTION RATING IS IP67 (MATED).

**ENVIRONMENTAL:**  
OPERATING TEMPERATURE RANGE: -25°C TO +80°C  
CABLE JACKET RESISTANCE: SUNLIGHT,MOISTURE  
CABLE JACKET FLAME RATING:VW-1

**MISCELLANEOUS**  
CABLE ASSEMBLIES TO BE TESTED FOR CONTINUITY  
CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: <math>\leq 12 [305]</math> = +1 [25] / -0 <math>> 12 [305]</math> <math>\leq 60 [1524]</math> = +2 [51] / -0 <math>> 60 [1524]</math> <math>\leq 120 [3048]</math> = +4 [102] / -0 <math>> 120 [3048]</math> <math>\leq 300 [7620]</math> = +6 [152] / -0 <math>> 300 [7620]</math> = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]   FRACTIONS ± 1/32 .XX = ± .02 [5]   ANGLES ± 1° .XXX = ± .005 [1.3]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY B.ZHANG	03/08/2021	
APPROVED BY DGUTTADAUR	03/08/2021	CATEGORY TELECOM/MODULAR	
THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION M12 8PAF PIGTAIL UNSHLD 24AWG PVC GRY	
REF	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	CAGE CODE <b>43321</b>
		DWG. NO. TRG887-C4G	REV. <b>A</b>
		SCALE: NONE	CAD FILE: TRG887-C4G.SLDDRW
		SHEET 1 OF 1	