


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	03/10/2021	DGUTTADAUR



NOTES


MATERIAL:
 MOLDED HOOD: PVC, BLACK, UL94V-0, UV RESISTANCE
 INSULATOR: PBT+GF, BLACK
 SHELL/SCREW NUT: BRASS, NICKEL PLATE
 CONTACTS: PHOSPHOR BRONZE, 1.5µ" MIN. GOLD PLATE

ELECTRICAL:
 NOMINAL VOLTAGE RATING: 30 V AC/DC
 MAX CURRENT: 2A

APPLICATION:
 INGRESS PROTECTION RATING IS IP67 (MATED).

ENVIRONMENTAL:
 CABLE JACKET RESISTANCE: SUNLIGHT, MOISTURE
 CABLE JACKET FLAME RATING: VW-1

MISCELLANEOUS
 CABLE ASSEMBLIES TO BE TESTED FOR CONTINUITY
 CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.



PART NUMBER	LENGTH	
	FEET	METERS
TRG888-C6G-2M	6.56	2.0
TRG888-C6G-5M	16.41	5.0

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [5] ANGLES ± 1° .XXX = ± .005 [13]	APPROVALS DRAWN BY: B.ZHANG CHECKED BY SPAN APPROVED BY: DGUTTADAUR	DATE 03/08/2021 03/08/2021 03/08/2021	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	CATEGORY TELECOM/MODULAR
REF	SIZE A	CAGE CODE 43321	DWG. NO. TRG888-C6G
SCALE: NONE	CAD FILE: TRG888-C6G.SLDDRW	SHEET 1 OF 1	REV. A