

## LIDO-420 WPB

### 4" Waterproof 2-way Passive Wall-Mount Speaker Pair, Black

LIDO series is specifically designed for both indoor and outdoor applications in projects with constant voltage or low impedance systems. Thanks to the IP65 protection rating, to the PP woofers, to the UV-resistant PP cabinets, to the stainless-steel metal parts, and to the aluminum grille, these speakers do not fear the rigors of exposure to atmospheric agents.

The high excursion custom transducers guarantee a clear and defined sound, always providing a higher audio quality even at high sound pressures. The power-tap selector allows you to select 3 powers and adapt the speaker to 100V or low impedance systems. The C-bracket allows you to adjust the horizontal (+55°/-55°) and vertical position (+20°/-20°).



## PRODUCT DETAILS

### Key features

2-Way Passive system with 20W RMS Power

---

IP65 Protection Rating for Outdoor/Indoor Applications

---

UV-Resistant PP Housing

---

Built-in 100V Line Transformer

---

Power Tap Selector for 100V or low-impedance systems

---

Horizontal and Vertical adjustable C-Bracket

---

Paintable Housing and Grille

---

## Specifications

<b>Speaker Type</b>	2-Way Passive
<b>IP Rating</b>	IP65
<b>RMS Power (@ 8ohm)</b>	20W
<b>70V Powers</b>	2.5W - 5W - 10W
<b>100V Powers</b>	5W - 10W - 20W
<b>Frequency Response (-10dB)</b>	90Hz-18kHz
<b>Sensitivity (1w@1m)</b>	88dB
<b>Impedance</b>	8ohm
<b>Woofers</b>	4" (103mm), PP cone
<b>Tweeter</b>	0.5" (13mm), Mylar dome
<b>Housing</b>	UV-Resistant PP, paintable
<b>Bracket</b>	C-Bracket with Pan/Tilt adjustable angle and stainless steel screws
<b>Grille</b>	Perforated aluminum, powder coated paint, acoustic transparent foam inside, paintable
<b>Color</b>	Nero
<b>Product Size (WxDxH)</b>	138 x 120 x 220mm
<b>Speaker Weight (single unit)</b>	1,432 kg
<b>Packing Size (WxDxH) (pair)</b>	335 x 190 x 260 mm
<b>Packing Weight (pair)</b>	3,6 kg