

192A.18CPE | 192A.CPE High-performance diagonal cutters



Standards:

NF ISO 5749, ISO 5749, DIN ISO 5749, ASME B107.500

Description:

- New head design to increase durability and cutting capacity
- Cutting edges designed to cleanly cut all types of wire: soft wires and modern materials to a maximum piano wire specification of: - 192A.16CPE : 2.0mm 210 kg/mm² - 192A.18CPE : 2.2mm 205 kg/mm² - 192A.20CPE : 2.5mm 200 kg/mm²
- High Mechanical advantage due to off-set rivet and cutting edge geometry reducing effort.
- High durability Carbon alloy steel, with induction hardened cutting edges.
- Bi-Material ergonomic grips resistant to chemical agents featuring: - Return spring - Tether ready point (Tether point adds 10mm to nominal length)
- Chrome finish for corrosion resistance

	192A.18CPE
Diameter D Maxi [mm]	2.2

Length L [mm]	180.0
Thickness E [mm]	11.0
Head Height C [mm]	20.0
Head Width B [mm]	26.0
Head Width B1 [mm]	18.0
Weight [Kg]	0.26