

405.10 | 405-416-425-435- Diagonal cutters





Standards:

NF ISO 9654, ISO 9654, DIN ISO 9654, ASME B107.500

Description:

- 405: Axial cut.
- 416 - 435: Semi-flush cut, slim nose.
- 425: Flush cut, nose extended 13 mm.
- Finish: Matt burnished finish, red grips - return spring.
- Copper only (for 405.10 and 405.12).



	405.10
Length L [mm]	110.0
Thickness E [mm]	10.5
Head Height C [mm]	10.5
Head Width B [mm]	11.5
Length L1 [mm]	7.0
Weight [g]	60.0