

432.LMT | Micro-Tech® thin nose grippers





Standards:

NF ISO 9655, ISO 9655, DIN ISO 9655, ASME B107.500

Description:

- Fine mesh, for high precision work.



 432.LMT	
Length L [mm]	140.0
Thickness E1 [mm]	1.6
Head Height C [mm]	35.0
Head Width B [mm]	9.0
Weight [g]	65.0