

433.LMT | Micro-Tech® 45° angled thin nose grippers





Standards:

NF ISO 9655, ISO 9655, DIN ISO 9655, ASME B107.500

Description:

- Thin angled for betles accessibility and control.



	433.LMT
Length L [mm]	135.0
Thickness E1 [mm]	1.6
Head Height C [mm]	35.0
Head Width B [mm]	9.0
Thickness E [mm]	6.0
Weight [g]	75.0