

467B.6 | 467B - Metric ratchet combination wrenches





Standards:

NF ISO 1711-1, NF ISO 691, ISO 1711-1, ISO 691, DIN ISO 1711-1, DIN ISO 691

Description:

- Ultra-Grip ratchet wrenches: retaining pin on the ring + securing notch on the open end. Does not slip on the nuts, optimum safety.
- Compact ratchet mechanism reversing by lever. Better accessibility.
- 5° increments (7.5° for size 6 mm; 6° for 7, 8 and 9 mm sizes). Enhanced productivity.
- Ring and open end tilted at 15°.
- Metric sizes: 6 to 41 mm
- Satin chrome finish.



	467B.6
A [mm]	6.0
A [in]	
Length L [mm]	128.0
Thickness E [mm]	4.0
Thickness E1 [mm]	6.3
Thickness E2 [mm]	2.7
Head Height C [mm]	6.5
Head Width B [mm]	14.1
Head Width B1 [mm]	14.1
Weight [Kg]	0,02