

## 467B.9 | 467B - Metric ratchet combination wrenches





### Standards:

NF ISO 1711-1, NF ISO 691, ISO 1711-1, ISO 691, DIN ISO 1711-1, DIN ISO 691

### Description:

- Ultra-Grip ratchet wrenches: retaining pin on the ring + securing notch on the open end. Does not slip on the nuts, optimum safety.
- Compact ratchet mechanism reversing by lever. Better accessibility.
- 5° increments (7.5° for size 6 mm; 6° for 7, 8 and 9 mm sizes). Enhanced productivity.
- Ring and open end tilted at 15°.
- Metric sizes: 6 to 41 mm
- Satin chrome finish.



	467B.9
A [mm]	9.0
A [in]	
Length L [mm]	149.0
Thickness E [mm]	4.6
Thickness E1 [mm]	6.9
Thickness E2 [mm]	3.2
Head Height C [mm]	9.0
Head Width B [mm]	21.0
Head Width B1 [mm]	18.6
Weight [Kg]	0,04