

## 985895 | Wire end crimping pliers




### Standards:

**NFC 63-023**

### Description:

- Stainless steel 5-cavity dies: - 0.5 to 0.75 mm<sup>2</sup>. - 1 to 1.5 mm<sup>2</sup>. - 2.5 mm<sup>2</sup>. - 4 mm<sup>2</sup>. - 6 mm<sup>2</sup>.
- Unlocking accessible at all times.
- Reversed crimping: terminal positioned on the fixed part for more effectiveness and precision.
- Capacity 0.5 to 6 mm<sup>2</sup>.
- Shape allowing hand setting.
- Soft touch.



	<b>985895</b>
Length L [mm]	230.0
Weight [g]	490.0