


## ES.134T | ES.1T - High Perf` bits series 1 for slotted head screws





### Standards:

NF ISO 2351-1, NF ISO 1173, ISO 2351-1, ISO 1173, DIN ISO 2351-1

### Description:

- For intense manual screwing.
- Drive 1/4" - 6.35 mm.



	ES.134T
A [mm]	4.0
Length L [mm]	25.0
Thickness E [mm]	0.5
Weight [g]	2.0