


J.17 | J - 3/8" metric 12-point sockets



Description:

- OGV® profile: more powerful tightening, preserves fasteners.
- Finish: bright chrome.

	J.17
A [mm]	17.0
Diameter [mm]	21.7
Diameter D1 [mm]	23.4
Length L [mm]	30.0
Length L1 [mm]	13.0
12-Point [mm]	12.0
Weight [g]	52.0