

J.19LA | J.LA - 3/8" long-reach metric 12-point sockets



Description:

- OGV® profile: more powerful tightening, preserves fasteners.
- Long-reach sockets for long recess or thread access.
- Available as rack sets (Ref JL.40U).
- Finish: bright chrome.

|  | J.19LA |
|--|--------|
| A [mm] | 19.0 |
| Diameter [mm] | 23.0 |
| Diameter D1 [mm] | 25.0 |
| Length L [mm] | 60.0 |
| Length L1 [mm] | 18.0 |
| 12-Point [mm] | 12.0 |
| Weight [g] | 110.0 |