



R.13 | R 1/4" drive metric 6-point sockets



Description:

- OGV® profile: more powerful tightening, preserves fasteners.
- Finish: bright chrome.
- Available as sets on metal rack (Ref R.40E).



	R.13
A [mm]	13.0
Diameter [mm]	17.7
Diameter D1 [mm]	17.7
Length L [mm]	22.0
Length L1 [mm]	10.0
Height H3 [mm]	10.0