

R.306-25D | 306D - Click wrenches without accessories




Standards:

NF EN ISO 6789, ISO 6789, DIN EN ISO 6789

Description:

- Factory accuracy: $\pm 2\%$ except: - R.306-25D - K.306A600 - K.306A1000 ($\pm 4\%$). - R.304DA ($\pm 6\%$).
- Reliability of mechanism: 50 000 cycles (wrenches up to 200 N.m).
- Use possible with accessories: - End fitting: 9 x 12 or 14 x 18 mm. - Diameter: 30 mm.
- One-way wrenches usable for unscrewing by reversing the bits.
- Numbered wrenches supplied with ISO 6789 calibration certificate.
- Supplied in plastic box.

	R.306-25D
Length L [mm]	271.0
Attachement ["]	9 x 12
Capacity [Nm]	5 - 25
Graduation [Nm]	0.1
Weight [Kg]	0.45