

S.19H | S.H - 1/2" metric 6-point sockets





Standards:

NF ISO 2725-1, NF ISO 1711-1,
ISO 2725-1, ISO 1711-1, DIN
3124, ASME B107.5

Description:

- OGV® profile: more powerful tightening, preserves fasteners.
- Finish: bright chrome.



 S.19H	
A [mm]	19.0
Diameter [mm]	24.6
Diameter D1 [mm]	26.6
Length L [mm]	36.0
Length L1 [mm]	14.0
Weight [g]	75.0