


Economical, Reversible Humidity Indicating Cards


**HC Series
100 to 500 Cards**

Reversible!


Humidity indicating cards allow a low cost method of indicating humidity conditions for various types of barrier packaging, including Mil Spec (MIL-I-8835) applications. The 30%-40%-50% card complies with MS 20003-2.




HC-30/50-125
3.125 x 2"



HC-10/30-125
3.125 x 2"




HC-10/60-200
4.56 x 1.5"



HC-8-500
2.19 x 1.5"

All models shown actual size.



HC-10/40-100
3.125 x 2"

To Order			
Model No.	Humidity Range	Quantity	Card Dimensions
HC-10/30-125	10 to 30% RH	125	79 x 51 mm (3.125 x 2")
HC-30/50-125	30 to 50% RH	125	79 x 51 mm (3.125 x 2")
HC-10/40-100	10 to 40% RH	100	79 x 51 mm (3.125 x 2")
HC-10/60-200	10 to 60% RH	200	116 x 38 mm (4.56 x 1½")
HC-8-500	8% RH	500	56 x 38 mm (2.19 x 1½")

Ordering Example: HC-10/30-125, humidity indicating cards, 10 to 30% RH, package of 125.

