


Contact/Non-Contact Pocket Laser Tachometer

with Totalizer/Counter/Timer Features



HHT12



HHT12

- ✓ Operating Range Up to 915 mm (36") (Red LED)

HHT13

- ✓ Operating Range Up to 7.6 m (25') (Class 3R Visible Laser)
- ✓ TTL Pulse Output



Specifications (HHT12)

Range: 5 to 99,999 rpm

Accuracy: 0.01% of reading or ± 1 digit

Resolution:

Auto-Ranging: 0.001 to 1.0 rpm

Fixed: ± 1 digit rpm

Operating Range: 50 to 915 mm (2 to 36")

Specifications (HHT13)

Range:

Optical: 5 to 200,000 rpm

Contact*: 0.5 to 20,000 rpm (Other ranges: inches, feet, yards, miles, cm, m, per hour, minutes, seconds)

Accuracy:

Optical: $\pm 0.01\%$ of reading

Contact*: $\pm 0.05\%$ of reading (rpm)

Resolution: 0.001 to 10 rpm (speed range dependent)

Operating Range: 50 mm to 7.6 m (2" to 25')

* With optional RCA.

Common Specifications

Display: 5-digit alphanumeric LCD

Memory: Max, min and last

Power: 2 "AA" 1.5 Vdc batteries (included)

Environmental: 5 to 40°C (41 to 104°F), 80% RH up to 30°C (86°F)

Dimensions: 176 L x 61 W x 41 mm D (6.9 x 2.4 x 1.6")

Weight: 210 g (7 oz)

OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.

To Order

Model No.	Description
HHT12	Basic tachometer with 350 mm (12") reflective tape
HHT13	Tachometer/timer/totalizer with NIST certificate
HHT13-KIT	Tachometer/timer/totalizer with NIST certificate, RCA, carrying case
HHT20-ROS	Remote optical sensor with 2.4 m (8') cable, mounting bracket and 305 mm (12") of reflective tape
HHT13-CC10	Padded pouch fits tachometers
HHT13-RCA	RCA includes contact tips (concave and convex) and 10 cm (3.9") linear contact wheel
HHT13-CTE	Rubber concave, convex tips and 10 cm (3.9") contact wheel
HHT13-LCW	Linear contact wheel with 305 mm (12") circumference for use with RCA
HHT-RT-5	Reflective tape 1.5 m (5') roll, 12 mm (0.5") wide

HHT12 comes complete with two 150 x 12 mm (6 x 0.5") strips of reflective tape, 2 "AA" batteries and operator's manual.

HHT13 comes complete with NIST-traceable certificate of calibration, two 150 x 12 mm (6 x 0.5") strips of reflective tape, 2 "AA" batteries and operator's manual. The HHT13-KIT comes with operator's manual, NIST-traceable certificate of calibration, 2 "AA" batteries, 1.5 m (5') roll of T-5 reflective tape, an RCA, including concave and convex tips, and a 10 cm (3.9") linear contact wheel, all in a latching hardcover carrying case.

Ordering Examples: HHT12, basic tachometer, HHT13-CC10, padded pouch, HHT-RT-5, spare reflective tape. OCW-3, OMEGACARESM extends standard 1-year warranty to a total of 4 years.

HHT13, tachometer, HHT-RT-5, spare reflective tape, MA-1214, reference book: Statistical Intervals. OCW-3, OMEGACARESM extends standard 1-year warranty to a total of 4 years.