

[Update related to COVID-19. Learn More →](#)[Products](#)[Industries](#)[About](#)[Resources](#)[Blog](#)[Contact us](#)[Find A Distributor](#)[Home](#) > [Products](#) > [Cooling Fans](#) > [DC Axial Fans](#) > [08015SS-12M-AL-00](#)[← Back To DC Axial Fans](#)

Have a question about this product?



[Ask Our Experts →](#)

DC Axial Fans - 08015SS-12M-AL-00

[Get a sample](#)

Resources

[Specification Sheet](#)[Series
Data
Sheet](#)



Specifications

Category	DC Axial Fans
Part Number	08015SS-12M-AL-00
Frame Width [mm]	80
Frame Height [mm]	80
Frame Depth [mm]	15

Max. Air Flow [CFM]	30
Max. Air Flow [m3 per min]	0.85
Max. Static Pressure [In H2O]	0.12
Max. Static Pressure [Pa]	29.5
Fan Speed [RPM]	2800
Noise [dB]	31
Life Expectancy [L10]	40 degree C 40,000 Hours
Bearing Type	Sleeve Bearing
Nominal Voltage [V]	12
Operating Voltage - Lower [V]	6
Operating Voltage - Upper [V]	13.8
Current [A]	0.15

Input Power [W]	1.8
Mass [g]	55
Tach / Locked Rotor Output	Locked Rotor
Status	Active

PRODUCTS[See All Products](#) →[Find A Distributor](#)[Find a Sales Representative](#)**INDUSTRIES**[See All Industries](#)[Automotive](#)[Industrial](#)[Medical](#)[Consumer Technology](#)[Smart City](#)[Lighting Innovations](#)**RESOURCES**[See All Resources](#) →[Application Notes & Whitepapers](#)[Latest News](#)[Videos](#)**CONTACT**

NMB Technologies Corporation

(248) 919-2250

info@nmbtc.com

Have A Question?

Our precision component experts can help you find the right solutions.

[Contact Us Today](#)[Find A Distributor](#)[Find Sales Rep For Fans](#) →

