

tesamoll® E-Profile

BNR 5361, 5445, 5463, 5464, 5491, 55701

The tesamoll® E-Profile is a self-adhesive and durable DIY rubber sealing tape. It is a flexible draught seal able to reduce your heating costs by up to 20%.

Features

- Saves up to 20% of energy costs
- Self-adhesive high quality rubber E-Profile
- Seals all gaps from 1 to 3.5mm
- Durability: 8 years
- Weather-, UV- and ozone-resistant
- Wipe-clean
- Easy to apply and to fit without screws or nails
- Easy to remove
- Temperature-resistant from -50°C to +60°C

Consumer Product Properties

- | | | | |
|---------------------------|--------|---------------------------------|------------|
| • Applicationfield | Home | • Energy saving potential up to | 20 % |
| • Durability | 8 Year | • Batteries required | no |
| • Humidity resistant | yes | • Gap coverage | 1 - 3.5 mm |
| • Resistance to chemicals | No | • Batteries included | no |
| • Solvent free | yes | | |

Consumer Technical Data

- | | | | |
|--------------------------|------------------|--------------------------------|--------|
| • Residue-free removable | yes | • Temperature resistant | yes |
| • Type of adhesive | synthetic rubber | • Temperature resistance from | -20 °C |
| • Backing material | Fabric | • Temperature resistance up to | 60 °C |

Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit
<http://l.tesa.com/?ip=05361>