

tesa® 61914



Product Information

Repulpable double-sided splicing tape

tesa® 61914 is a double-sided repulpable tape consisting of a tissue paper backing and a modified water soluble acrylic adhesive.

tesa® 61914 features especially

- High tack properties
- Good adhesion values on coated and uncoated papers
- Good shear strength
- Good repulpability (w/o liner) over full pH-range (pH3 –pH9)

Colour: Blue

Main Application

tesa® 61914 is particularly suitable for

- Flying and static splices in the printing and paper producing industry

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Technical Data

- | | | | |
|--------------------|------------------|-----------------------------------|----------------------|
| • Backing material | non-woven | • Type of liner | bi-siliconised paper |
| • Total thickness | 70 µm | • Shelf life time (packed) < 25°C | 12 months |
| • Type of adhesive | modified acrylic | | |

Properties

- | | | | |
|--------|-----|---------------------------|-----|
| • Tack | ●●● | • Static shear resistance | ●●● |
|--------|-----|---------------------------|-----|

Evaluation across relevant tesa® assortment: ●●●● very good ●●● good ●● medium ● low

Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit
<http://l.tesa.com/?ip=61914>