



CAT6A Modular RJ-45 Plugs w/Boots, Solid/Stranded STP, 100PK

**MFR:** FMTP6AS-CL-100PAK

**All-in-one multipack includes connectors and clear snagless boots for use in assembly of CAT6A patch cabling**

- Premium CAT6A connectors constructed to exceed industry standards
- 50- $\mu$ " (1.27- $\mu$ m) Gold Plated Contacts Plug meets PoE++ IEEE802.3bt; Class 8.110w
- Meets UL<sup>®</sup> 94V-2, ANSI<sup>®</sup>/TIA<sup>®</sup>-568.2-D and ISO<sup>®</sup>/IEC 11801 Class EA standards
- For use with 24 or 26 AWG solid/stranded cable up to 5.7-mm OD
- Load bar included to keep integrity of pairs and for ease of termination
- Warranty: 25 Year Double Diamond<sup>™</sup> Warranty (Standard)