

# Bench Counting and Weighing Scales **multicomp**<sup>PRO</sup>

---

**RoHS  
Compliant**



## Description

Compact bench counting scales provide quality performance for counting and weighing tasks. With three displays and a full numeric keypad, users can freely select samples when counting and the display clearly shows the total weight, count, and unit weight of the samples being counted. Powered by the included AC adapter or internal rechargeable battery, is ideal for a range of applications in production or warehouse facilities. A fully charged battery operates for an impressive 240 hours before needing to be recharged and, for convenience, the can be operated using a USB power source.

## Features

- Vivid, backlit LCD easily visible in any lighting conditions
- Overload protection helps prevent damage to internal components
- Rugged construction stands up to industrial use
- Sealed keypad protects against dirt and spills
- Simple operation allows quick startup and use with little or no training
- Large, grade 304 stainless steel pan allows swift cleaning
- Adjustable leveling feet help optimize setup
- External calibration allows for verification and adjustment with weights
- Parts counting with freely selectable sample sizes
- Memory accumulation totals results
- Rechargeable battery included for operation almost anywhere
- Programmable auto power-off to save energy
- Battery level is clearly displayed to show the user when the scale needs to be recharged
- Operates with a low voltage USB input providing flexibility for powering the device

## Applications

- Weighing
- Parts Counting
- Accumulation of Weight

# Bench Counting and Weighing Scales **multicomp** PRO

## Specification

Maximum Capacity	3kg	6kg	15kg	30kg
Readability	0.1g	0.2g	0.5g	1g
Repeatability (sd)	0.2g	0.4g	1g	2g
Linearity	0.2g	0.4g	1g	2g
Pan Size	180x245mm			
Weighing Units	g, kg, lb, lb:oz, oz			
Stabilisation Time (sec)	1			
Calibration	External calibration			
Display	Backlit LCD with 24mm high digits			
Power Supply	5V DC 1A adapter / Internal rechargeable battery			
Operating Temperature	0° to 40°C / 32° to 104°F			
Housing	ABS plastic			
Overall Dim.	225mm × 290mm × 105mm			
Net Weight	2.5kg			

## Part Number Table

Description	Part Number
Bench Counting and Weighing Scale, 3kg, 0.1g Readability	MP700637
Bench Counting and Weighing Scale, 6kg, 0.2g Readability	MP700638
Bench Counting and Weighing Scale, 15kg, 0.5g Readability	MP700639
Bench Counting and Weighing Scale, 30kg, 1g Readability	MP700640

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro  
 Farnell.com/multicomp-pro  
 Element14.com/multicomp-pro

**multicomp** PRO