




## Pre-Mixed pH Calibration Solutions and Deionized Water

### PHA-4 Series



All shown smaller than actual size.

- ✓ Deionized Water
- ✓ Pre-Mixed pH Solutions
- ✓ Two Bottle Sizes Available
- ✓ pH Solutions Standardized Against NIST Certified Sample

Formulated to provide precise pH determinations, these buffer solutions which are standardized against NIST-certified reference samples, are ideal for calibrating electrodes and pH meters. The buffers are color-coded to avoid error and accurate to within  $\pm 0.01$  pH at 25°C (77°F). Each buffer contains a preservative/mold inhibitor and a shrink-sealed cap to prevent contamination and leakage. Temperature compensation charts are included with each buffer solution.



**PHAB-PH**  
5 each 4, 7 and 10 buffer packs with 5 deionized water packs. Shown smaller than actual size.

To Order	
Model No.	Description
PHA-4	4.00 pH buffer solution 500 mL (1 pint) bottle
PHA-4-GAL	4.00 pH buffer solution 4 L (1 gal) bottle
PHA-7	7.00 pH buffer solution 500 mL (1 pint) bottle
PHA-7-GAL	7.00 pH buffer solution 4 L (1 gal) bottle
PHA-10	10.00 pH buffer solution 500 mL (1 pint) bottle
PHA-10-GAL	10.00 pH buffer solution 4 L (1 gal) bottle
PHA-DI	Deionized water 500 mL (1 pint) bottle
PHA-DI-GAL	Deionized water 4 L (1 gal) bottle
PHAB-DI	20 single use deionized water packets
PHAB-PH	5 each 4, 7 and 10 buffer packs with 5 deionized water packs

Ordering Examples: PHA-7-GAL, 7.00 pH buffer solution 1 gallon bottle. PHA-7, 7.00 buffer solution, 1 pt bottle.