

DATA SHEET



ODESSA

Odessa 50W LED Floodlight White PIR 840

IP65 LED Slim Floodlights
 Supplied with Prewired Flex
 Quick and Easy to Install



GENERAL INFORMATION	
Product Code	NOD50/WH/PIR/840
Product Range	Odessa
Product Category	Floodlighting
Fixing Method	Surface
IP Rating	65
IK Rating	N/A
Warranty	5 Years 20000 Hours
DIMENSION/WEIGHT	
Dimensions (L x W x H) (mm)	L=undefined, W=74, H=268
Cut-out Size (mm)	N/A
Product Weight (Kg)	3
CONSTRUCTION	
Body Material	Die Cast Aluminium
Body Colour	Black
Optical Material	Glass
Optical Finish	Clear
Termination	1m H05RN-F Flex
Driver - Integral or Remote	Integral
PACKAGING	
Carton Dimensions (mm)	N/A
Quantity per Outer Carton	N/A
Total Weight incl. Carton (Kg)	N/A



LUMINAIRE PERFORMANCE	
Energy Rating	N/A
Luminaire Lumens (lm)	5300
Power Consumption (W)	50
Efficacy (l.lm/c.W)	100
Operating Temp. (Min/Max)	-20°C - 25 °C
LIGHT SOURCE	
Type	LED
Correlated Colour Temp.	4000
Colour Rendering Index (CRI)	>80
Lumen Depreciation	L70:B10 50000
SDCM	<5
ELECTRICAL INPUT	
Voltage (V)	220-240V AC
Operating Frequency	50
In Rush	12A
Drivers per MCB*	N/A
Class	Class 1
Power Factor	>0.95
Cable Entry	Prewired
ELECTRICAL OUTPUT	
Forward Current (mA)	N/A
Forward Voltage (Vf)	N/A
EMERGENCY DATA	
Mode of Operation	N/A
Battery Duration	N/A
Battery Type	N/A
Battery Specification	N/A
Ballast Lumen Factor (BLF)	N/A
DIMMING	
DALI	N/A
OTHER	N/A
Switch Dim	N/A
Corridor Function	N/A
SENSORS	
Microwave	N/A
PIR	Yes
STANDARDS/APPROVALS	
CE Marked	yes
Certificate of Conformity	yes
Accreditations	N/A
BARCODE	
EAN Number	5055943026469

* GUIDE ONLY