


WIRE DUCT

WD Series



- Excellent Lid Retention to Combat Vibration
- Design Aids in Cable Retention During Installation
- Made of Self Extinguishing PVC-UL 94 V-0 Rating
- Cover Included
- Meets DIN Standard 43659




WD-B25X40S, standard slot wire duct 29 x 41 mm (1.14 x 1.61") with cover, shown smaller than actual size.

SPECIFICATIONS

Length: 2 m (6.6')
 Service Temperature: -15 to 60°C (-5 to 140°F)
 Standard Slot:
 Width: 8 mm (0.31")
 Pitch: 20 mm (0.79")

Thin Slot:
 Width: 4 mm (0.16")
 Pitch: 10 mm (0.39")



SINGLE PIECE MODEL NO.	EXTERNAL DIMENSIONS	
	WIDTH mm (inch)	HEIGHT mm (inch)
WD-B25X40S	29 (1.14)	41 (1.61)
WD-B25X40T	29 (1.14)	41 (1.61)
WD-B25X60S	29 (1.14)	54 (2.13)
WD-B25X60T	29 (1.14)	54 (2.13)
WD-B25X80S	29 (1.14)	79 (3.11)
WD-B25X80T	29 (1.14)	79 (3.11)
WD-B40X40S	41 (1.61)	41 (1.61)
WD-B40X40T	41 (1.61)	41 (1.61)
WD-B40X60S	41 (1.61)	54 (2.13)
WD-B40X60T	41 (1.61)	54 (2.13)
WD-B40X80S	41 (1.61)	79 (3.11)
WD-B40X80T	41 (1.61)	79 (3.11)
WD-B60X60S	54 (2.13)	54 (2.13)
WD-B60X60T	54 (2.13)	54 (2.13)
WD-B60X80S	54 (2.13)	79 (3.11)
WD-B60X80T	54 (2.13)	79 (3.11)

Note: S = Standard slot width, T = Thin slot width

Ordering Examples: WD-B25X40S, one standard slot width wire duct with cover, 2 m (6.6') L, 29 W x 41 mm H.

WD-B25X40T, thin slot width duct with cover, 2 m (6.6') L, 29 W x 41 mm H.