

Brannan Product Data Sheet

PDS0307.20.REV0

Weatherproof, Digital 'Classic' Max Min Thermometer

Robust, digital max min thermometer, uniquely designed by Brannan to resemble the traditional liquid-in-glass style, quick-set, push button max min thermometers. Triple display simultaneously shows maximum, minimum and current temperature. Weatherproof design - suitable for indoor or outdoor use.


Product Features:

- Brannan unique weatherproof design
- Maximum, current and minimum readings simultaneously
- High accuracy
- Clear, easy to read LCD
- Hanging hook
- Customer branding available (MOQs apply)

Product Specifications:

Temperature Range:	-20°C to 50°C/°F (switchable)
Accuracy:	+/-1°C (between 0°C and 50°C)
Ingress Protection:	IP66
Display Resolution:	0.1°C/0.1°F - current temperature 1.0°C/2.0°F - max/min temperature
Sampling Rate:	Every 10 seconds
Battery:	1 x AAA
Customer Logo:	Available on request (MOQ apply)
CE & RoHS/WEEE:	Compliant
Hazard Information (SDS):	See www.brannan.co.uk for information
LCD Dimensions:	15.3mm x 52.3mm (current temperature display)
Product Dimensions:	210mm x 70mm x 20.5mm
Product Weight:	150g (including batteries)

Note: Current temperature LCD reads "LL.L" at -20°C and "HH.H" at 49.9°C



Description	Barcode	Product No
Weatherproof Digital 'Classic' Max Min	5 011405 124340	12/434/3

www.brannan.co.uk





Measurement for Life.



Brannan Product Data Sheet

PDS0307.20.REV0

Product Dimensions:



www.brannan.co.uk



Measurement for Life.

