

TACWISETM

worldwide



Catalogue

Issue 4 Hand | Corded | Cordless | Air | Gas | Hot / Cool Melt

FASTENING TOOLS FOR THE PROFESSIONAL

Europe's widest quality programme

Tacwise has the widest quality stapling and nailing programme to tackle virtually every fastening challenge.

Key

PSI value	Weight of tool	Staple type	Pin/nail type	Strip/coil type	Packaging type	Number of units

Production Line	Professional	Semi Professional	DIY/Semi-Pro
Offers speed and reliability for tough and repetitive work	Versatile and durable tool for frequent stapling/nailing	A quality tool but not for continuous, repetitive work	A quality, affordable tool designed for occasional use

Safety Trigger	Contact Trip (Bump Fire)	Sequential	Single Shot	Single Shot/Contact Trip	Contact Trip/Sequential
----------------	--------------------------	------------	-------------	--------------------------	-------------------------

Inch/mm Conversion Chart

mm	4	5	6	8	10	12	14	16	17	18	19	20	22	25	28	30	32	35	38	40	45	50	55	60	64	65	70	75	83	90	100	130
Inches	5/32	3/16	1/4	5/16	3/8	1/2	9/16	5/8	11/16	11/16	3/4	3/4	7/8	1	1 1/8	1 1/4	1 1/4	1 3/8	1 1/2	1 1/2	1 3/4	2	2 1/4	2 3/8	2 1/2	2 1/2	3	3 1/4	3 3/8	4	5 1/8	

Tacwise Group Plc, Sevenoaks, Kent TN14 5DF, England. T: +44 (0)844 725 9600
E: sales@tacwise.com www.tacwise.com



3-4 TACWISE STORY

Tacwise is the dominant brand associated with hand and electric stapling and nailing tackers within the UK.

5-6 ENVIRONMENTAL MANAGEMENT

Like quality, environmental management is a journey without a destination. We have to think globally and act locally. After all, we are in this together.

7-20 HAND/CABLE TACKERS

Design and engineering has been extended across a very comprehensive range, varying from small, compact and lightweight through to heavy and durable versions.

- 7-12 Z1 Series
- 13-16 Z3 Series
- 17-18 Cable Tackers
- 19 Technical Specifications & Applications
- 20 Staple Removers
- 20 A11 Hammer Tacker

21-43 CORDED ELECTRIC TACKERS

From compact through to the top of the range of corded tools.

- 21-26 Compact Electrics - Hobby 53EL, 13EL & 140EL
- 27-29 Medium Duty Electrics - 181ELS Pro, 191EL Pro & 191ELS Pro
- 30-39 Heavy Duty Electrics - Duo 50, Duo 35, Nailer 40, Nailer 50 & 400ELS Pro
- 40 Hand & Corded Tacker Kits

41-43 CORDLESS NAILERS

18v cordless nailing up to 40mm. Powerful, sturdy and convenient, the Ranger gives you the freedom to work anywhere.

- 41 Ranger 18G Brad Nailer
- 42 Ranger 16G Finish Nailer
- 43 Technical Specifications & Applications

44-46 HAND/ELECTRIC STAPLES/NAIls

Produced from premium quality raw materials our exacting specifications include tolerances of 0.1mm to ensure the most accurate and consistent stapling/nailing actions time after time.

47-82 AIR NAILING & STAPLING

Built for the professional, Tacwise is committed to creating the ultimate air fastening tools.

- 49-52 General Purpose & Upholstery Tackers & Staples
- 53-55 Narrow Crown Staplers & Staples
- 56-59 Heavy Duty & Wide Crown Staplers & Staples
- 60-66 Nailers & Pinners, Nails & Pins
- 67-74 Coil Nailers & Nails
- 75-77 Strip Nailers & Metal Connector Nailer
- 78-81 Ranger Gas Strip Nailer & Nails
- 81-82 Technical Specifications & Applications/Easy Reference

83-86 HOT & COOL MELT GUNS/GLUE

Offering a strong permanent alternative for many hobby, craft, DIY and industrial fixing jobs.

- 83-85 Glue Guns
- 86 Glue

87-88 PACKAGING INFORMATION

Our quality thinking extends from the product design and function right through to the packaging it is supplied in.

89-90 MERCHANDISING

Two different sized stand options. Various accessories allow you to create a perfect display for any combination of Tacwise products.

91 ADDITIONAL INFORMATION

Discontinued items

Why we do what we do



Tacwise

Tacwise is the dominant brand associated with hand and electric stapling and nailing tackers within the UK market. We have the widest range of quality industrial fastenings and pneumatic tackers in Europe and over 50 years of knowledge and experience.

Utilising all of our expertise we continue to create class leading tools and fasteners for the whole of Europe and beyond. Using state-of-the-art zinc and aluminium extrusion technology, learnt from the aviation industry and high performance plastics demanded by the automotive industry, Tacwise products offer the very best in performance, durability and innovation.

Care throughout the supply chain

We are committed to excellence in health and safety management and are continually seeking ways to conserve natural resources, to reduce the amount of energy we use, to eliminate pollutants and hazardous substances from our products, processes and to maximise the use of recycling.

Time and focus has been directed towards the coatings on our metal products to ensure traditional methods are changed in favour of modern eco-friendly ones without ever compromising quality. Galvanising in place of copper and nickel in place of chrome. Parts are easily disassembled in order to allow for specific recycling, such as our tackers, when compared with others, which are welded or pressed together making them impossible to repair and difficult to recycle.

We are putting the environment in front of our marketing desires so that packaging is not oversized, nor overly complicated and considerable thought into making its eventual recycling as easy as possible. Products are designed and created to achieve strength and longevity with strong materials formed into shapes able to out-perform larger heavier non eco-friendly items supplied by others.

Our worldwide customers expect us to make our designs, developments, manufacturing processes and products as energy efficient and environmentally responsible as possible. It is a continuing mission.

Like quality, environmental management is a journey without a destination. We have to think globally and act locally. After all, we are all in this together.

Stapling up to 8mm (Z1) & 14mm (Z3 & CT)

Hand Tackers

Radical design, outstanding engineering with small, large, lightweight and heavy duty models all available for the very popular 13, 53 and 140 series staples. The Tacwise programme delivers superb performance with every imaginable user comfort.



Z1-53T See-Through

Stylish, compact and lightweight but built for the professional and affordable by the hobby user too.

Z1-53T Staple Tacker Black 53/4-8mm

Semi-Professional Code: 0951 Includes: 200pcs 53 staples

Magazine Capacity: 125 Staples, 0.22kgs
 53 Staples 4-8mm
 Pack Style: Retail Clam
 Trade = 6 Units, Transit = 36 Units

Z1-53T Staple Tacker Green 53/4-8mm

Semi-Professional Code: 0858 Includes: 200pcs 53 staples

Magazine Capacity: 125 Staples, 0.22kgs
 53 Staples 4-8mm
 Pack Style: Retail Clam
 Trade = 6 Units, Transit = 36 Units

Loaded with features

All models are loaded with features including a quick release bottom loading system to make the changeover between staple lengths fast and simple. Perfect for an easy clearance in the unlikely event of a jam. All tools incorporate a stainless steel belt hook - practical when working up ladders when both hands are required to position the work piece and a personalisation window.




Quick release bottom loading system with no loose parts.



Covering the popular 13, 53 and 140 type staples.



Stainless steel belt hook and personalisation window feature on all models.



Linear Power Curve

Avoids that uncomfortable "snap" at the end of the firing cycle. All Z1, Z3 and CT series tackers incorporate this superb feature which reduces hand strain and improves the level of comfort during prolonged periods of stapling.

Stapling up to 8mm

Z1 - Compact Metal

These compact die-cast tools feature cutaway noses for enhanced firing access and broad comfortable grips to avoid hand strain, combined with low grasp heights to deliver the optimum in handling comfort, even for users with small hands.

Durable Die-Cast

With their unique metal sectioning to create additional strength and outstanding balance these die-cast tools are still lightweight at just 0.4kg.



Ultra compact with its neat lock-down handle



Cutaway nose



Ergonomic grip

Z1-140 Metal Staple Tacker 140/6-8mm

Professional	Code: 0854	Includes: 200pcs 140 staples
---------------------	------------	------------------------------

Magazine Capacity	0.4kgs	140 Staples 6-8mm	Pack Style	Retail Clam	Trade = 6 Units	Transit = 36 Units
83 Staples						

Whilst small and compact this model uses the professional 140 flat wire staple. Perfect for tradesmen wanting a small but light tool.

Tool Features

Performance, Comfort & Safety	Z1-13 / 53 / 140	Z1-13L / 53L / 140L	Z1-53T
1 Wide ergonomic grip	✓	✓	✓
2 Lock-down switch	✓	✓	✓
3 Belt hanger	✓	✓	✓
4 Personalisation window	✓	✓	✓
5 Bottom loading magazine	✓	✓	✓
6 Staple viewing window	✓	✓	✓
7 Recessed cutaway nose	✓	✓	✓
8 Impact resistant metal die-cast body	✓		
Tough polymer lightweight body		✓	✓



Z1-53 Metal Staple Tacker Kit 53/4-8mm

Professional	Code: 0889	Includes: staple remover, 200pcs 53 staples
---------------------	------------	---

Magazine Capacity	0.4kgs	53 Staples 4-8mm	Pack Style	Retail Clam	Trade = 6 Units	Transit = 36 Units
125 Staples						

Z1-53 Metal Staple Tacker 53/4-8mm

Professional	Code: 0856	Includes: 200pcs 53 staples
---------------------	------------	-----------------------------

Magazine Capacity	0.4kgs	53 Staples 4-8mm	Pack Style	Retail Clam	Trade = 6 Units	Transit = 36 Units
125 Staples						

Z1-13 Metal Staple Tacker 13/4-8mm

Semi-Professional	Code: 0882	Includes: 200pcs 13 staples
--------------------------	------------	-----------------------------

Magazine Capacity	0.4kgs	13 Staples 4-8mm	Pack Style	Retail Clam	Trade = 6 Units	Transit = 36 Units
145 Staples						

Z1-53 uses the discreet fine wire 53 type staple, popular for DIY and the Z1-13 uses the fine wire 13 type staple popular within educational establishments.

Z1L - Lightweight

Powerful but extremely lightweight at just 0.25kgs these polymer-bodied tools are tough yet comfortable to use for long periods of time.

Z1/Z1-L Tool Features


Z1 Series: comfortable and ergonomic. Incorporating a powerful range of features unseen before on traditional hand stapling tackers. Even our smallest tackers include a full steel chassis with a hardened steel magazine rail to avoid wear as the staple strip travels.



Belt hanger



Easily recyclable



Steel inner rail



Z1-140L Staple Tacker 140/6-8mm

Professional Code: 0855 Includes: 200pcs 140 staples

Magazine Capacity: 83 Staples, 0.25kgs, 140 Staples 6-8mm, Retail Clam, Trade = 6 Units, Transit = 36 Units

This is the lightweight version of the Z1-140 using the 140 flat wire professional staple. Super-light at just 0.25kgs it's perfect for the busy tradesman on the move.

Z1 Series Staple Tackers

Technical Specification

Dimensions: H 95 x W 160 x D 27mm

Code	Tool Description	Weight (kg)	Magazine Capacity	Staples Type/Length	Min. Firing from wall	Source Tagged
0854	Z1-140 Metal	0.4	83	140/6-8mm	5mm	✓
0889	Z1-53 Metal Kit	0.4	125	53/4-8mm	5mm	✓
0856	Z1-53 Metal	0.4	125	53/4-8mm	5mm	✓
0882	Z1-13 Metal	0.4	145	13/4-8mm	5mm	✓
0855	Z1-140L	0.25	83	140/6-8mm	5mm	✓
0857	Z1-53L	0.25	125	53/4-8mm	5mm	✓
0883	Z1-13L	0.25	145	13/4-8mm	5mm	✓
0951	Z1-53T (See-Through Black)	0.25	125	53/4-8mm	5mm	✓
0858	Z1-53T (See-Through Green)	0.25	125	53/4-8mm	5mm	✓

Stapling up to 8mm



Z1-53L Staple Tacker 53/4-8mm

Semi-Professional Code: 0857 Includes: 200pcs 53 staples

Magazine Capacity: 125 Staples, 0.25kgs, 53 Staples 4-8mm, Retail Clam, Trade = 6 Units, Transit = 36 Units

Z1-13L Staple Tacker 13/4-8mm

Semi-Professional Code: 0883 Includes: 200pcs 13 staples

Magazine Capacity: 145 Staples, 0.25kgs, 13 Staples 4-8mm, Retail Clam, Trade = 6 Units, Transit = 36 Units

These entry model tackers are compact, lightweight and inexpensive whilst still loaded with features. Uses the popular 53 (Z1-53L) or 13 (Z1-13L) fine wire staples.

Z3 - 3-in-1 Tackers

Designed with the professional in mind the Z3 series incorporates the most powerful performance in its class with the ability to fire three types of fastenings (staples, nails and headless pins). Includes many superb features.



Z3-140 Metal Staple/Nail Tacker 140/6-14mm 180/15mm 180/15mm headless

Professional	Code: 0806	Includes: 200pcs 140 staples
Magazine Capacity 90 Nails 83 Staples	140 Staples 6-14mm 180 Nails 15mm	180/15mm Headless Pin
0.9kgs	Retail Clam	Pack Style
		Trade = 6 Units Transit = 12 Units

Sitting at the top of the range this all professional workhorse drives 140 flat wire staples and is built to withstand years of trouble-free use... a true heavyweight.

Z3-53 Metal Staple/Nail Tacker 53/6-14mm 180/15mm 180/15mm headless

Semi-Professional	Code: 0808	Includes: 200pcs 53 staples
Magazine Capacity 90 Nails 125 Staples	53 Staples 6-14mm 180 Nails 15mm	180/15mm Headless Pin
0.9kgs	Retail Clam	Pack Style
		Trade = 6 Units Transit = 12 Units

The 53 discreet fine wire version of the heavyweight all professional tool. Ideally suited to tradesmen on the move and working around site.

Z3-13 Metal Staple/Nail Tacker 13/6-14mm 180/15mm 180/15mm headless

Semi-Professional	Code: 0880	Includes: 200pcs 13 staples
Magazine Capacity 90 Nails 150 Staples	13 Staples 6-14mm 180 Nails 15mm	180/15mm Headless Pin
0.9kgs	Retail Clam	Pack Style
		Trade = 6 Units Transit = 12 Units



Durable Die Cast

Ultra tough and weighing in at a heavyweight 0.9kgs these die cast tools reach the highest standards within their category. Utilising Z-tec zinc die cast extrusion technology, resulting in fewer parts for enhanced reliability.



Margin edge adjuster



Perfect for heavy-duty applications

Stapling up to 14mm & Nailing up to 15mm

Z3L - Lightweight Polymer 3-in-1 Tackers

Tough and durable but extremely lightweight at just 0.4kg the polymer line is a big hit with tradesmen on the move.



Tool Features

	1	2	3	4	5	6	7	8	9								
Performance, Comfort & Safety	Wide ergonomic grip	Rubber handle grip	Staple viewing window	Recessed cutaway nose	Belt hanger	Lock-down switch	Pull-out handle lock	Impact power adjuster	Personalisation window	Bottom loading magazine	Impact resistant metal die-cast body	Extended cutaway nose	Tough polymer lightweight body	Full length cable guide	Removable margin edge adjuster	BT Approved	Cable stapling switch
Z3-13 / 53 / 140	✓		✓	✓	✓	✓		✓	✓	✓	✓						✓
Z3-13L / 53L / 140L	✓		✓	✓	✓	✓		✓	✓	✓			✓				✓
Z3 4-in-1	✓	✓	✓				✓	✓		✓		✓	✓	✓			✓
CT-45 / 60	✓		✓				✓	✓		✓		✓	✓	✓			✓
Z3-CT45 / 60	✓		✓	✓	✓		✓	✓	✓	✓	✓	✓	✓	✓			✓
Combi Cable Tacker				✓			✓	✓		✓				✓			

Z3-140L Polymer Heavy-Duty Kit

140/6-14mm 180/15mm 180/15mm headless

Semi-Professional Code: 0878 Includes: staple remover, 200pcs 140 staples

Magazine Capacity: 90 Nails, 83 Staples | 0.4kgs | 140 Staples 6-14mm, 180 Nails 15mm | 180/15mm Headless Pin | Pack Style | Retail Clam | Trade = 6 Units, Transit = 12 Units

This handy kit includes the super-light Z3L tacker for the 140 flat wire staple, a pro staple remover and a starter kit of staples.

Z3-140L Staple/Nail Tacker

140/6-14mm 180/15mm 180/15mm headless

Semi-Professional Code: 0807 Includes: 200pcs 140 staples

Magazine Capacity: 90 Nails, 83 Staples | 0.4kgs | 140 Staples 6-14mm, 180 Nails 15mm | 180/15mm Headless Pin | Pack Style | Retail Clam | Trade = 6 Units, Transit = 12 Units

Incorporating all of the features of the Z3 metal bodied tool, this model is ultra-light but still robust with its internal steel running gear and external polymer body construction.



Z3 4-in-1 Tacker



Z3 4-in-1 is also available as a value added kit. See page 38 (Cable staples supplied in kit may not be white)

Z3 4-in-1 Features

Loading any one of 4 different types of staple/nail is simple and easy, as is switching the small lever for cable staples. With the added benefits from bottom loading as with other Tacwise Z3 tools.



Z3 4-in-1 Staple/Nail Tacker

53/8-14mm 180/15mm 180/15mm headless CT-60/12-14mm

Semi-Professional Code: 1022 Includes: 200pcs 53 staples
 Magazine Capacity: 85 Nails, 150 Staples, 85 Cable Staples | 0.4kgs | 53 Staples 8-14mm, 180 Nails 15mm | CT-60 Staples 12-14mm, 180/15mm Headless Pin | Pack Style | Retail Clam | Trade = 6 Units, Transit = 12 Units

Z3-53L Staple/Nail Tacker

53/6-14mm 180/15mm 180/15mm headless

Semi-Professional Code: 0847 Includes: 200pcs 53 staples
 Magazine Capacity: 90 Nails, 125 Staples | 0.4kgs | 53 Staples 6-14mm, 180 Nails 15mm | 180/15mm Headless Pin | Pack Style | Retail Clam | Trade = 6 Units, Transit = 12 Units

Z3-13L Staple/Nail Tacker

13/6-14mm 180/15mm 180/15mm headless

Semi-Professional Code: 0881 Includes: 200pcs 13 staples
 Magazine Capacity: 90 Nails, 150 Staples | 0.4kgs | 13 Staples 6-14mm, 180 Nails 15mm | 180/15mm Headless Pin | Pack Style | Retail Clam | Trade = 6 Units, Transit = 12 Units

Driving fine wire staples up to 14mm (and nails and pins), this tool is perfect for tasks where leaving a neat/discreet staple head showing is essential.

Cable Tackers

Designed to bring speed, comfort and precision to the task of low voltage cable tacking, these high impact tools feature a new advanced system for recoilless action and incorporate many safety features.

Ideal for:

Cables up to 4.5mm diameter
Lightweight CT-45 and Z3-CT45

Telephone 6 pair 0.5mm

Alarm to BS4773

Alarm 4 core

Cables up to 6mm diameter
Lightweight CT-60 and Z3-CT60

Cat 5e/data cable

Cat 6 cable (Z3-CT60 Tacker)

Coaxial air spaced 1mm white

Satellite coaxial screened

Coaxial air spaced 1mm brown

2 core electric cable, in low voltage applications



Combi Cable Tacker

CT-45/8-10mm CT-60/10-14mm

Professional Code: 1153

Magazine Capacity
85 Staples (CT-45)
82 Staples (CT-60) 0.8kgs

Pack Style Retail Clam Trade = 6 Unit
Transit = 12 Units

A unique all metal cable tacker driving both CT-45 and CT-60 staples through the same tool without the need for any adjustment.

Cable stapling up to 14mm

New Z3-CT60... now ideal for Cat 5 & Cat 6 Cable



Z3-CT45/60 All Metal



Ideal for fixing neatly and securely into tight corners. Perfect for low voltage telecommunications and security cabling. Plus a wide range of electrical related installations.

Lightweight

CT-45 Cable Tacker CT-45/8-10mm

Professional Code: 0320

Magazine Capacity
75 Staples 0.4kgs CT-45 Staples 8-10mm Pack Style Retail Clam Trade = 6 Units
Transit = 12 Units

CT-60 Cable Tacker CT-60/10-14mm

Professional Code: 0321

Magazine Capacity
75 Staples 0.4kgs CT-60 Staples 10-14mm Pack Style Retail Clam Trade = 6 Units
Transit = 12 Units

Ideal for high level installation of cabling and for the mobile user where the reduced weight will take the strain out of larger fixing tasks.



Lightweight CT-45/60

All Metal

Z3-CT45 Metal Cable Tacker CT-45/8-10mm

Professional Code: 0809 Includes: 200pcs CT45 cable staples

Magazine Capacity
75 Staples 0.9kgs CT-45 Staples 8-10mm Pack Style Retail Clam Trade = 6 Units
Transit = 12 Units

Z3-CT60 Metal Cable Tacker CT-60/10-14mm

Professional Code: 0926 Includes: 200pcs CT60 cable staples

Magazine Capacity
75 Staples 0.9kgs CT-60 Staples 10-14mm Pack Style Retail Clam Trade = 6 Units
Transit = 12 Units

BT approved, these top end tools make light work of fastening telecommunications, alarm and other low voltage cables.

Z3 Series Staple, Nail & Cable Tackers

Technical Specifications

Code	Tool Description	Dimensions (H x W x D)	Weight (kg)	Magazine Capacity		Fasteners Type/length (mm)		Min. Firing from wall	Source Tagged
				Nails & Pins	Staples	Nails & Pins	Staples		
0806	Z3-140 Metal	230 x 220 x 33	0.9	90	83	180/15 180/15 headless	53/4-14	5mm	✓
0808	Z3-53 Metal	230 x 220 x 33	0.9	90	125	180/15 180/15 headless	53/4-14	5mm	✓
0880	Z3-13 Metal	230 x 220 x 33	0.9	90	150	180/15 180/15 headless	53/4-14	5mm	✓
0878	Z3-140L Polymer Heavy-Duty Kit	230 x 220 x 33	0.4	90	83	180/15 180/15 headless	53/6-14	5mm	✓
0807	Z3-140L	230 x 220 x 33	0.4	90	83	180/15 180/15 headless	53/6-14	5mm	✓
0847	Z3-53L	230 x 220 x 33	0.4	90	125	180/15 180/15 headless	53/6-14	5mm	✓
0881	Z3-13L	230 x 220 x 33	0.4	90	150	180/15 180/15 headless	53/6-14	5mm	✓
1022	Z3 4-in-1	120 x 190 x 33	0.4	85 Cable staples = 85	150	180/15 180/15 headless	53/8-14 CT-60/12-14	5mm	✓
0320	CT-45 Cable Tacker	117 x 185 x 30	0.4	-	75	-	CT-45/8-10	5mm	✓
0321	CT-60 Cable Tacker	117 x 185 x 30	0.4	-	75	-	CT-60/10-14	5mm	✓
1153	Combi Cable Tacker	114 x 188 x 25	0.8	-	85 82	-	CT-45/8-10 CT-60/10-14	5mm	
0809	Z3-CT45 Metal Cable Tacker	230 x 220 x 33	0.9	-	75	-	CT-45/8-10	5mm	✓
0926	Z3-CT60 Metal Cable Tacker	230 x 220 x 33	0.9	-	75	-	CT-60/10-14	5mm	✓
0206	Pro Staple Remover	180 x 27 x 32	0.1	-	-	-	-	-	✓
1073	91 Staple Remover	192 x 27 x 46	0.1	-	-	-	-	-	✓
0322	A11 Hammer Tacker	168 x 21 x 85	0.9	-	150	-	140/6-10	-	✓

Tool Applications

Application	Z1-53	Z1-53L	Z1-53T	Z1-140	Z1-140L	Z1-13	Z1-13L	Z3-53	Z3-53L	Z3-140	Z3-140L	Z3-13	Z3-13L	Z3-4-in-1	Z3-CT45	Z3-CT60	CT-45	CT-60	CT-Combi	A11
Alarm/data cable																				
Blinds & awnings																				
Carpeting & underlay				•	•					•	•									•
Display/shop fitting				•	•	•	•			•	•									•
Exhibition/shows				•	•	•	•			•	•									•
Fabrics & blinds	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
Hobby crafts	•	•	•					•	•											
Insulation				•	•					•	•									•
Moulding & beading								•	•	•	•									
Netting/wire fencing				•	•					•	•							•	•	•
Picture framing	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
Posters/displays	•	•	•			•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
Plastic sheeting				•	•					•	•									•
Roofing				•	•					•	•									•
Schools/education	•	•	•			•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
Telecommunications														•	•	•	•	•	•	
Theatre/film scenery	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
Trellis/garden	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
Upholstery				•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
Window dressing						•	•					•	•							

Staple Removers



Pro Staple Remover

Professional Code: 0206



Retail Clam



Trade = 12 Units
Transit = 48 Units

Grips and retains staples whilst removing them. Ideal for lifting out many types of staples. from panelling, insulation & lining, upholstery, carpet underlay and many more... The ergonomic grip provides comfort during extended periods of use.

91 Staple Remover

Professional Code: 1073



Retail Clam



Trade = 12 Units
Transit = 48 Units

Removes 91 type and other narrow crown staples from timber. Incorporating a stepped lifting device this remover will handle staples with both short and long legs. With ergonomic grip.

Hammer Tacker



A11 (140 Type) Hammer Tacker 140/6-10mm

Professional Code: 0322



150 Staples



0.9 kgs



140 Staples 6-10mm



Retail Box



Trade = 10 Units
Transit = 20 Units

All steel "slap" hammer designed with few working parts for years of trouble-free operation. Popular for securing flooring underlay, plastic sheeting and breather membrane.

New heavy duty hammer up to 12mm coming April 2014

Stapling up to 40mm & Nailing up to 50mm

Just load, plug in and fire

Utilising our 50 years of knowledge, experience and expertise, our range of corded electric tackers offer the very best in performance across a range of stapling and nailing tasks. There's no need for batteries, gas cells or compressors; simply load, switch on the power and you're ready to go. Excellence in design and engineering as standard across a comprehensive range of fastening tools ranging from small, compact and lightweight through to heavy duty nailers and staplers.

1. Compact

Our range of semi-pro and professional models are small, fast and lightweight. An ideal step-up from manual hand tackers, these compact electric tackers are highly balanced with an ergonomic design that makes repetitive stapling tasks easy and comfortable.

Perfect for applications including upholstery, insulation, picture framing, wire fencing carpeting and more.

2. Medium Duty

With tremendous versatility, Tacwise Medium Duty electric tackers offer extraordinary value for money and are a must for every tool bag. Coupling superb performance with user comfort, our Medium Duty electric tackers are extremely fast semi-professional tools capable of firing nails up to 35mm.

Hugely capable and loaded with features, these tackers are ideal for applications including cabinet assembly, door frames, carpeting, soft wood flooring and many more second fix tasks.

3. Heavy Duty **NEW**

The new generation of Tacwise electrics feature redesigned electronics and enhanced engineering, making them the tool of choice for the discerning tradesman.

These tools eat up second fix and reconstruction tasks with speed and precision. With unrivalled performance in their class, our Heavy Duty electric tackers boast a range of dynamic and innovative new features.

Essential for tradesmen, these tools will make light work of a range of second fix and making good tasks including flooring, sub flooring, underlay gripper, insulation and more.



Corded Electric Tackers



Supplied with either UK, Euro or other International plug/cable variations.

Stapling up to 14mm & Nailing up to 15mm

Compact Electrics

Always ready at hand these tackers are designed with the minimum of parts to enhance reliability and reduce weight which, combined with a robust chassis and body materials, result in the tools delivering maximum durability.

DIY/Semi-Pro... 53EL & 13EL

These ultra-compact corded tackers boast a host of dynamic and innovative features and are ideal for professional and lightweight applications. Featuring an all polymer body, the compact 53EL uses the popular 53 type (DIY, fine wire) staple, ideal for professionals seeking discreet fastening and light users alike and the 13EL uses the fine wire 13 type staple particularly popular in schools.



Great for retail

Compressed into a neat clam which will hang on Euro hooks/pegs or stand alone on a display shelf.

Hobby 53EL 53/6-14mm 180/15mm

DIY/Semi-Pro	Code: 0273	Includes: This pack does not contain nails or staples
	Code: 0434 (EURO)	Includes: This pack does not contain nails or staples

Magazine Capacity: 90 Nails / 125 Staples | Weight: 0.75kgs | Staple Size: 53 Staples 6-14mm / 180 Nails 15mm | Pack Style: Retail Box | Trade = 1 Unit / Transit = 10 Units

Hobby 53EL 53/6-14mm 180/15mm

DIY/Semi-Pro	Code: 0865	Includes: 100pcs 180 nails, 200pcs 53 staples
	Code: 0879 (EURO)	Includes: 100pcs 180 nails, 200pcs 53 staples

Magazine Capacity: 90 Nails / 125 Staples | Weight: 0.75kgs | Staple Size: 53 Staples 6-14mm / 180 Nails 15mm | Pack Style: Retail Clam | Trade = 1 Unit / Transit = 10 Units

Hobby 13EL (Euro) 13/6-14mm 180/15mm

DIY/Semi-Pro	Code: 0962	Includes: 100pcs 180 nails, 200pcs 13 staples
--------------	------------	---

Magazine Capacity: 90 Nails / 150 Staples | Weight: 0.75kgs | Staple Size: 13 Staples 6-14mm / 180 Nails 15mm | Pack Style: Retail Clam | Trade = 1 Unit / Transit = 10 Units

Hobby 53EL is also available as a value added kit. See page 38



Tool Applications

	Blinds & awnings	Carpeting & underlay	Display/shop fitting	Exhibition/shows	Fabrics & blinds	Hobby crafts	Insulation	Moulding & beading	Netting/wire fencing	Picture framing	Posters/displays	Plastic sheeting	Roofing	Schools/education	Theatre/film scenery	Trellis/garden	Upholstery	Window dressing
Hobby 53EL					•	•		•	•	•	•			•	•	•	•	
Hobby 13EL			•	•	•			•		•	•			•	•		•	•
140EL	•	•	•	•	•		•	•	•			•	•			•	•	

Stapling up to 14mm & Nailing up to 15mm



Semi-Pro... 140EL

Suitable for professionals such as general builders and tradesmen. Taking the popular 140 flat wire staples in lengths 6mm to 14mm and 180/15mm series nails.

140EL 140/6-14mm 180/15mm

Semi-Pro Code: 0274 Includes: 1000pcs 180 nails, 1000pcs 140 staples

Magazine Capacity: 90 Nails, 83 Staples | Weight: 0.75kgs | Includes: 140 Staples 6-14mm, 180 Nails 15mm | Pack Style: Retail Box | Trade = 1 Unit, Transit = 10 Units

140EL (Euro) 140/6-14mm 180/15mm

Semi-Pro Code: 0928 Includes: 100pcs 180 nails, 200pcs 140 staples

Magazine Capacity: 90 Nails, 83 Staples | Weight: 0.75kgs | Includes: 140 Staples 6-14mm, 180 Nails 15mm | Pack Style: Retail Clam | Trade = 1 Unit, Transit = 10 Units

Technical Specifications

Dimensions: H 135 x W 195 x D 55mm

Code	Tool Description	Weight (kg)	Magazine Capacity		Fastener Type/Length (mm)		Min. Firing from wall	Source Tagged
			Nails	Staples	Nails	Staples		
0865	Hobby 53EL	0.75	90	125	180/15	53/6-14	6mm	✓
0273	Hobby 53EL	0.75	90	125	180/15	53/6-14	6mm	✓
0879	Hobby 53EL Euro	0.75	90	125	180/15	53/6-14	6mm	✓
0434	Hobby 53EL Euro	0.75	90	125	180/15	53/6-14	6mm	✓
0962	Hobby 13EL Euro	0.75	90	150	180/15	13/6-14	6mm	✓
0274	140EL	0.75	90	83	180/15	140/6-14	6mm	✓
0928	140EL Euro	0.75	90	83	180/15	140/6-14	6mm	✓

Tool Features


Performance, Comfort & Safety	Hobby 53EL	Hobby 13EL	140EL
1 Long power cord	✓	✓	✓
2 Wide ergonomic grip	✓	✓	✓
3 On/off switch	✓	✓	✓
4 Personalisation window	✓	✓	✓
5 Belt hanger	✓	✓	✓
6 Tough polymer lightweight body	✓	✓	✓
7 On/off light indicator	✓	✓	✓
8 Safety lock switch	✓	✓	✓
9 Trigger	✓	✓	✓
10 Air vents	✓	✓	✓
11 Bottom loading magazine	✓	✓	✓
12 Staple/nail viewing window	✓	✓	✓

Loaded with features

Each with their own powerful features Tacwise compact electric tools are carefully designed for user safety and convenience.

Bottom Loading

Full strip bottom loading for speed and simplicity with no loose parts.



Features include the light indicator on/off for safety, belt hanger for convenience and personalisation window. Easily disassembled for recycling.



Stapling up to 30mm & Nailing up to 35mm

Medium Duty Electrics

An essential for the busy tradesman these medium duty electrics will save time and effort day in, day out.

Suitable for a wide range of second fix and fastening tasks, these electric nailers and staplers achieve great results with minimum effort. All tools in this range feature a positive action trigger, a separate on/off switch and nose safety device which much be pressed against the work piece to fire.



181ELS

The dedicated nailing incarnation of our top-selling 191EL/191ELS Pro, the 181ELS is a versatile nailer that fires 180 nails up to 35mm.

Feature-rich and light-weight, the 181ELS is a highly practical and lightweight nailer that's perfect for repetitive nailing tasks.

Master Nailer™ 181ELS Pro Electric Nailer 180/15-35mm

Semi-Pro	Code: 1176	Includes: 2000pcs 180 nails
	Code: 1177 (EURO)	Includes: 200pcs 180 nails

Magazine Capacity: 100 Nails | Weight: 1.6kgs | Nail Size: 180 Nails 15-35mm | Pack Style: Carry Case | Trade = 1 Unit, Transit = 4 Units

191EL Ultimate Versatility

191EL Pro is a 'must have' for all professional tradesmen tackling any number of second fix and making good tasks as well as precision jobs in the workshop. Hugely popular for flooring including boarding out and soft wood floorboards.



Popular for securing glued items to avoid movement.



Light, compact size for jobs that are difficult to access.



Great for getting into tight corners. Excellent for dry wall lining with 91DP (divergent point) staples.

191EL is the tool everyone should have in their toolbag regardless of which other staple or nail guns they own. The best value, most versatile corded stapler/nailer on the market.



191EL

Firing seven different lengths of nails and four different lengths of staple, the 191EL Pro is a nailer & stapler that's perfect for a wide range of fixing applications.

Versatile, ergonomic and lightweight; the 191EL Pro is perfect for continuous nailing tasks, especially those in difficult to reach areas. Simple, easy to use and the fastest tool of its kind, it's no wonder the 191EL Pro is the UK's favourite nailer/stapler.



Master Nailer™ 191EL Pro Electric Nailer/Stapler 91/15-30mm 180/10-35mm

Semi-Pro	Code: 0326	Includes: 500pcs 180 nails & 500pcs 91 staples
----------	------------	--

Magazine Capacity: 100 Nails, 100 Staples | Weight: 1.8kgs | Nail/ Staple Size: 91 Staples 15-30mm, 180 Nails 10-35mm | Pack Style: Retail Box | Trade = 1 Unit, Transit = 6 Units

Semi-Pro	Code: 0327	Includes: 2000pcs 180 nails & 2000pcs 91 staples
	Code: 0190 (EURO)	Includes: 500pcs 180 nails & 500pcs 91 staples

Magazine Capacity: 100 Nails, 100 Staples | Weight: 1.8kgs | Nail/ Staple Size: 91 Staples 15-30mm, 180 Nails 10-35mm | Pack Style: Carry Case | Trade = 1 Unit, Transit = 4 Units

Master Nailer™ 191ELS Pro Electric Nailer/Stapler 91/15-30mm 180/10-35mm

Not featured

Semi-Pro	Code: 1180	Includes: This pack does not contain nails or staples
	Code: 1200 (EURO)	Includes: This pack does not contain nails or staples

Magazine Capacity: 100 Nails, 100 Staples | Weight: 1.8kgs | Nail/ Staple Size: 91 Staples 15-30mm, 180 Nails 10-35mm | Pack Style: Carry Case | Trade = 1 Unit, Transit = 4 Units

New Model with quick release nose available Jan 2014



Stapling up to 30mm & Nailing up to 50mm

Medium Duty Electrics

Tool Applications

Application	181ELS Pro	191EL Pro	191ELS Pro		181ELS Pro	191EL Pro	191ELS Pro
Cabinet/woodwork assembly	•	•	•	Plasterboard		•	•
Cane/rattan furniture	•	•	•	Cabins, mobile homes, caravans	•	•	•
Carpeting & underlay	•			Saunas	•	•	•
Display/shop fitting	•	•	•	Sheds & garden buildings	•	•	•
Door frames & skirting	•	•	•	Shoe repair		•	•
Drawer bottoms	•	•	•	Soft & medium wood flooring	•	•	•
Exhibition/show(s)	•	•	•	Staircase/bannister construction	•	•	•
External pelmets	•	•	•	Sub flooring/boarding out	•	•	•
Fencing	•	•	•	Tacking plasterboard/pre-screwing	•	•	•
Gripper & thresholds	•	•	•	Tacking with glue applications	•	•	•
Insulation/sheeting & lining		•	•	Theatre/film scenery	•	•	•
Moulding & beading	•	•	•	Tongue & groove flooring	•		
Netting/wire fencing		•	•	Trellis/panelling	•	•	•
Pet cages, runs & enclosures	•	•	•	Window dressing		•	•
Picture/mirror framing	•	•	•				

Technical Specifications

Code	Tool Description	Dimensions (H x W x D)	Weight (kg)	Magazine Capacity		Fastener Type/Length (mm)		Min. Firing from wall	Source Tagged
				Nails	Staples	Nails	Staples		
1176	181EL Pro	230 x 255 x 68	1.6	100	-	180/15-35	-	2mm	✓
1177	181EL Pro Euro	230 x 255 x 68	1.6	100	-	180/15-35	-	2mm	✓
0326	191EL Pro (Boxed)	230 x 255 x 68	1.8	100	100	180/10-35	91/15-30	2mm	✓
0327	191EL Pro	230 x 255 x 68	1.8	100	100	180/10-35	91/15-30	2mm	✓
0190	191EL Pro Euro	230 x 255 x 68	1.8	100	100	180/10-35	91/15-30	2mm	✓
1180	191ELS Pro	230 x 255 x 68	1.8	100	100	180/10-35	91/15-30	2mm	✓
1200	191ELS Pro Euro	230 x 255 x 68	1.8	100	100	180/10-35	91/15-30	2mm	✓

Tool Features

Performance, Comfort & Safety	181ELS Pro	191EL Pro	191ELS Pro
Single shot trigger	✓	✓	✓
Quick release loading	✓	✓	✓
Quick release nose plate	✓		✓
Nose protector	✓	✓	✓
Nose safety device	✓	✓	✓
Safety on/off switch	✓	✓	✓
Nail/staple viewing window	✓	✓	✓
Impact resistant industrial body	✓	✓	✓
Spare noses – 5pcs	✓	✓	✓
Max. speed per minute	30	30	30

Replacement Nose Pieces

Code	Tool Description	Pack Qty.
0849	Nose 191EL (Orange)	5
0848	Nose 181EL (Orange)	5
1172	Nose 181ELS (Black)	5

Heavy Duty Electrics

New for 2013; the next generation of Tacwise electric nailers and staplers. Built for the professional, these electric tools will eat up second fix jobs with ease and comfort.

Offering the very best in performance, innovation and versatility, the new corded nailers and staplers from Tacwise are perfect for a wide range of tasks.

NEW



Tool Features

Performance, Comfort & Safety	1	2	3	4	5	6	7	8	9	Max. speed per minute	
	Single shot trigger	Quick release loading	Quick release nose plate	Nose protector	Nose safety device	Safety on/off switch	Nail/staple viewing window(s)	Impact resistant industrial body	Belt hanger		Safety on off light
Duo 35	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	30
Duo 50	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	30
400ELS	✓	✓	✓	✓	✓	✓	✓	✓			30
18G/50	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	30
16G/45	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	30

Stapling up to 45mm & Nailing up to 50mm



Duo 50

The world's first corded 50mm nailer and 45mm stapler, the Duo 50 is a high spec tool that sits at the top of the new generation Tacwise tool line. It has an air tool magazine for fast easy loading, a flip open nail-gate, a belt hook and a compact nose to get into those hard-to-reach areas.

Master Nailer™ Duo 50 Electric Nailer/Stapler

91/20-45mm

180/20-50mm

Professional	Code: 1166	Includes: This pack does not contain nails or staples
	Code: 1168 (EURO)	Includes: This pack does not contain nails or staples

NEW

- Magazine Capacity: 100 Nails / 100 Staples
- ⚠️ 2.7kgs
- 🔧 91 Staples 20-45mm / 180 Nails 20-50mm
- 📦 Pack Style: Carry Case
- 📦 Trade = 1 Unit / Transit = 4 Units



Stapling up to 45mm & Nailing up to 50mm

18G/50 Nailer

This dedicated nailing tool has a precision air tool construction and will accurately drive 18 gauge brads with little marking to the surface of the timber. Ideal to speed through a wide variety of tasks this will save the busy tradesman a lot of time and free one hand to guide and position the work piece. Also ideal for a temporary fix during glue drying.



Master Nailer™ 18G/50 Electric Nailer 180/20-50mm

Professional	Code: 1183	Includes: This pack does not contain nails
	Code: 1207 (EURO)	Includes: This pack does not contain nails


Magazine Capacity 100 Nails	2.7kgs	180 Nails 20-50mm	Carry Case No colour sleeve	Trade = 1 Unit Transit = 4 Units
--------------------------------	--------	-------------------	--------------------------------	-------------------------------------

NEW

Available January 2014

All new magazine

The 18G/50 Nailer and 16G/45 Finish Nailer both embrace an all new magazine with a high level of precision and the 18G tool featured has two viewing windows. As with all new generation Tacwise electrics there is a quick release nail gate and easy close side load system.



16G/45 Finish Nailer

Firing the popular 16 gauge finish nail (a heavier nail than the 18 gauge version) this tool is perfect for a wide selection of applications and in particular those requiring a heavier more secure second fix nail.




Master Nailer™ 16G/45 Electric Finish Nailer 16G/20-45mm

Professional	Code: 1187	Includes: This pack does not contain nails
	Code: 1208 (EURO)	Includes: This pack does not contain nails

Magazine Capacity 100 Nails	2.7kgs	16G Nails 20-45mm	Carry Case no colour sleeve	Trade = 1 Unit Transit = 4 Units
--------------------------------	--------	-------------------	--------------------------------	-------------------------------------

NEW


Available January 2014



No gas or compressor required

Fast and convenient these second fix, dedicated nailers, are quick to load and do not require gas packs or compressors... simply load, plug in / turn on and fire. Perfect in the work shop or for the busy tradesman on the move.

Stapling up to 45mm & Nailing up to 50mm



Duo 35

A compact tool with tremendous versatility the Duo 35 gives unrivalled performance and eats up second fix jobs with speed and precision. With all-new electronics, enhanced switch-gear and improvements throughout, this nailer and stapler is another great addition to the exciting new generation of electric tools from Tacwise.

Perfect for precision as well as demanding fixing jobs, the Duo 35 has been re-designed with the tradesmen in mind so you can work on flooring, panelling or skirting, architrave and more.

The Duo 35 is your essential tool; made for second fix jobs, compact, durable and affordable.

NEW



Master Nailer™ Duo 35 Electric Nailer/Stapler 91/15-30mm 180/15-35mm

Professional	Code: 1165	Includes: This pack does not contain nails or staples
	Code: 1167 (EURO)	Includes: This pack does not contain nails or staples

- Magazine Capacity: 100 Nails / 100 Staples
- Weight: 2.10kgs
- 91 Staples 15-30mm / 180 Nails 15-35mm
- Pack Style: Carry Case
- Trade = 1 Unit / Transit = 4 Units

New model for 71 upholstery staple coming April 2014




Outstanding Quality and Performance

Our dedication to delivering design and engineering excellence has led to our exciting range of new Electric Tackers. Utilising our 50 years knowledge, expertise and experience, these tools form the vanguard of our New Generation of class-leading corded nailers and staplers. A must have for every tradesman tackling second fix, restoration and repair projects.

Duo 35 Tool Features

The re-designed Duo 35 is fully loaded with host of innovative features, making it the tool of choice for the discerning tradesman. Features include a flip-open nail gate, an air-tool magazine, a nose safety device, power light and a separate on/off switch. Compact, durable and affordable; the Duo 35 is your essential tool.



Quick release magazine

Flip-open nail gate

Inclined Professional Nailers

Sitting at the top of the Tacwise tool line, the 400ELS offers ultimate convenience with the inclined magazine system.

400ELS Pro

The Master Nailer™ 400ELS is fast and light and its handy angled design makes it ideal for tackling fixing tasks where elbow room or access is at a premium – such as under stairs, behind baths or sanitaryware etc. Delivering the closest thing to air-tool performance in an electric nailer, the 400ELS fires six lengths of nail up to 40mm, and at speeds of up to 30 nails per minute – more than enough for practically all purposes.



An unrivalled performance

400ELS (the all new nailer replacing 400EL) is a little different from the other Tacwise electrics. The key feature is its angled magazine which makes the tool extremely compact and capable of firing into very tight spaces. It is also the only model to include a rubber grip and surface pad on the top of the tool and a removeable wire stand, which can be clipped on and off in an instant, positions the tool upright 'ready to go' when used in tasks such as securing floor boards and boarding out.



400ELS incorporates a rifle butt style quick release catch for rapid reloading and a unique easy access nail gate makes freeing fastenings simple in the unlikely event of a misfire.

Stapling up to 45mm & Nailing up to 50mm



NEW

Master Nailer™ 400ELS Pro Electric Angled Nailer 500/15-40mm

Professional	Code: 0733	Includes: This pack does not contain nails
	Code: 0876 (EURO)	Includes: This pack does not contain nails

Magazine Capacity 100 Nails	1.8kgs	500 Angled Nails 15-40mm	Carry Case	Trade = 1 Unit Transit = 4 Units
--------------------------------	--------	-----------------------------	------------	-------------------------------------



Complete in their tough work case

Tough professional work/carry cases are standard with most corded tools including the heavy duty and inclined models...look for the symbol alongside each tool to see if it's supplied in a box, carry case or retail clampack.

Carry Case

Stapling and Nailing up to 15mm

Heavy Duty Electrics

Technical Specifications

Code	Tool Description	Dimensions (H x W x D)	Weight (kg)	Magazine Capacity		Fasteners Type/length (mm)		Min. Firing from wall	Source Tagged
				Nails	Staples	Nails	Staples		
1165	Duo 35	226 x 271 x 66	1.7	100	100	180/15-35	91/15-30	2mm	✓
1167	Duo 35 Euro	226 x 271 x 66	1.7	100	100	180/15-35	91/15-30	2mm	✓
1166	Duo 50	294 x 275 x 73	2.4	100	100	180/20-50	91/20-45	2mm	✓
1168	Duo 50 Euro	294 x 275 x 73	2.4	100	100	180/20-50	91/20-45	2mm	✓
1183	Nailer 50 18G Brad Nailer	294 x 275 x 73	2.4	100	100	180/20-50	91/20-45	2mm	
1207	Nailer 50 18G Brad Nailer Euro	294 x 275 x 73	2.4	100	100	180/20-50	91/20-45	2mm	
1187	Nailer 40 16G Finish Nailer	294 x 275 x 73	2.4	100	100	180/20-50	91/20-45	2mm	
1208	Nailer 40 16G Finish Nailer Euro	294 x 275 x 73	2.4	100	100	180/20-50	91/20-45	2mm	
0733	400ELS Inclined Nailer	210 x 290 x 57	1.7	100	100	500/15-40		2mm	✓
0876	400ELS Inclined Nailer Euro	210 x 290 x 57	1.7	100	100	500/15-40		2mm	✓

Tool Applications

Application	Duo 35	Duo 50	18G/50	16G/45	400ELS
Cabinet/woodwork assembly	•	•	•	•	•
Cane/rattan furniture	•	•	•	•	•
Carpeting & underlay					
Display/shop fitting	•	•	•	•	•
Door frames & skirting	•	•	•	•	•
Drawer bottoms	•	•	•	•	•
Exhibition/show(s)	•	•	•	•	•
External pelmets	•	•	•	•	•
Fencing	•	•	•	•	•
Garden furniture	•	•	•	•	•
Gripper & thresholds	•	•	•	•	•
Insulation/sheeting & lining	•	•	•	•	•
Moulding & beading	•	•	•	•	•
Netting/wire fencing	•	•	•	•	•
Pet cages, runs & enclosures	•	•	•	•	•
Picture/mirror framing	•	•	•	•	•
Plasterboard	•	•	•	•	•
Cabins, mobile homes, caravans	•	•	•	•	•
Saunas	•	•	•	•	•
Sheds & garden buildings	•	•	•	•	•
Shoe repair	•	•	•	•	•
Soft & medium wood flooring	•	•	•	•	•
Soffits & fascias	•	•	•	•	•
Staircase/bannister construction	•	•	•	•	•
Sub flooring/boarding out	•	•	•	•	•
Tacking plasterboard/pre-screwing	•	•	•	•	•
Tacking with glue applications	•	•	•	•	•
Theatre/film scenery	•	•	•	•	•
Tongue & groove flooring	•	•	•	•	•
Trellis/panelling	•	•	•	•	•
Window dressing	•	•	•	•	•

Replacement Nose Pieces

Code	For Tool Models	Pack Qty.
1172	Duo 50, Duo 35, 18G/50, 16G/45, 400ELS & 181ELS	5
1206	Duo 50 (Extra Thick)	5



Duo Tools

Stapling as well as nailing. Versatile tools for the busy tradesman



Dedicated Nailers

Brilliant for a variety of second fix and making good tasks these are a must have, filling the space between hand and gas/air tools



Inclined Nailers

The angled, compact design make these tools perfect for nailing into tight spaces

Hand & Corded Tacker Kits



Z1-53 Metal Staple Tacker Kit 53/4-8mm

Professional Code: 0889 Includes: Staple remover, 200pcs 53 staples

Magazine Capacity: 125 Staples, 0.4kgs. Includes: 53 Staples 4-8mm, Retail Clam, Trade = 6 Units, Transit = 36 Units.

Z3-140L Heavy-Duty Tacker Kit 140/6-14mm 180/15mm 180/15mm headless

Semi-Professional Code: 0878 Includes: Staple remover, 200pcs 140 staples

Magazine Capacity: 90 Nails, 83 Staples, 0.25kgs. Includes: 140 Staples 6-14mm, 180 Nails 15mm, 180/15mm Headless Pin, Retail Clam, Trade = 6 Units, Transit = 12 Units.



Z3 4-in-1 Staple/Nail Tacker Kit 53/8-14mm 180/15mm 180/15mm headless CT60/12-14mm

Semi-Professional Code: 1053 Includes: Staple remover, 4000pcs 53 staples, 180 nails, 180 headless pins & CT60 cable staples

Magazine Capacity: 85 Nails, 150 Staples, 85 Cable Staples, 0.4kgs. Includes: 53 Staples 8-14mm, 180 Nails 15mm, CT-60 Staples 12-14mm, 180/15mm Headless Pin, Retail Clam, Trade = 1 Unit, Transit = 10 Units.

Many more consumables included. (Cable staples supplied in kit may not be white).

Hobby 53EL Tacker Kit 53/6-14mm 180/15mm

DIY/Semi-Pro Code: 1038 Includes: Staple remover, 4000pcs 53 staples & 180 nails

Magazine Capacity: 90 Nails, 125 Staples, 0.75kgs. Includes: 53 Staples 6-14mm, 180 Nails 15mm, Retail Box, Trade = 1 Unit, Transit = 10 Units.



Many more consumables included than pictured.

Nailing up to 40mm

Ranger 18G Brad Nailer

Offering greater precision than the well known Ranger duo tool, it is also better suited to joinery applications where it is important that the driver blade and nose safety device do not mark the wood surface. As the entry tool in the Ranger series the 18G is also the most competitively priced and offers extraordinary value.

180/15-40mm

Master Nailer Ranger 40 18G Nailer Tradesmans Pack

Professional	Code: 0966	Includes:	2 x 1.7 batteries, 1 x 1hr charger, 2000 35mm nails, goggles
Magazine Capacity 105 Nails	3.7kgs (inc battery)	180 Nails 15-40mm	Trade = 1 Unit Transit = 2 Units

New cordless models coming soon

Ranger 16G Finish Nailer

Delivering the heavier gauge 16G finish nail which is less discreet but provides a more substantial fixing and is popular for many joinery applications. The tool is also, of course, ideal for the multi tasking builder who requires versatility on site for any number of second fix applications.

Master Nailer Ranger 40 16G Finish Nailer Tradesmans Pack

Professional	Code: 0969	Includes:	2 x 1.7 batteries, 1 x 1hr charger, 2000 35mm nails, goggles
Magazine Capacity 75 Nails	3.7kgs (inc battery)	16G Nails 20-40mm	Trade = 1 Unit Transit = 2 Units

New cordless models coming soon

Features


Dual nail windows allow the user to quickly understand both the nail length loaded and the number of nails remaining in the tool. Removable/replaceable soft rubber nose to prevent marking.



Staples up to 40mm & Nails up to 50mm

Versatility

No gas, air hoses or mains cables to hold you back. Ranger gives you power, fastening flexibility and total independence around site. Delivers fast turnaround, less downtime and a quality job every time.



Replacement Rubber Nose Pieces

Code	Tool Description	Pack Qty.
0848	Rubber Nose Ranger 40 Duo	1
0970	Rubber Nose Ranger 40 18G & 16G	1



Battery 18v (NiCd) Specifications

Code	Capacity/shots per charge	Weight (kg)
0759	1.7Ah/1,700 shots	0.9kg
0760	1.4Ah/1,400 shots	0.8kg

Charger Specifications

Code	Mains voltage /input VAC	Approx. charging time (mins)	Weight (kg)	Fitted plug
0761	240v	60	0.7kg	UK

Tool Features

Performance, Comfort & Safety	Ranger 18G	Ranger 16G
Single shot trigger	✓	✓
Quick release loading	✓	✓
Swivel quick release nose plate	✓	✓
Rubber nose protector	✓	✓
Nose safety device	✓	✓
Safety on/off switch	✓	✓
Adjustable power lever	✓	✓
Nail/staple capacity viewing window	✓	✓
Impact resistant industrial body	✓	✓
Spare rubber noses – 5pcs	✓	✓
Max. nailing/stapling speed per min	40	40

Technical Specifications

Code	Tool Description	Dimensions (H x W x D)	Weight (kg)	Magazine Capacity		Fastener Type/Length (mm)		Min. Firing from wall	Source Tagged
				With Battery	Nails	Staples	Nails		
0966	Ranger 40 18G Tradesman Pack	325 x 290 x 80	3.7	105	-	180/15-40	-	6mm	✓
0969	Ranger 40 16G Tradesman Pack	325 x 290 x 80	3.7	75	-	16G/20-40	-	6mm	✓




1hr Battery Charger. Designed for the professional with the latest fast charge features.



Standard (5hr) Battery Charger. With separate transformer unit.


Two Battery types available; • 1.7 Ah NiCd 18v Pack, Includes battery meter - designed for the demanding tradesman. • 1.4 Ah NiCd 18v Pack, A durable professional unit a little lighter than the 1.7Ah option.

Nails & staples for use in hand, corded and cordless tackers




140 staples

Code	Staple Length/Type	Box Qty.	For Use In:
0350	140 Selection Pack	4400	Z1-140, Z1-140L, Z3-140, Z3-140L, A11, 140EL
0340	140/6mm	5000	Z1-140, Z1-140L, Z3-140, Z3-140L, A11, 140EL
0341	140/8mm	5000	Z1-140, Z1-140L, Z3-140, Z3-140L, A11, 140EL
0342	140/10mm	5000	Z3-140, Z3-140L, A11, 140EL
0477	140/10mm stainless steel	5000	Z3-140, Z3-140L, A11, 140EL
0343	140/12mm	5000	Z3-140, Z3-140L, 140EL
0344	140/14mm	5000	Z3-140, Z3-140L, 140EL
0345	140/6mm	2000	Z1-140, Z1-140L, Z3-140, Z3-140L, A11, 140EL
0346	140/8mm	2000	Z1-140, Z1-140L, Z3-140, Z3-140L, A11, 140EL
0347	140/10mm	2000	Z3-140, Z3-140L, A11, 140EL
0348	140/12mm	2000	Z3-140, Z3-140L, 140EL
0349	140/14mm	2000	Z3-140, Z3-140L, 140EL




53 staples

Code	Staple Length/Type	Box Qty.	For Use In:
1095	53 Selection Pack	6000	Z1-53, Z1-53L, Z1-53T, Z3-53, Z3-53L, Hobby 53EL
0331	53/6mm	5000	Z1-53, Z1-53L, Z1-53T, Z3-53, Z3-53L, Hobby 53EL
0332	53/8mm	5000	Z1-53, Z1-53L, Z1-53T, Z3-53, Z3-53L, Z3-4 in 1, Hobby 53EL
0431	53/10mm	5000	Z3-53, Z3-53L, Z3-4 in 1, Hobby 53EL
0450	53/12mm	5000	Z3-53, Z3-53L, Z3-4 in 1, Hobby 53EL
0452	53/14mm	5000	Z3-53, Z3-53L, Z3-4 in 1, Hobby 53EL
0453	53/16mm	5000	Z3-53, Z3-53L, Z3-4 in 1, Hobby 53EL
0333	53/4mm	2000	Z1-53, Z1-53L, Z1-53T
0334	53/6mm	2000	Z1-53, Z1-53L, Z1-53T, Z3-53, Z3-53L, Hobby 53EL
0335	53/8mm	2000	Z1-53, Z1-53L, Z1-53T, Z3-53, Z3-53L, Z3-4 in 1, Hobby 53EL
0336	53/10mm	2000	Z3-53, Z3-53L, Z3-4 in 1, Hobby 53EL
0337	53/12mm	2000	Z3-53, Z3-53L, Z3-4 in 1, Hobby 53EL
0338	53/14mm	2000	Z3-53, Z3-53L, Z3-4 in 1, Hobby 53EL




CT-45 cable tacker staples

Code	Staple Length/Type	Box Qty.	For Use In:
0351	CT-45/8mm	5 x 1000	CT-45, Z3-CT45
0980	CT-45/8mm white	5 x 1000	CT-45, Z3-CT45
0352	CT-45/10mm	5 x 1000	CT-45, Z3-CT45
0353	CT-45/10mm white	5 x 1000	CT-45, Z3-CT45



CT-60 cable tacker staples

Code	Staple Length/Type	Box Qty.	For Use In:
0354	CT-60/10mm	5 x 1000	CT-60, Z3-CT60
1094	CT-60/10mm white	5 x 1000	CT-60, Z3-CT60
0355	CT-60/12mm	5 x 1000	CT-60, Z3-CT60, Z3-4 in 1
0356	CT-60/14mm	5 x 1000	CT-60, Z3-CT60, Z3-4 in 1
0357	CT-60/14mm white	5 x 1000	CT-60, Z3-CT60, Z3-4 in 1
1061	CT-60/14mm black	5 x 1000	CT-60, Z3-CT60, Z3-4 in 1




13 staples

Code	Staple Length/Type	Box Qty.	For Use In:
0232	13/4mm	5000	Z1-13, Z1-13L
0233	13/6mm	5000	Z1-13, Z1-13L, Z3-13, Z3-13L, Hobby 13EL
0234	13/8mm	5000	Z1-13, Z1-13L, Z3-13, Z3-13L, Hobby 13EL
0235	13/10mm	5000	Z3-13, Z3-13L, Hobby 13EL
0236	13/14mm	5000	Z3-13, Z3-13L, Hobby 13EL

Staples up to 40mm & Nails up to 50mm


Nails & staples for use in hand, corded and cordless tackers

91 staples




Code	Staple/Nail Length/Type	Box Qty.	For Use In:
0204	91 Selection Pack	2800	191EL/S, Duo 35, Duo 50, Ranger 2, Ranger 40 Duo
0283	91/15mm	1000	191EL/S, Duo 35, Ranger 2, Ranger 40 Duo
0287	91/18mm divergent	1000	191EL/S, Duo 35, Ranger 2, Ranger 40 Duo
1069	91/18mm divergent s/steel	1000	191EL/S, Duo 35, Ranger 2, Ranger 40 Duo
0284	91/20mm	1000	191EL/S, Duo 35, Duo 50, Ranger 2, Ranger 40 Duo
0288	91/22mm divergent	1000	191EL/S, Duo 35, Duo 50, Ranger 2, Ranger 40 Duo
1070	91/22mm divergent s/steel	1000	191EL/S, Duo 35, Duo 50, Ranger 2, Ranger 40 Duo
0285	91/25mm	1000	191EL/S, Duo 35, Duo 50, Ranger 2, Ranger 40 Duo
1071	91/25mm stainless steel	1000	191EL/S, Duo 35, Duo 50, Ranger 2, Ranger 40 Duo
0286	91/30mm	1000	191EL/S, Duo 35, Duo 50, Ranger 2, Ranger 40 Duo
0289	91/30mm divergent	1000	191EL/S, Duo 35, Duo 50, Ranger 2, Ranger 40 Duo
0746	91/35mm	1000	Duo 50, Ranger 2, Ranger 40 Duo
0768	91/40mm	1000	Duo 50, Ranger 2, Ranger 40 Duo
1174	91/45mm	1000	Duo 50

180 nails




0205	180 Selection Pack	4000	Z3 Series, 140EL, Compact Series, 181ELS, 191EL/S, Duo 35, Duo 50, Ranger 2, Ranger 40 Duo
0358	180/10mm	2000	191EL
0359	180/15mm	2000	Z3 Series, 140EL, Compact Series, 181ELS, 191EL/S, Duo 35, Duo 50, Ranger 2, Ranger 40 Duo
0360	180/20mm	1000	181EL/S, 191EL/S, Duo 35, Duo 50, 18G/50, Ranger 2, Ranger 40 Duo
0361	180/25mm	1000	181EL/S, 191EL/S, Duo 35, Duo 50, 18G/50, Ranger 2, Ranger 40 Duo
1066	180/25mm stainless steel	1000	181EL/S, 191EL/S, Duo 35, Duo 50, 18G/50, Ranger 2, Ranger 40 Duo
0362	180/30mm	1000	181EL/S, 191EL/S, Duo 35, Duo 50, 18G/50, Ranger 2, Ranger 40 Duo
1067	180/30mm stainless steel	1000	181EL/S, 191EL/S, Duo 35, Duo 50, 18G/50, Ranger 2, Ranger 40 Duo
0363	180/32mm	1000	181EL/S, 191EL/S, Duo 35, Duo 50, 18G/50, Ranger 2, Ranger 40 Duo
0364	180/35mm	1000	181EL/S, 191EL/S, Duo 35, Duo 50, 18G/50, Ranger 2, Ranger 40 Duo
1068	180/35mm stainless steel	1000	181EL/S, 191EL/S, Duo 35, Duo 50, 18G/50, Ranger 2, Ranger 40 Duo
0747	180/40mm	1000	191EL/S, Ranger 2, Duo 50, 18G/50, Ranger 40 Duo
1156	180/50mm	1000	191EL/S, Duo 50, 18G/50, Ranger 2

180 headless pin




0478	180/15mm	2000	Z3 Series
------	----------	------	-----------

71 staples



0367	71/6mm	20000	71EL
1014	71/6mm stainless steel	20000	71EL
0368	71/8mm	20000	71EL
1065	71/8mm black	20000	71EL
0369	71/10mm	20000	71EL
0373	71/10mm black	20000	71EL
0375	71/10mm stainless steel	20000	71EL
0370	71/12mm	20000	71EL
0290	71/12mm black	20000	71EL
0488	71/12mm beige	20000	71EL
0371	71/14mm	10000	71EL
0374	71/14mm black	10000	71EL
0372	71/16mm	10000	71EL

73 staples




0456	73/10mm	5000	All 31 Type Pliers
0457	73/12mm	5000	All 31 Type Pliers

Tacwise HD73 Plier, code: 1169, for 73/6-12mm. Now available




500 angled nails



Code	Staple/Nail Length/Type	Box Qty.	For Use In:
0971	500/15mm	1000	400EL, 400ELS
0823	500/20mm	5000	400EL, 400ELS, 500EL
0479	500/20mm	1000	400EL, 400ELS, 500EL
1131	500/20mm stainless steel	1000	400EL, 400ELS, 500EL
0824	500/25mm	5000	400EL, 400ELS, 500EL
0480	500/25mm	1000	400EL, 400ELS, 500EL
0825	500/30mm	5000	400EL, 400ELS, 500EL
0481	500/30mm	1000	400EL, 400ELS, 500EL
1132	500/30mm stainless steel	1000	400EL, 400ELS, 500EL
0826	500/35mm	5000	400EL, 400ELS, 500EL
0482	500/35mm	1000	400EL, 400ELS, 500EL
1133	500/35mm stainless steel	1000	400EL, 400ELS, 500EL
0827	500/40mm	5000	400EL, 400ELS, 500EL
0483	500/40mm	1000	400EL, 400ELS, 500EL
1134	500/40mm stainless steel	1000	400EL, 400ELS, 500EL
0828	500/45mm	5000	500EL
0484	500/45mm	1000	500EL
0829	500/50mm	5000	500EL
0485	500/50mm	1000	500EL
1135	500/50mm stainless steel	1000	500EL

16G finish nails



0665	16G/20mm	2500	Ranger 16G, 16G/45
0666	16G/25mm	2500	Ranger 16G, 16G/45
0293	16G/30mm	2500	Ranger 16G, 16G/45
0294	16G/32mm	2500	Ranger 16G, 16G/45
0295	16G/35mm	2500	Ranger 16G, 16G/45
0296	16G/38mm	2500	Ranger 16G, 16G/45
0319	16G/40mm	2500	16G/45
0297	16G/45mm	2500	16G/45

160 (16G) stainless steel finish nails

1096	160/32mm S/Steel	1000	DFN50V, FFN64LHH, GFN64V, FCT50LHH
1097	160/38mm S/Steel	1000	DFN50V, FFN64LHH, GFN64V, FCT50LHH
1098	160/50mm S/Steel	1000	DFN50V, FFN64LHH, GFN64V, FCT50LHH

Precision

Years and years of experience in this field have resulted in the precision manufacturing of all Tacwise staples and nails. Produced from premium quality raw materials our exacting specifications include tolerances of 0.1mm to ensure the most accurate and consistent stapling/nailing actions time after time. Our standard staples and nails suit all other major brands of stapling and nailing tools.

Colour coded

Colour Coding: useful and convenient for quickly selecting the correct fastenings for Tacwise and other popular tools.



Stapling up to 50mm & Nailing up to 130mm

Air Nailing & Stapling

We believe that design and manufacturing innovation is the key to success and we continue to refine our designs to bring you the very best tools within their class. Our aim is to develop new standards of performance utilising the most advanced aluminium, magnesium and titanium materials, to define products that do more than simply function – but that perform better and last longer.



Built for the professional

Tacwise is committed to creating the ultimate fastening product range from hand, corded, cordless, air and gas powered equipment, combined together to provide the widest quality tools and consumables programme in Europe.



Loaded with features

Each with their own powerful features Tacwise air tools are carefully designed for user safety, convenience and durability.




Many tools include a flip open quick release nail gate for clearance of a fastener in the unlikely event of a jam.



They have neat features like soft noses to avoid damaging soft timber as well as reload indicators.



Handy and easy to use controls for depth adjustment make precision tasks simple.



This small lever allows the user to quickly switch between single shot and contact trip (bump fire).



Quick release magazines of different styles mean ultra fast re-loading.

Stapling up to 16mm

General Purpose & Upholstery Tackers

Unrivalled quality and performance from our top selling upholstery and general purpose air staplers. From the fastest to the lightest, we have a programme that covers all applications.

Market Leader

Probably selling more staples into the upholstery and general stapling channels than any other manufacturer, Tacwise has continued to refine its programme after many years of industry experience.



Extra Long Nose 71 Staple Tacker (71/4-16mm)

Production Line Code: A7116LN BEST VALUE

60-100
 1.1kgs
 71 Staples 4-16mm
 Carry Case
 Trade = 1 Unit
 Transit = 6 Units

Magnesium bodied stapler with an extended 50mm nose to allow for stapling into awkward areas. Lightweight and compact with rear exhaust, this tool is a firm favourite in the re-upholstery trade.

Technical Specifications

Tool Data	Model A7116LN	A7116V	A7116P	A8016V	A8016LN	A14014V
Width (mm)	230	218	218	218	230	235
Depth (mm)	45	43	43	43	45	46
Height (mm)	220	150	152	150	220	159
Weight (kg)	1.1	0.9	0.8	0.9	1.3	0.9
Takes staple type	71	71	71	80	80	140
Fasteners length (mm)	4-16	4-16	4-16	4-16	4-16	4-14
Capacity	180	180	180	150	150	150
Max dBA sound/noise level (on surface impact)	77	77	77	77	77	77
PSI	60-100	60-100	60-100	60-100	60-100	60-100
Trigger	Single Shot	Single Shot	Single Shot	Single Shot	Single Shot	Single Shot

Tool Features

Performance, Comfort & Safety	Model A7116LN	A7116V	A7116P	A8016V	A8016LN	A14014V
1 Soft rubber safety grip	✓	✓	✓	✓	✓	✓
2 Single shot trigger	✓	✓		✓	✓	✓
3 Slender length nose	✓	✓	✓	✓	✓	✓
4 Neat rear exhaust	✓	✓	✓	✓	✓	
5 Double safety trigger		✓		✓		✓
6 High capacity magazine	✓	✓	✓	✓	✓	✓
7 High durability driver blade system	✓	✓	✓	✓	✓	✓
Bottom loading	✓	✓	✓	✓	✓	✓
Extra long nose	✓				✓	
Ultra quick release reloading system		✓	✓	✓		✓



Tool Features

A7116V & A8016V incorporate a double sided magazine quick release. The rear exhaust and baffle are a convenient feature on most models.



Hardened metal hammer cap



Staple viewing window

71 Upholstery Staple Tacker (71/4-16mm)

Production Line Code: A7116V BEST VALUE

60-100
 0.9kgs
 71 Staples 4-16mm
 Carry Case
 Trade = 1 Unit
 Transit = 10 Units

Fast, reliable and the first choice for many professional upholsterers. Incorporating every essential feature insisted upon by the most demanding of users. Quiet, reliable and extremely quick to load.

Stapling up to 16mm



Premium 71 Staple Tacker 71/4-16mm

Production Line Code: A7116P

- 60-100 PSI
- 0.8kgs
- 71 Staples 4-16mm
- Pack Style Commercial Box
- Trade = 1 Unit
- Transit = 10 Units

This model is fast and well balanced. Designed for the production line environment. Incorporating every essential feature insisted upon by the most demanding of users. Quiet, reliable and extremely quick to reload.

Now available as auto/long magazine version: A71AUTO



80 Upholstery Staple Tacker 80/4-16mm

Production Line Code: A8016V **BEST VALUE**

- 60-100 PSI
- 0.9kgs
- 80 Staples 4-16mm
- Pack Style Carry Case
- Trade = 1 Unit
- Transit = 10 Units

Fast, reliable and the ultimate first choice for many professional upholsterers. Ideal for production line use. The wide 80 series staple provides additional fastening strength for materials such as plastic sheeting. Especially popular with our European users.



Extra Long Nose 80 Staple Tacker 80/4-16mm

Production Line Code: A8016LN **BEST VALUE**

- 60-100 PSI
- 1.1kgs
- 80 Staples 4-16mm
- Pack Style Carry Case
- Trade = 1 Unit
- Transit = 6 Units

Magnesium bodied stapler with an extended 50mm nose to allow for stapling into awkward areas. Lightweight, compact and with rear exhaust, this tool is a firm favourite in the re-upholstery trade.



Pro Staple Remover

Production Line Code: 0206


- Pack Style Retail Clam
- Trade = 12 Units
- Transit = 48 Units

Removes many types of staples from panelling, insulation & lining, upholstery, carpet underlay and many more... The ergonomic grip provides comfort during extended periods of use.

71 staples

Code	Staple Length/Type	Box Qty.
1126	71/4mm stainless steel	20000
0365	71/4mm	20000
0366	71/5mm	20000
0367	71/6mm	20000
1014	71/6mm stainless steel	20000
0368	71/8mm	20000
1065	71/8mm black	20000
0369	71/10mm	20000
0373	71/10mm black	20000
0375	71/10mm stainless steel	20000
0370	71/12mm	20000
0290	71/12mm black	20000
0488	71/12mm beige	20000
0371	71/14mm	10000
0374	71/14mm black	10000
0372	71/16mm	10000



For Use In:
All Tacwise 71 Series and other industry standard 71 tools



80 staples

0380	80/4mm	10000
0381	80/6mm	10000
0382	80/8mm	10000
0383	80/10mm	10000
1075	80/10mm stainless steel	10000
0384	80/12mm	10000
0385	80/14mm	10000
1141	80/16mm	10000

All Tacwise 80 Series and other industry standard 80 tools



1400 staples

0378	1400/10mm	10000
0379	1400/12mm	10000

Haubold® Type Tackers
Haubold® Type Tackers

140 Staple Tacker 140/4-14mm

Professional Code: A14014V **BEST VALUE**



- 60-100 PSI
- 0.9kgs
- 140 Staples 4-14mm
- Pack Style Carry Case
- Trade = 1 Unit
- Transit = 6 Units

This professional tool handles the 140 (T-50 Type) staple, commonly used in hand and electric tackers. Ideal for hand tool users tackling volume stapling tasks with standard and stainless steel staples.

140 staples listed on page 42



Stapling up to 40mm

Narrow Crown Staplers

Our narrow crown programme offers outstanding performance and versatility. The C9725V is compact and fast. The D9040V is versatile, reliable and with many stand-out features puts it at the top of the class in cabinet making and many garden furniture applications.



NEW

91 Staple Remover (for use with narrow crown staples)

Professional Code: 1073 Featured on page 20

Pack Style Retail Clam Trade = 12 Units Transit = 48 Units

Removes 91 type and other narrow crown staples from timber. Incorporating a stepped lifting device this remover will handle staples with both short and long legs. With ergonomic grip.

25mm Narrow Crown Stapler

Production Line Code: C9725V BEST VALUE

60-100 1.2kgs 97 Staples 10-25mm Pack Style Carry Case Trade = 1 Unit Transit = 6 Units

Built to last, this performance stapler copes easily with high volume stapling. Narrow nose/quick release staple gate and safety. Top multi-directional exhaust and recessed magazine release.



Outstanding Quality and Performance

Sophisticated progressive tooling, intelligent electronics engineering and a commitment to precision and detail, create the greatest air tacker programme available worldwide. Our dedication to quality begins in the initial stages of design with every component machined to extraordinary precision for years of trouble-free use.



32mm Narrow Crown Stapler 90/12-32mm

Production Line Code: C9032V BEST VALUE

60-100 1.2kgs 90 Staples 12-32mm Pack Style Carry Case Trade = 1 Unit Transit = 6 Units

Magnesium bodied stapler offering tremendous versatility and speed of use. Top selling model with excellent performance. Narrow nose with protector/quick release staple gate and safety. Top multi-directional exhaust and recessed magazine release.




40mm Narrow Crown Stapler 90/15-40mm

Production Line Code: D9040V BEST VALUE


60-100 1.7kgs 90 Staples 15-40mm Pack Style Carry Case Trade = 1 Unit Transit = 5 Units

With contact trip (bump fire) & sequential firing adjustment this fast and versatile 90 series tool comes with soft nose protector/quick release staple gate and safety. Top multi-directional exhaust.



97 narrow crown staples

Code	Staple Length/Type	Box Qty.	For Use In:
0302	97/10mm	5000	C9725V, C9725VHH
0303	97/15mm	5000	C9725V, C9725VHH
0304	97/20mm	5000	C9725V, C9725VHH
0305	97/25mm	5000	C9725V, C9725VHH



90 narrow crown staples

0306	90/15mm	5000	C9032V, D9040V, C9030VHH, C9040LHH, DNS50PHH
0312	90/18mm divergent point	5000	C9032V, D9040V, C9030VHH, C9040LHH, DNS50PHH
0307	90/20mm	5000	C9032V, D9040V, C9030VHH, C9040LHH, DNS50PHH
0313	90/22mm divergent point	5000	C9032V, D9040V, C9030VHH, C9040LHH, DNS50PHH
0308	90/25mm	5000	C9032V, D9040V, C9030VHH, C9040LHH, DNS50PHH
0309	90/30mm	5000	C9032V, D9040V, C9030VHH, C9040LHH, DNS50PHH
1144	90/32mm	5000	C9032V, D9040V, C9030VHH, C9040LHH, DNS50PHH
0310	90/35mm	5000	D9040V, C9040LHH, DNS50PHH
0311	90/40mm	5000	D9040V, C9040LHH, DNS50PHH

Stapling up to 50mm



Fully Featured

D9040V comes with a wide foot ideal for speed stapling with applications such as plasterboarding and a quick release nose plate to clear jams.

Heavy Duty & Wide Crown Staplers

Outstanding power and speed from our range of heavy duty and wide crown staplers. Rugged tools which are highly reliable.

Tool Features

Performance, Comfort & Safety	Model C9725V	C9032V	D9040V
1 High durability driver blade system	✓	✓	✓
2 High capacity magazine	✓	✓	✓
3 Soft rubber safety grip	✓	✓	✓
4 Slender length nose	✓	✓	✓
5 360° adjustable exhaust port	✓	✓	✓
Open (viewable) magazine system	✓	✓	✓
Quick release nose plate to release jams	✓	✓	✓
Non marking nose		✓	✓
Depth control adjustment for precise countersinking		✓	✓
Side mounted quick release loading system		✓	✓

Technical Specifications

Tool Data	Model C9725V	C9032V	D9040V
Width (mm)	248	273	302
Depth (mm)	55	67	88
Height (mm)	192	231	253
Weight (kg)	1.2	1.2	1.7
Takes staple type	97	90	90
Fasteners length (mm)	10-25	12-32	15-40
Capacity	125	100	100
Max dBA sound/noise level (on surface impact)	86	88	88
PSI	60-100	60-100	60-100
Trigger	Single Shot	Contact Trip	Contact Trip & Sequential



50mm Heavy Duty Stapler

Production Line Code: G1450V **BEST VALUE**

70-120
 2kgs
 14 Staples 19-50mm
 Pack Style Carry Case
 Trade = 1 Unit Transit = 6 Units

Preferred throughout the bedding and furniture industry, this durable framing tool is a first choice. Loaded with features including firing variations, depth control and a quick release nose plate in the unlikely event of a staple jam.

Stapling up to 50mm



50mm Heavy Duty Stapler

Production Line Code: F1450M

- 70-120
- 2.4kgs
- 14 Staples 19-50mm
- Commercial Box
- Trade = 1 Unit
Transit = 2 Units

Lightweight, compact and powerful this 50mm tool delivers an impressive performance. Beautifully balanced and highly reliable. Well established in many "blue chip" furniture factories. Also available with a "wraparound" front nose safety at extra cost. Can be supplied without the quick release nose plate (as per image).



Heavy Duty Wide Crown Stapler

Production Line Code: G1738XHH


- 70-120
- 3.0kgs
- 17 Staples 16-38mm
- Carry Case
- Trade = 1 Unit
Transit = 2 Units

This quality wide crown workhorse is primarily used for attaching packaging materials to wooden pallets. Tough, reliable and incorporating several neat features such as a magazine stabilising bar.

New model: G1738V (not featured) coming January 2014



Quick release nose plate



Easy top loading



Single shot - contact trip



Depth control adjustment

Corrugated Fastener



Premium 15mm Corrugated Fastener

Production Line Code: FCF15XCB

- 65-115
- 2.6kgs
- Corrugated Fasteners 9-15mm
- Commercial Box
- Trade = 1 Unit
Transit = 5 Units

Powerful fastening tool, capable of countersinking 15mm fasteners. Easy bottom loading of any size with minor adjustment. Ideal for butt joints in cabinet and furniture frames and for door and window sash manufacturers.




Tool Features

Performance, Comfort & Safety	G1450V	F1450M	G1738XHH	FCF15XCB
1 High durability driver blade system	✓	✓	✓	✓
2 Easy top loading system	✓	✓	✓	
3 Non marking nose	✓	✓	✓	
4 Soft rubber safety grip	✓	✓	✓	✓
5 360° adjustable exhaust port	✓			
6 Double power cylinder system	✓	✓	✓	
7 Open (viewable) magazine system	✓	✓	✓	
8 Depth control adjustment for precise countersinking	✓			
Neat rear exhaust system		✓	✓	
Quick release nose plate to release jams	✓			
High capacity magazine	✓	✓	✓	

Technical Specifications

Tool Data	G1450V	F1450M	G1738XHH	FCF15XCB
Width (mm)	368	360	276	300
Depth (mm)	97	78	93	87
Height (mm)	290	272	271	270
Weight (kg)	2.0	1.9	3.0	2.6
Takes staples type	14	14	17	CF
Fasteners length (mm)	19-50	19-50	16-38	9-15
Capacity	150	150	140	80
Max dBA sound/noise level (on surface impact)	90	85	86	80
PSI	70-120	70-120	70-120	65-115
Trigger	Single Shot & Contact Trip	Contact Trip	Contact Trip	Contact Trip


Nailing/Pinning up to 64mm



Our precision wide crown staples are ideal for attaching packaging material to wood, as well as a wide variety of furniture framing applications.




The depth control adjustment avoids the need to manually gauge the staple depth by adding downward force when firing the tool.




14 heavy duty staples galv. coated

0179	14/19mm	15000	F1440L, G1450V, F1450M, F1440LHH, G1450MHH
0180	14/25mm	15000	F1440L, G1450V, F1450M, F1440LHH, G1450MHH
0181	14/28mm	15000	F1440L, G1450V, F1450M, F1440LHH, G1450MHH
0173	14/32mm	10000	F1440L, G1450V, F1450M, F1440LHH, G1450MHH
0174	14/35mm	10000	F1440L, G1450V, F1450M, F1440LHH, G1450MHH
0175	14/38mm	10000	F1440L, G1450V, F1450M, F1440LHH, G1450MHH
0176	14/45mm	10000	G1450V, F1450M, G1450MHH
0177	14/50mm	10000	G1450V, F1450M, G1450MHH




17 wide crown staples

0780	17/19mm	10000	G1738XHH
0386	17/25mm	10000	G1738XHH
0387	17/32mm	10000	G1738XHH



32 carton closing staples

0186	32/15mm	2000	Standard carton top and bottom sealers
0187	32/18mm	2000	Standard carton top and bottom sealers



Corrugated fasteners

0447	CF9 9mm	2000	FCF15XCB
0448	CF12 12mm	1750	FCF15XCB
0449	CF15 15mm	1500	FCF15XCB

Nailers & Pinners

A programme of 8 quality nailers and pinners; meeting all your requirements.



64mm Angled Finish Nailer

Production Line Code: GDA64V **BEST VALUE**

70-120 PSI

1.8kgs

15G 'D' Head Inclined Finish Nails 38-64mm

Pack Style Carry Case

Trade = 1 Unit Transit = 5 Units

Popular on-site as well as for workshop/joinery applications. Supplied with a non marking nose safety and fast reload system, this tool is light and compact. Capable of counter-sinking a 64mm nail.

Nailing/pinning up to 64mm



35mm Headless Pinner

Production Line Code: A6435

60-100 PSI 0.9kgs 23G 'A64' 12-35mm Pack Style Commercial box Trade = 1 Unit Transit = 10 Units

This quality, lightweight tool is perfect for fixing fine beading. Ultra slim nose for accurate pin placement. No adjustment is required to fire pins of different lengths. Rear exhaust, double trigger safety system and high durability driver.



32mm Brad Nailer 180/10-32mm 18G/10-32mm

Production Line Code: C1832V **BEST VALUE**

60-100 PSI 1.1kgs 180 (18G) Nails 10-32mm Pack Style Carry Case Trade = 1 Unit Transit = 6 Units

This hugely popular lightweight tool is accurate and reliable and offers tremendous value. Compact and versatile it can be bump fired with its contact trip valve. Fires up to 5 shots per second.



35mm Mini Brad Nailer

Professional Code: CMB35PHH

60-100 PSI 1.3kgs 21G 'Mini Tip' Mini Brads 15-35mm Pack Style Carry Case Trade = 1 Unit Transit = 5 Units

High durability nail driver system. Out-performs metal bodied versions which cost a great deal more. Firing up to 35mm mini brad nails, it has virtually no vibration/recoil. Nail reload indicator. Small nose for accurate fixing.



50mm Brad Nailer 180/20-50mm 18G/20-50mm

Semi Professional Code: DGN50V **BEST VALUE**

60-100 PSI 1.2kgs 180 (18G) Nails 20-50mm Pack Style Carry Case Trade = 1 Unit Transit = 6 Units

All professional fully featured tool including a depth adjuster. Comfortable fast and lightweight. Specified by trade professionals throughout Europe this model is already a Tacwise best seller.



50mm Finish Nailer 160/20-50mm 16G/20-50mm

Production Line Code: DFN50V **BEST VALUE**

70-120 PSI 1.7kgs 160 (16G) Nails 20-50mm Pack Style Carry Case Trade = 1 Unit Transit = 5 Units

Offering excellent value and widely accepted in the furniture manufacturing industry, this ergonomic model delivers peak performance. Fast and accurate, this finish nailer comes with a flush, quick release nose gate designed to avoid obstructing tool access in tight spaces. With essential user features it's reliable and demanded for volume nailing tasks.

64mm Finish Nailer 160/20-64mm 16G/20-64mm

Production Line Code: GFN64V **BEST VALUE**

70-120 PSI 1.8kgs 160 (16G) Nails 20-64mm Pack Style Carry Case Trade = 1 Unit Transit = 6 Units

Versatility at its best. Uses 20-64mm nails without requiring any magazine adjustment. Features a nailing depth control and a special side opening jam clearance system to keep "down time" to a minimum.

Available November 2013



Nailing/pinning up to 64mm

Nailers & Pinners

Proven nailers and pinners that are tough and reliable. Tacwise's lightweight polymer bodied nailers are the perfect choice for all your low volume nailing requirements. As our range of quality nailers and pinners are highly specified they require little or no adjustment and so for repeated nailing time after time insist on Tacwise.

Technical Specifications

Tool Data	Model	GDAG4V	A6435	C1832V	CMB35PHH	DGN50V	DFN50V	FFN64LHH
Width (mm)		331	240	228	250	273	302	299
Depth (mm)		100	44	67	49	67	88	74
Height (mm)		302	162	288	200	249	270	281
Weight (kg)		1.8	0.9	1.1	1.3	1.2	1.7	1.7
Takes nail type		15G	23G/.64	18G/180	21G	18G	16G	16G
Fasteners length (mm)		38-64	12-35	10-32	15-35	20-50	20-50	20-64
Capacity		100	170	100	150	100	100	100
Max dBA sound/noise level (on surface impact)		89	77	81	86	86	86	89
PSI		70-120	60-100	60-100	60-100	60-100	70-120	70-120
Trigger		Single Shot & Contact Trip	Safety Trigger	Contact Trip	Sequential	Contact Trip	Contact Trip	Sequential

Tool Features

Performance, Comfort & Safety								
1	High durability driver blade system	✓	✓	✓	✓	✓	✓	✓
	Ultra quick release reloading system		✓	✓	✓	✓	✓	✓
2	Neat rear exhaust system		✓					
	Soft rubber safety grip	✓	✓	✓	✓	✓	✓	✓
3	Slender length nose		✓	✓		✓		✓
	360° adjustable exhaust port	✓		✓	✓	✓	✓	✓
	Nail refill window		✓		✓	✓		
	Automatic pin length adjuster		✓					
4	Open (viewable) magazine system	✓						✓
5	Quick release nose plate to release jams	✓		✓	✓	✓	✓	✓
	Non marking nose	✓	✓	✓	✓	✓		✓
	Depth control adjustment for precise countersinking	✓		✓	✓	✓		
	High capacity magazine		✓	✓		✓	✓	✓
	Side mounted quick release loading system							✓



Tacwise air tackers – quieter by design

With noise pollution in the workplace at the forefront of our minds, Tacwise tools are carefully created to perform at lower, more acceptable decibel sound/noise levels (dBA) than others in their class.


Versatility and diversity

A comprehensive programme of accurate and reliable fine nailing tools and fastenings designed to satisfy the demands of a huge range of woodworking applications.





180 nails

Code	Length/Type	Box Qty.	For Use In:
0205	180 selection pack	4000	C1832V, DGN50V, DGN50LHH, DGN50VHH
0358	180/10mm	2000	C1832V
0359	180/15mm	2000	C1832V
0360	180/20mm	1000	C1832V, DGN50V, DGN50LHH, DGN50VHH
0361	180/25mm	1000	C1832V, DGN50V, DGN50LHH, DGN50VHH
NEW 1066	180/25mm S/Steel	1000	C1832V, DGN50V, DGN50LHH, DGN50VHH
NEW 0362	180/30mm	1000	C1832V, DGN50V, DGN50LHH, DGN50VHH
NEW 1067	180/30mm S/Steel	1000	C1832V, DGN50V, DGN50LHH, DGN50VHH
0363	180/32mm	1000	C1832V, DGN50V, DGN50LHH, DGN50VHH
0364	180/35mm	1000	DGN50V, DGN50LHH, DGN50VHH
NEW 1068	180/35mm S/Steel	1000	DGN50V, DGN50LHH, DGN50VHH
0747	180/40mm	1000	DGN50V, DGN50LHH, DGN50VHH
1156	180/50mm	1000	DGN50V, DGN50LHH, DGN50VHH



18G brad nails

Code	Length/Type	Box Qty.	For Use In:
0392	18G/10mm	5000	C1832V, DGN50V
0393	18G/13mm	5000	C1832V
0394	18G/15mm	5000	C1832V
0395	18G/20mm	5000	C1832V, DGN50V
0396	18G/25mm	5000	C1832V, DGN50V
0397	18G/30mm	5000	C1832V, DGN50V
0398	18G/32mm	5000	C1832V, DGN50V
0399	18G/35mm	5000	DGN50V
0400	18G/40mm	5000	DGN50V
0401	18G/50mm	5000	DGN50V




18G angled brad nails (500 Series)

Code	Nail Length/Type	Box Qty.	For Use In:
0823	500/20mm	5000	400EL, 400ELS, 500EL, BeA™ 350-226C
NEW 1131	500/20mm S/Steel	1000	400EL, 400ELS, 500EL, BeA™ 350-226C
0824	500/25mm	5000	400EL, 400ELS, 500EL, BeA™ 350-226C
0825	500/30mm	5000	400EL, 400ELS, 500EL, BeA™ 350-226C
NEW 1132	500/30mm S/Steel	1000	400EL, 400ELS, 500EL, BeA™ 350-226C
0826	500/35mm	5000	400EL, 400ELS, 500EL, BeA™ 350-226C
NEW 1133	500/35mm S/Steel	1000	400EL, 400ELS, 500EL, BeA™ 350-226C
0827	500/40mm	5000	400EL, 400ELS, 500EL, BeA™ 350-226C
NEW 1134	500/40mm S/Steel	1000	400EL, 400ELS, 500EL, BeA™ 350-226C
0828	500/45mm	5000	400EL, 400ELS, 500EL, BeA™ 350-226C
0829	500/50mm	5000	400EL, 400ELS, 500EL, BeA™ 350-226C
NEW 1135	500/50mm S/Steel	1000	400EL, 400ELS, 500EL, BeA™ 350-226C

160 (16G) stainless steel finish nails

Code	Nail Length/Type	Box Qty.	For Use In:
NEW 1096	160/32mm S/Steel	1000	DFN50V, FFN64LHH, GFN64V, FCT50LHH
NEW 1097	160/38mm S/Steel	1000	DFN50V, FFN64LHH, GFN64V, FCT50LHH
NEW 1098	160/50mm S/Steel	1000	DFN50V, FFN64LHH, GFN64V, FCT50LHH



16G finish nails

Code	Nail Length/Type	Box Qty.	For Use In:
0665	16G/20mm	2500	DFN50V, FFN64LHH, GFN64V, FCT50LHH
0666	16G/25mm	2500	DFN50V, FFN64LHH, GFN64V, FCT50LHH
0293	16G/30mm	2500	DFN50V, FFN64LHH, GFN64V, FCT50LHH
0294	16G/32mm	2500	DFN50V, FFN64LHH, GFN64V, FCT50LHH
0295	16G/35mm	2500	DFN50V, FFN64LHH, GFN64V, FCT50LHH
0296	16G/38mm	2500	DFN50V, FFN64LHH, GFN64V, FCT50LHH
0319	16G/40mm	2500	DFN50V, FFN64LHH, GFN64V, FCT50LHH
0297	16G/45mm	2500	DFN50V, FFN64LHH, GFN64V, FCT50LHH
0298	16G/50mm	2500	DFN50V, FFN64LHH, GFN64V, FCT50LHH
0299	16G/55mm	2500	FFN64LHH, GFN64V
0300	16G/60mm	2500	FFN64LHH, GFN64V
0301	16G/64mm	2500	FFN64LHH, GFN64V




16G angled finish nails

Code	Nail Length/Type	Box Qty.	For Use In:
0769	16G Angled/32mm	2500	DeWalt™ DC618, Paslode® IM250A & IM65A F16 Nailers
0770	16G Angled/38mm	2500	DeWalt™ DC618, Paslode® IM250A & IM65A F16 Nailers
0771	16G Angled/45mm	2500	DeWalt™ DC618, Paslode® IM250A & IM65A F16 Nailers
0772	16G Angled/50mm	2500	DeWalt™ DC618, Paslode® IM250A & IM65A F16 Nailers
0773	16G Angled/63mm	2500	DeWalt™ DC618, Paslode® IM250A & IM65A F16 Nailers

15G 'D' head inclined finish nails

Code	Nail Length/Type	Box Qty.	For Use In:
0402	DA13/25mm	4000	FBA50VCB
0403	DA15/32mm	4000	FBA50VCB, GBA64LHH
0404	DA17/38mm	4000	FBA50VCB, GDA64V, GBA64LHH
0405	DA19/44mm	4000	FBA50VCB, GDA64V, GBA64LHH
0406	DA21/50mm	4000	FBA50VCB, GDA64V, GBA64LHH
0407	DA25/64mm	4000	GDA64V, GBA64LHH



Nailing up to 130mm

10 high performance coil nailers

Unrivalled

Most Tacwise coil nailers fire 4+ nails per second and can be used single handedly. This is because lightweight magnesium is used to manufacture many of the tool bodies and triple hardened internal parts facilitate rapid firing and excellent durability. Ergonomic design provides great balance and comfort and neat touches, such as external top cap crash bars help to ensure less down time than other nailers.

Versatility

Popular for traditional nailing applications such as building sheds, fence panels and pallets. Coil nailers are also a brilliant time saving solution for any number of nailing applications where speed and efficiency are desirable. High capacity magazines contain a large volume of nails and offer continuous effective operation.

Increasingly demanded within the construction industry, the ability to fire up to 400 nails without re-loading increases productivity and makes coil nailing the preferred option when compared to strip nailers which only load around 100 nails at a time.

All Tacwise coil nailers up to 90mm are light enough for single handed operation.



Coil Nailers

FCN57V featured here offers unrivalled performance and the lightweight magnesium alloy body provides exceptional power and complete ease of use. It is especially suited for shed and fence manufacture as its 350 nail high capacity magazine means less reloading is required.

Serious about coil nailing

This category forms a particularly important focus for Tacwise and our full tool line covers most major and niche applications with an extensive and heavily stocked fastening programme to cater for pressures of demand from our dealers and their largest users.

57mm Mini Coil Nailer

Production Line Code: FCN57V **BEST VALUE**

- 70-120
- 2.3kgs
- 2.1-2.5 Flat Coil Nails 25-57mm
- Pack Style Carry Case
- Trade = 1 Unit
Transit = 5 Units

Highly versatile heavy duty nailer taking 25-57mm round head, wire collated coil nails in a transparent nail drum. Perfect for packaging applications including pallet reconditioning and top-decking pallets in particular. Also very popular for the construction of garden buildings.

Nailing up to 130mm



50mm Mini Coil Nailer

Production Line Code: DCN50LHH

- 70-120
- 1.5kgs
- 2.1 Conical Coil Nails 22-50mm
- Carry Case
- Trade = 1 Unit
Transit = 2 Units

An exceptional tool for 2.1 diameter round head nails. Weighing a mere 1.5kgs it will nevertheless countersink a 45mm ring shank nail. Compact design with a single or bump fire trigger. Very popular in the fencing and shed industry.



70mm Coil Nailer

Production Line Code: GCN70V **BEST VALUE**

- 70-120
- 3.7kgs
- 2.3-2.9 Flat Coil Nails 40-70mm
- Carry Case
- Trade = 1 Unit
Transit = 2 Units

This tough production line tool has a highly developed construction and specification, firing up to 300 nails without reloading. Contact trip trigger. Tool ideal for the pallet and packaging industries.



50mm Coil Nailer

Production Line Code: FCN50LHH

- 60-120
- 2.0kgs
- 2.1 Flat & Conical Coil Nails 27-50mm
- Commercial Box
- Trade = 1 Unit
Transit = 2 Units

Weighing only 2kg, this tool has superhuman speed and will take 27-50mm flat and conical head nails making it ideal for fencing and shed manufacture. Single or bump fire trigger.



83mm Coil Nailer

Production Line Code: HCN83P **BEST VALUE**

- 70-120
- 3.9kgs
- 2.5-3.3 Flat Coil Nails 38-83mm
- Carry Case
- Trade = 1 Unit
Transit = 2 Units

Robust traditional tool for reliable and tough continuous nailing. Especially hardened working parts ensure a long and productive life. Developed for the rugged pallet and case industries in particular.



57mm Coil Nailer

Production Line Code: GCN57P **BEST VALUE**

- 60-120
- 2.7kgs
- 2.1-2.3 Flat Coil Nails 25-57mm
- Carry Case
- Trade = 1 Unit
Transit = 5 Units

An extremely heavy duty workhorse, this tough production line tool has a highly developed construction and specification, firing up to 400 nails without reloading. Contact trip trigger. Suitable for exhibition, pallet, crate and packaging industries.



90mm Coil Nailer

Production Line Code: JCN90XHH

- 70-120
- 3.6kgs
- 2.5-3.1 Flat Coil Nails 45-90mm
- Commercial Box
- Trade = 1 Unit
Transit = 2 Units

A more specialist tool firing up to 90mm. Super-lightweight magnesium alloy body for the ultimate power to weight ratio. Nose safety designed to avoid slippage. Tough construction to withstand the rigours of continuous on-site use.



65mm Coil Nailer

Production Line Code: FCN65V

- 70-120
- 2kgs
- 2.1-2.9 Flat & Conical Coil Nails 32-65mm
- Commercial Box
- Trade = 1 Unit
Transit = 2 Units

Ultra lightweight, this professional production line tool has a highly developed construction and specification, firing up to 350 nails without reloading. Extremely versatile as it accepts a wide range of nail diameters.



130mm Coil Nailer

Production Line Code: LCN130V

- 70-100
- 6.5kgs
- 3.1-3.8 Flat Coil Nails 75-130mm
- Commercial Box
- Trade = 1 Unit
Transit = 1 Unit

Supplied with side handle (shown above) for two-handed operation and suspension point. This powerful nailer has a single shot trigger and good power to weight ratio. Mainly designed for large packing case, crate and cable drum manufacture. Also widely used for heavy duty pallets, framing and steel skids.



• Side handle for easy grip of this sturdy tool

Nailing up to 130mm

Technical Specifications

Tool Data	Model	DCN50LHH	FCN50LHH	GCN57P	FCN57V	HCN65P	FCN65V	GCN70V	HCN83P	JCN90XHH	LCN130V
Width (mm)		260	305	380	305	305	268	330	305	385	370
Depth (mm)		108	128	130	130	130	128	132	132	143	165
Height (mm)		284	294	290	302	312	306	308	340	370	479
Weight (kg)		1.5	2.0	2.7	2.3	2.5	2.0	3.7	3.9	3.6	6.5
Takes nail type		2.1	2.1	2.1-2.3	2.1-2.5	2.3-2.9	2.1-2.9	2.3-2.9	2.5-3.3	2.5-3.1	3.1-3.8
Fasteners length (mm)		22-50	27-50	25-57	25-57	32-65	32-65	40-70	38-83	45-90	75-130
Capacity		400	400	300-400	300-350	250-350	250-350	250-350	250-300	300	225-300
Max dBA sound/noise level (on surface impact)		83	96	96	96	96	95	83	95	88	98
PSI		70-120	60-120	60-120	70-120	70-120	70-120	70-120	70-120	70-120	70-120
Trigger		Single Shot / Contact Trip	Single Shot / Contact Trip	Contact Trip	Single Shot / Contact Trip	Single Shot / Contact Trip	Single Shot / Contact Trip	Single Shot / Contact Trip	Contact Trip	Contact Trip	Single Shot

Tool Features

Performance, Comfort & Safety

1	High durability driver blade system	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
2	Soft rubber safety grip	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
3	360° adjustable exhaust port	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
4	High capacity nail drum	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
5	Safety yoke to avoid slippage	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
	Non marking foot	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
6	Countersinking adjustment	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
	Slender length nose	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
	Open (viewable) magazine system	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓



Hardened steel protection bars and ears



Powerful but simple nail drive train



Adjustable trigger for single/continuous (bump) fire



Cutting edge air flow technology

65mm Coil Nailer

Production Line Code: HCN65P **BEST VALUE**

- 70-120 PSI
- 2.5kgs
- 2.3-2.9 Flat Coil Nails 32-65mm
- Pack Style
- Carry Case
- Transit = 4 Units

Outstanding power to weight ratio. Sinking a 65mm ring nail, this tough production line tool accepts both reduced head and standard (7mm diameter) head nails. Fires up to 350 nails without reloading.



Complete Versatility

The HCN65P featured here is the benchmark tool for a wide number of timber frame house applications and is particularly versatile as this single tool, without the need for any adjustment, drives both the reduced head or standard 7mm head 50mm nails used for sheathing. Whilst compact, it incorporates outstanding power and speed driving up to 65mm. A premium quality, highly recommended tool.

Nailing up to 130mm



Put to the test


We admit – we’re tough on our products. We have to be when they’re used in busy industrial environments. They need to be able to withstand the toughest treatment, which is why we painstakingly stress test every new item and why we then hand test every single tool.

Outstanding Quality and Performance


Sophisticated progressive tooling, intelligent electronic engineering and a commitment to precision and detail, create the greatest air tacker programme available worldwide. Our dedication to quality begins in the initial stages of design with every component machined to extra ordinary precision for years of trouble-free use.

High Performance Coil Nails

Increasingly demanded within the construction industry, the ability to fire up to 400 nails without re-loading increases productivity.



Coil nails wire collated flat top			
0993	2.1 30mm bright, ring (replaces code 0812)	14400	FCN50LHH, GCN57P, FCN57V
0994	2.1 35mm bright, ring (replaces code 0813)	14400	FCN50LHH, GCN57P, FCN57V, FCN65V
0995	2.1 40mm bright, ring (replaces code 0814)	14400	FCN50LHH, GCN57P, FCN57V, FCN65V
0996	2.1 40mm galv, ring (replaces code 0275)	14400	FCN50LHH, GCN57P, FCN57V, FCN65V
0997	2.1 45mm bright, ring (replaces code 0815)	14400	FCN50LHH, GCN57P, FCN57V, FCN65V
0998	2.1 45mm galv, ring (replaces code 0276)	14400	FCN50LHH, GCN57P, FCN57V, FCN65V
0999	2.1 50mm bright, ring (replaces code 0816)	14400	FCN50LHH, GCN57P, FCN57V, FCN65V
0495	2.1 50mm galv., ring	14400	FCN50LHH, GCN57P, FCN57V, FCN65V
0279	2.3 50mm bright, ring	9000	GCN57P, FCN57V, HCN65P, GCN70V
0421	2.5 45mm bright, ring	9000	FCN57V, HCN65P, FCN65V, GCN70V, HCN83P, JCN90XHH
0422	2.5 50mm bright, ring	9000	FCN57V, HCN65P, FCN65V, GCN70V, HCN83P, JCN90XHH
0423	2.5 50mm galv., ring	9000	FCN57V, HCN65P, FCN65V, GCN70V, HCN83P, JCN90XHH
0424	2.5 55mm bright, ring	9000	FCN57V, HCN65P, FCN65V, GCN70V, HCN83P, JCN90XHH
0425	2.5 60mm bright, ring	9000	HCN65P, FCN65V, GCN70V, HCN83P, JCN90XHH
0427	2.5 64mm bright, ring	9000	HCN65P, FCN65V, GCN70V, HCN83P, JCN90XHH
1074	2.5 64mm bright, smooth	9000	HCN65P, FCN65V, GCN70V, HCN83P, JCN90XHH
0428	2.5 64mm galv., ring	9000	HCN65P, FCN65V, GCN70V, HCN83P, JCN90XHH
0489	2.5 70mm bright, ring	9000	GCN70V, HCN83P, JCN90XHH
1093	2.5 70mm bright, smooth	9000	HCN65P, FCN65V, GCN70V, HCN83P, JCN90XHH
0429	2.7 64mm bright, ring	6000	HCN65P, GCN70V, HCN83P, JCN90XHH
0430	2.7 75mm bright, ring	6000	HCN83P, JCN90XHH
0820	2.7 75mm CE/12 micron galv., ring	6000	HCN83P, JCN90XHH
0172	2.8 50mm galv., smooth	4000	HCN65P, GCN70V, HCN83P, JCN90XHH
1140	2.8 50mm CE/12 micron galv., smooth	4000	HCN65P, GCN70V, HCN83P, JCN90XHH
0777	2.8 50mm CE/12 micron galv., ring	4000	HCN65P, GCN70V, HCN83P, JCN90XHH
0964	2.8 64mm CE/12 micron galv., ring	4000	HCN65P, GCN70V, HCN83P, JCN90XHH
0965	2.8 83mm bright, ring	4000	HCN83P, JCN90XHH
0433	3.1 90mm CE/12 micron galv., ring	4000	JCN90XHH, LCN130V
1021	3.1 90mm bright., ring	4000	JCN90XHH, LCN130V
1036	3.3 65mm CE/12 micron galv., ring	4000	HCN83P, JCN90XHH, LCN130V
1035	3.3 75mm CE/12 micron galv., ring	4000	HCN83P, JCN90XHH, LCN130V
1154	3.3 98mm bright ring	4000	LCN130V
1155	3.8 130mm bright screw	1500	LCN130V



Coil nails wire collated conical top			
1128	2.1 22mm galv., ring	14400	DCN50LHH
1000	2.1 27mm galv., ring blunt (replaces code 0408)	14400	DCN50LHH, FCN50LHH
1001	2.1 32mm bright, ring (replaces code 0409)	14400	DCN50LHH, FCN50LHH, FCN65V
1002	2.1 32mm galv., ring (replaces code 0410)	14400	DCN50LHH, FCN50LHH, FCN65V
1003	2.1 32mm galv., ring blunt (replaces code 0411)	14400	DCN50LHH, FCN50LHH, FCN65V
1004	2.1 38mm bright, ring (replaces code 0412)	14400	DCN50LHH, FCN50LHH, FCN65V
1005	2.1 38mm galv., ring (replaces code 0413)	14400	DCN50LHH, FCN50LHH, FCN65V
1006	2.1 38mm galv., ring blunt (replaces code 0414)	14400	DCN50LHH, FCN50LHH, FCN65V
1007	2.1 45mm bright, ring (replaces code 0415)	14400	DCN50LHH, FCN50LHH, FCN65V
1008	2.1 45mm bright, smooth (replaces code 0416)	14400	DCN50LHH, FCN50LHH, FCN65V
1009	2.1 45mm galv., ring (replaces code 0417)	14400	DCN50LHH, FCN50LHH, FCN65V
1010	2.1 45mm galv., ring blunt (replaces code 0418)	14400	DCN50LHH, FCN50LHH, FCN65V
1011	2.1 50mm bright, ring (replaces code 0419)	14400	DCN50LHH, FCN50LHH, FCN65V
1012	2.1 50mm galv., ring (replaces code 0420)	14400	DCN50LHH, FCN50LHH, FCN65V

12 Micron galvanised CE nails. Now available



Point Varieties	Shank Varieties	Nail Treatments
Diamond Point Blunt Point	Smooth Shank - smooth plain surface Ring Shank - appears twisted	Bright: Untreated (no coating) Galvanised (Galv.): Rust protected by electroplated zinc coating approx. 6-8 microns Extra Galvanised (Extra Galv.): Rust protected by electroplated zinc coating 12+ microns






Nailing up to 100mm

Strip Nailers

The ultimate range of angled strip nailers, offering sheer power, outstanding performance and reliability. An essential for all those tough jobs.

90mm 34° Angled Strip Nailer

Professional Code: KDH90V **BEST VALUE**

-  70-120
-  3.8kgs
-  2.8-3.7mm diameter
34° Paper Collated 'D'
Head Strip Nail/50-90mm
-  Carry Case
-  Trade = 1 Unit
Transit = 2 Units

Extremely powerful and reliable, this 34° 'D' head strip nailer is very popular with timber frame house builders and is perfect for a wide variety of first fix roofing applications.



90mm Angled Strip Nailer

Professional Code: JSN90MH

-  70-120
-  3.9kgs
-  2.9-3.3mm diameter
22° Plastic Collated
Strip Nails/50-90mm
-  Carry Case
-  Trade = 1 Unit
Transit = 2 Units

An extremely powerful first fix strip nailer that won't let you down. The lightweight angled magazine provides easy access in all frame construction applications day in, day out. Probably the most reliable tool on the market.



This robust tool is complimented with a range of great user features including a bumper/belt hanger and floating nose system.

Metal Connector Nailer

Professional Code: FRH38TH

-  70-120
-  2.1kgs
-  3.75mm diameter
34° Paper Collated
Nails/25-38mm
-  Commercial box
-  Trade = 1 Unit
Transit = 2 Units

A compact and lightweight tool designed for quickly locating the nail point into the holes of joist hangers and any number of other metal braces and timber construction metal links.

Nailing up to 90mm

For your heavy duty nailing tasks

These heavy duty strip nailers handle the popular and standard 34° 'D' head paper collated nails up to 100mm. Tough and reliable yet relatively lightweight by way of their magnesium alloy bodies they are perfect for a wide range of timber frame and construction tasks. Plus many applications where these longer nails are required including heavy weight decking and fencing, cable drums and steel skids, pallet and case construction.



Valuable and robust tool features

Single shot/contact trip trigger in one

Ultra fast loading

Depth control adjustment



Technical Specifications

Tool Data	Model	KDH90V	JSN90MHH	FRH38THH
Width (mm)		470	526	326
Depth (mm)		150	137	114
Height (mm)		364	364	260
Weight (kg)		3.8	3.9	2.1
Takes nail type		2.8-3.7	2.9-3.3	3.75
Fasteners length (mm)		50-90	50-90	25-38
Capacity		75-95	80	55
Max dBA sound/noise level (on surface impact)		86	91	84
PSI		70-120	70-120	70-120
Trigger		Single Shot / Contact Trip	Contact Trip	Single Shot

Tool Features

Performance, Comfort & Safety	Model	KDH90V	JSN90MHH	FRH38THH
High durability driver blade system		✓	✓	✓
Soft rubber safety grip		✓	✓	✓
Slender length nose		✓	✓	
360° adjustable exhaust port		✓	✓	✓
Open (viewable) magazine system		✓	✓	
Non marking nose		✓	✓	
Depth control adjustment for precise countersinking		✓	✓	
High capacity magazine		✓	✓	✓
Floating nose system				✓
Belt hanger				✓

Ranger Gas Strip Nailer

The new Tacwise Gas Ranger is a portable masterpiece. Created using years of experience producing gas tools this Ranger uses industry standard paper collated strip nails and fires effortlessly from 50 to 90mm. Beautifully balanced it can fire between 2-3 nails per second, and features a convenient digital counter to indicate ongoing servicing requirements. Tacwise is the brand name you can rely on.



Ranger Gas Strip Nailer

Professional	Code: 1147
Professional	Code: 1162 EURO
Magazine Capacity	62 Nails
Weight	3.7kgs
Nail Size	2.8-3.3 diameter 34° Paper Collated 'D' Head Strip Nail/50-90mm
Pack Style	Carry Case
Trade	Trade = 1 Unit
Transit	Transit = 1 Unit

Features an anti dry-fire mechanism to prevent nail usage when just 3-5 nails remain in the tool magazine. Highly accurate, the Gas Ranger comes with two NiMH batteries and recharging unit, and is capable of driving up to 1,000 nails per hour and up to 5,000 per day. The in-built flashing light system provides real-time information on tool performance. Has fixed term service intervals dependant upon nail usage.

Flexibility to work anywhere

Use the Gas Ranger anywhere for up to 4,000 nails on one full battery charge. Firing approximately 1,100 nails using a Tacwise premium 80ml fuel cell, the tool is ideal for timber frame erection, roof battening, stud work, cladding, joists and many other on-site and in house applications. Ranger gives you power, fastening flexibility and total independence around site. Delivers fast turnaround, less downtime and a quality job every time.



Nailing up to 38mm

Ranger Gas Strip Nailer



Quick and easy to reload



Cutting edge air flow technology



Great value replaceable service parts



Sturdy belt hanger



Replaceable non-marking nose

Specifications



Tool Features

Performance, Comfort & Safety

High durability driver blade system	✓
Soft rubber safety grip	✓
Replaceable ABS nose cap	✓
Open (viewable) magazine system	✓
Digital nail counter	✓
Belt hanger	✓
High capacity magazine	✓

Gas Ranger tool

Lamp indicators

Green	Charging		✓
Green + Red	Fully charged		✓
Green	Tool running properly	✓	
Green + Red (Flashing alternately)	Tool getting hot	✓	
Red (Flashing)	Tool over heating, stop/allow to cool	✓	
Red	Battery low	✓	

Gas Ranger tool

Charger

Replacement Parts

Code	Tool Description	Pack Qty.
1152	Replacement nose	5

Replacement Charger/Specifications

Code	Charger Description	Voltage input	Charge time	Weight (kg)	Fitted plug
1149	Gas Ranger UK	240v	60 mins	0.4kg	UK
1150	Gas Ranger Euro	230v	60 mins	0.4kg	Euro




Ranger Gas Nailer battery (1148) and 1hr fast charger (1149-UK, 1150-Euro).

Replacement Battery/Specifications

Code	Tool	Voltage/type/Ah	Shots per charge	Weight (kg)
1148	Gas Ranger	7.2v/Ni-MH/1.5Ah	4,000	0.3kg

Technical Specifications - Tool

Code	Tool Description	Dimensions (H x W x D)	Weight (kg)	Magazine Capacity	Fastener Type/Length (mm)	Min. Firing from wall	Shots per gas cell	Source Tagged
1147	Gas Ranger	449 x 406 x 112	3.7	62	2.8-3.3 dia. 34° Paper Collated 'D' Head Strip Nail/50-90mm	6mm	1200	✓





Strip nails plastic collated (22° inclined round head)

Code	Nail Diameter/Length/Type	Box Qty.	For Use In:
0435	2.9 50mm CE/12 micron galv., screw	3000	JSN90MHH, JSN00LHH
0436	3.1 90mm CE/12 micron galv., screw	3000	JSN90MHH, JSN00LHH
0437	3.3 65mm CE/12 micron galv., screw	3000	JSN90MHH, JSN00LHH
0438	3.3 75mm CE/12 micron galv., screw	3000	JSN90MHH, JSN00LHH
0439	3.4 100mm CE/12 microngalv., screw	3000	JSN00LHH

Strip nails paper collated (34° inclined 'D' head)

Code	Nail Diameter/Length/Type	Box Qty.	For Use In:
0496	2.8 50mm galv., ring	5000*	KDH90V, KDH90XHH, JDH90FHH, Gas Ranger
1124	2.8 50mm CE/12 micron galv., ring	3300	KDH90V, KDH90XHH, JDH90FHH, Gas Ranger
0502	2.8 65mm bright, ring	5000*	KDH90V, KDH90XHH, JDH90FHH, Gas Ranger
1125	2.8 65mm CE/12 micron galv., ring	3300	KDH90V, KDH90XHH, JDH90FHH, Gas Ranger
1120	3.1 65mm CE/12 micron galv., ring	2200	KDH90V, KDH90XHH, JDH90FHH, Gas Ranger
1121	3.1 75mm CE/12 micron galv., ring	2200	KDH90V, KDH90XHH, JDH90FHH, Gas Ranger
0505	3.1/75mm galv plain	2500*	KDH90V, KDH90XHH, JDH90FHH, Gas Ranger
0506	3.1 75mm bright, ring	2500*	KDH90V, KDH90XHH, JDH90FHH, Gas Ranger
0949	3.1 75mm bright, plain	2500*	KDH90V, KDH90XHH, JDH90FHH, Gas Ranger
1122	3.1 90mm CE/12 micron galv., plain	2200	KDH90V, KDH90XHH, JDH90FHH, Gas Ranger
1123	3.1 90mm CE/12 micron galv., ring	2200	KDH90V, KDH90XHH, JDH90FHH
0510	3.1 90mm bright, ring	2500*	KDH90V, KDH90XHH, JDH90FHH
0511	3.1 90mm extra galv., ring	2500*	KDH90V, KDH90XHH, JDH90FHH

* While stocks last



Positive placement nails paper collated (34° inclined round head)

0984	3.75 38mm CE/12 micron galv., ring	3000	FRH38THH
------	------------------------------------	------	----------

Strip nails and Gas Fuel Cell Packs (Paper Collated 34° inclined)

1118	2.8/50mm CE/12 micron galv., ring + 3 Gas Fuel Cells	3300	Gas Ranger
1119	2.8/65mm CE/12 micron galv., ring + 3 Gas Fuel Cells	3300	Gas Ranger
1114	3.1/65mm CE/12 micron galv., ring + 2 Gas Fuel Cells	2200	Gas Ranger
1115	3.1/75mm CE/12 micron galv., ring + 2 Gas Fuel Cells	2200	Gas Ranger
1116	3.1/90mm CE/12 micron galv., plain + 2 Gas Fuel Cells	2200	Gas Ranger
1117	3.1/90mm CE/12 micron galv., part ring + 2 Gas Fuel Cells	2200	Gas Ranger

Gas Fuel Cells

1113	Gas Fuel Cell 80ml (2 pcs per hanging clam)	1	Gas Ranger
------	---	---	------------

12 Micron galvanised CE nails. Now available

NEW



Quality gas/nail and nail only packs

The Tacwise Gas Ranger is designed for use with all top quality 34° 'D' head paper collated strip nails.

The Tacwise 80ml fuel cell can be used with all compatible first fix gas nailing tools. COSHH and material safety data sheet details are available on request. These fuel cells are available as a gas only twin cell pack or complete with nails as featured here.

Wide carton handle makes carrying safe and easy. Rain resistant laminated packaging.

Technical specifications at a glance

General Purpose & Upholstery	Narrow Crown	HD, Wide Crown & Corr Fastener	Nailers & Pimners	Coil Nailers		Strip Nailers																																
				Strip Nailers	Strip Nailers	Coil Nailers	Strip Nailers																															
A7116LN	A7116V	A7116P	A8016V	A8016LN	A14014V	C9725V	D9040V	G1450V	F1450M	G1738XH	FCF15XCB	GDA64V	A6435	C1832V	CMB35PHH	DGN50V	DFN50V	GFN64V	DGN50LHH	FCN50LHH	GCN57P	FCN57V	HGN65P	FCN65V	GCN70V	HGN83P	JCN90XHH	LCN130V	KDH90V	JSN90MH	FRH38TH	GAS RANGER						
230	218	218	218	230	235	248	273	302	360	276	300	331	240	273	250	273	302	302	282	260	305	380	305	305	330	305	385	370	470	526	326	449						
45	43	43	43	45	46	55	67	88	78	93	87	100	44	67	49	67	88	88	88	108	128	130	130	132	132	143	165	150	137	114	112	406						
220	150	152	150	220	159	192	231	253	272	271	270	302	162	228	200	249	270	270	295	284	294	290	302	312	308	340	370	364	364	260	406							
1.1	0.9	0.8	0.9	1.3	0.9	1.2	1.2	1.7	1.9	3.0	2.6	1.8	0.9	1.1	1.3	1.2	1.7	1.8	1.5	2.0	2.7	2.7	2.5	2.0	3.7	3.6	6.5	3.8	3.9	2.1	3.7							
71	71	71	80	80	140	97	90	14	14	17	CF	23G/0.64	186G/1.80	166G/2.16	180	180	160	160	160	216	2.1	2.1	2.1	2.3	2.3	2.5	2.5	3.1	2.8	2.9	3.3	2.8	2.8	2.8				
4-16	4-16	4-16	4-16	4-16	10-12	10-12	10-12	15-19	19-38	16-19	9-15	38-64	12-35	10-35	15-35	20-50	20-50	20-50	20-50	22-50	27-50	25-50	32-50	40-50	38-50	75-90	75-90	50-90	50-90	25-38	25-38	25-38	25-38	25-38	25-38			
180	180	180	150	150	150	125	100	100	150	140	80	100	170	100	150	100	100	100	100	400	400	400	350	350	350	300	225	225	75-95	80	55	62	62	62	62			
77	77	77	77	77	77	86	88	88	88	86	80	89	77	81	86	86	86	88	88	83	96	96	96	96	96	83	95	88	86	91	84	84	84	84	84	84		
60-100	60-100	60-100	60-100	60-100	60-100	60-100	60-100	60-100	70-120	70-120	65-115	70-120	60-100	60-100	60-100	60-100	60-100	60-100	70-120	70-120	70-120	70-120	70-120	70-120	70-120	70-120	70-120	70-120	70-120	70-120	70-120	70-120	70-120	70-120	70-120	70-120	70-120	
SS	SS	SS	SS	SS	SS	SS	CT	CT	CT	CT	CT	ST	CT	CT	SE	CT	CT	SE	SE	SE	SE	CT	SE	SE	SE	CT	CT	SS	SS	SS	SS	SS	SS	SS	SS	SS	SS	SS

Performance, Comfort & Safety

- Soft rubber safety grip
- Single shot trigger
- Slender length nose
- Neat rear exhaust system
- Double safety trigger
- High capacity magazine/nail drum
- Extra long nose
- Bottom loading
- High durability driver blade system
- Quick release reloading system
- Depth control countersinking
- Non marking foot
- Quick release nose plate
- Open (viewable) magazine system
- 360° adjustable exhaust port
- Double power cylinder system
- Side quick release loading system
- Staple/nail refill window
- Automatic pin length adjuster
- Safety yoke to avoid slippage
- Protective bumper

CT Contact Trip (Bump Fire)

SE Sequential

SS Single Shot

ST Single Shot/Contact Trip

SE Contact Trip/Sequential

BEST VALUE

Applications

- Attaching wire mesh netting to wood
- Bed frames
- Furniture frames
- Cane/rattan furniture
- Carpet/underlay/gripper/thresholds
- Coffin linings
- Coffin manufacture
- Drawer bottoms/cabinet assembly
- Exhibition/show construction
- Exhibition/show upholstery
- Fencing
- Fixing underlayment
- Furniture/cabinet/woodwork assembly
- Insulation & lining
- Kitchen & bedroom furniture
- Office screens
- Pallet/crate/packing case manufacture
- Paneling
- Pelmets, blinds & awnings
- Pet cages, runs and enclosures
- Plasterboard
- Cabins, mobile homes, caravans
- Presentation boxes
- Roofing felt
- Sheds & garden buildings
- Shoe repair
- Sign manufacture
- Soft and hardwood floorboards
- Staircase construction and banisters
- Sub flooring/boarding out & plywood
- Theatre & film scenery
- Trellis work
- Tubs and barrels
- Upholstery & re-upholstery
- Window display/shop fitting
- Window frames & beading

General Purpose & Upholstery

- A7116LN
- A7116V
- A7116P
- A8016V
- A8016LN
- A14014V
- C9725V
- C9032V
- D9040V
- G1450V
- F1450M
- G1738XH

Heavy Duty, Wide Crown & Corr Fastener

- FCF15XCB

Nailers & Pimners

- GDA64V
- A6435
- C1832V
- CMB35PHH
- DGN50V
- DFN50V
- GFN64V
- FCF150LHH
- DGN50LHH
- GCN57P
- FCN57V
- HGN65P

Coil Nailers

- FCN65V
- GCN70V
- HGN83P
- JCN90XHH
- LCN130V
- KDH90V
- JSN90MH
- FRH38TH
- GAS RANGER

Strip Nailers

- JCN90XHH
- LCN130V
- KDH90V
- JSN90MH
- FRH38TH
- GAS RANGER

Applications

- Beading & picture/mirror frames
- Boat building
- Cane/rattan furniture
- Coffin manufacture
- Construction
- Decking
- Display & shop fitting
- Door frames & skirting
- Exhibition/show construction
- Fencing
- Fire surrounds
- Cable drums and steel skids
- Fixing gripper and thresholds
- Furniture/cabinet/woodwork assembly
- Insulation & lining
- Kitchen & bedroom furniture
- Pallet/crate/packing case manufacture
- Paneling
- Pet cages, runs and enclosures
- Pine furniture manufacture
- Cabins, mobile homes, caravans
- Presentation boxes
- Saunas
- Sheds & garden building
- Shoe repair
- Skirting boards/dado to masonry
- Soft and medium wood floorboards
- Staircase construction and banisters
- Sub flooring/boarding out
- Suspended ceilings
- Theatre & film scenery
- Timber framing
- Tongue and groove flooring
- Toy manufacture
- Trellis work
- Window frames & beading

Hot & Cool Melt Glue Guns

Offering a strong permanent alternative for many hobby, craft, DIY and industrial fixing jobs.

Speed and durability

The 207 leads the glue gun programme. For the hobby and professional alike, Tacwise glue guns and adhesives are a superb, powerful essential for every tool bag and workshop.

All our versatile, high impact trigger fed glue guns bond almost anything in less than two minutes.



207 Tool Features

Durable 3 minute heat up melting chamber, cooling "air flow" vents, a removable non-drip push on nozzle for accurate gluing, a platform and retractable stand as well as a 4-finger trigger operation for ease and convenience.



150/202 Tool Features

Models 150/202 have handy features including insulated rubber nose protectors, on/off switches (illuminated for 202) and pressure touch feed systems for speed and reliability.

Rubber nose protector



Illuminated on/off switch (model 202)



Pressure touch feed system

150 Cool Melt Glue Gun

DIY/Semi-Pro Code: 0465 Includes: 2pcs 7.4mm x 100mm clear glue sticks

0.3kgs Diameter/Length 7.4mm x 100mm Pack Style Retail Box Trade = 12 Units Transit = 36 Units

Safe, compact gun, ideal for hobby use, arts and crafts or general low volume applications. Cool melt offers a safer alternative with the adhesive running at a much lower temperature.



202 Hot Melt Glue Gun

Semi-Professional Code: 0466 Includes: 1pc 11.75mm x 100mm clear glue stick

0.5kgs Diameter/Length 11.75mm x 300mm Pack Style Retail Box Trade = 6 Units Transit = 24 Units

Well balanced gun for maximum control and an easier output flow of glue.

New high wattage model (not featured) coming February 2014



207 Hot Melt Glue Gun

Professional Code: 0003

1.5kgs Diameter/Length 11.75mm x 300mm Pack Style Carry Case Trade = 4 Units Transit = 8 Units

Robust gun offering high performance during high volume glue output. Rear clutch trigger mechanism enables fast and steady glue flow. 2kg glue output per hour.



Hot & Cool Melt Glue Gun Technical Specifications

Code	Tool Description	Dimensions (H x W x D)	Weight (kg)	Glue Diameter/Length (mm)
0465	150 Cool Melt Glue Gun	117 x 127 x 24	0.3	7.4 x 100mm
0466	202 Hot Melt Glue Gun	157 x 187 x 32	0.5	11.75 x 300mm/100mm
0003	207 Hot Melt Glue Gun	175 x 265 x 48	1.5	11.75 x 300mm/100mm

Tool Applications

Application	150	202	207
Beading/mouldings		•	•
Decorative/general DIY	•	•	•
Display/shop fitting		•	•
Exhibition/shows			•
Exhibition/shows upholstery			•
Fixing carpets/underlay		•	•
Fixing gripper/thresholds		•	•
Floristry	•	•	•
Hobby crafts	•	•	•
Kitchen/bedroom furniture			•
Picture/mirror frames		•	
Pine furniture			•
Schools/education	•	•	
Shoe repair			•
Theatre/film scenery		•	
Upholstery/re-upholstery		•	•
Window dressing	•	•	

Tool Features

Performance, Comfort & Safety	150	202	207
Long power cord	✓	✓	✓
Wide ergonomic grip	✓	✓	✓
On/off switch	✓	✓	
Tough polymer lightweight body	✓	✓	✓
On/off light indicator		✓	
Multi-finger trigger		✓	✓
Air vents			✓
Stand	✓	✓	✓
Wide safety stand			✓
Nose heat protector	✓	✓	✓
Fast heating system	✓	✓	✓



Ideal for a wide variety of industrial/semi-industrial applications from packaging, carpentry assembly, flooring (gripper) and many more.

Glue Stick Technical Specifications

Hot Melt Glue

Code	Description	Dimension	Pack Qty	Pack Style	Application	For Use In:
0469	Clear Hot Melt Glue Sticks	11.75 x 100mm	6 Sticks	Retail Card	Multi purpose	202, 207
0470	Clear Hot Melt Glue Sticks	11.75 x 300mm	16 Sticks	Retail Box	Multi purpose	202, 207
0471	Clear Hot Melt Glue Sticks	11.75 x 300mm	5kg/160 Sticks	Carton	Multi purpose	202, 207
0472	Tan Hot Melt Glue Sticks	11.75 x 300mm	5kg/160 Sticks	Carton	Packaging/flooring	202, 207
1013	Tan Hot Melt Glue Slugs	43mm	10kg/168 Slugs	Carton	Packaging/flooring	Standard 43mm Slug Guns

Cool Melt Glue

0476	Clear Cool Melt Mini Glue Sticks	7.4 x 100mm	12 Sticks	Retail Card	Multi purpose	150
------	----------------------------------	-------------	-----------	-------------	---------------	-----



Models 150/202 are great for arts, crafts, blinds and furnishings.

Glue Stick Applications

Hot Melt Glue

Glue Type	Open Time (seconds)	Ideal For:
White/Woodworking	45 - 60	Woodworking and where white packaging/finish is needed
Clear Multi-Purpose	45 - 60	General packaging, product assembly, upholstery and dried flower displays
Tan Glue	20 - 25	Packaging and flooring applications including carpet and grippers
Tan Glue Slugs	20 - 35	Packaging and flooring trade high volume usage in industrial guns
Clear Premium Multi-Purpose	60	A multitude of applications. Popular for 'fabric to fabric'

Cool Melt Glue

Clear Multi-Purpose	60	Hobby crafts, schools and floristry
---------------------	----	-------------------------------------

Packaging

Great products need to be perfectly packaged too. Our quality thinking extends from the product design and function right through to the packaging it is supplied in. With environmental needs at the forefront of our thinking we strive for eco-friendly solutions and aim to provide customers with all essential information. Packs display great consumer detail such as compatibility, function, major applications and features plus, of course, any related safety issues. We are committed to Euro 5 labelling.



Commercial Packs

Many staple and nail packs come in both small retail versions as well as these larger commercial boxes for the tradesman using large quantities. Information includes references to popular tools from other manufacturers, translations and EAN 13 barcodes.

Carton

Styled to a high standard with tough and super clear product information, our cartons display easy product/re-order code identification and large "at a glance" content details on two sides, translations and EAN 13 barcodes. Most cartons are water resistant too.

Retail Clams

Neat "try me" clams show off tool features. Most tools are supplied with an information booklet and a starter supply of fastenings. Packaging for higher value items also includes a security device label. All with translations and EAN 13 barcodes.



Innovative and Convenient Alternatives

Aside from popular standard packs of staples and nails in both small retail and bulk versions, Tacwise also offers a number of innovative packs including its nail and staple selection packs. All are designed to provide convenience and best value for the consumer.

Floor Standing Merchandisers

Look out for these promotional stands which showcase leading Tacwise products and offer tremendous value.



Retail Tool Box

The benefits are clear to see on our bright eye-catching full colour packaging. Descriptive details of major applications, translations on the leading surface and easy product/re-order code identification for nails/staples used. Safety/warning precautions and easy reference symbols, EAN 13 barcodes as well as instruction manuals with clear illustrations.



Carry Case

Tough carry cases are the most popular form of packaging for tool protection and to retain associated components in one neat store. These cases are retailed with full colour sleeves to make clear the suitability of each tool to its prospective new owner. Incorporates all of the features of the retail tool box.



Selection Packs

A super convenient and cost effective alternative to buying single-sized fixings in bulk. These premium quality assorted staples and nails come in handy selection packs. Offering significant added value the unique packs provide a similar level of user friendliness to the drill bit and blade selection packs that are common within the tools trade.



Modular Floor Standing Displays

Intelligent; two different sized stand options combined with various accessories allow you to create a perfect display for any combination of Tacwise products. Versatile; completely versatile, all components clip together so that they can be moved or added to as the range increases and as promotions and new products need to be dominantly positioned.



Industrial air tackers sit neatly alongside small hand tackers. Fast moving consumables are easily identified by busy tradesmen. Hero products can be prominently displayed at eye level and handled in a "try me" fashion so that buyers can identify the build quality, product size and weight and appreciate product features.



Rolling display

Any combination of stands can be lined up together to create a rolling display in-store. Grabbing the attention of all customers, this is a great retail selling tool and creates an exciting and professional impression to the consumer.

Components Explained

The empty stand comes as 3 parts which are quickly clipped together plus the three logos which are easily screwed into place. The accessories are all clipped into any position you wish to create a display built to your specification. Displays can be used individually, side by side or back to back. All accessories are packed and coded singularly for convenience.



(1 metre display shown)

Display Stands

Code	Description	For use with	Pack Qty
1 0836	1 metre display stand (900 x 165 x 50 x 510mm-base)	-	1
2 0837	Bar (900mm)	1m stand	1
3 0838	Tray/shelf (900 x 120 x 340mm)	1m stand	1
4 0839	Air tacker display bar including brass couplings (900mm)	1m stand	1
0840	1/2 metre display stand (550 x 165 x 50 x 510mm-base)	-	1
0841	Bar (550mm) (not illustrated)	1/2m stand	1
0842	Tray/shelf (550mm x 120 x 340mm) (not illustrated)	1/2m stand	1
5 0844	Hooks	1m & 1/2m stand	10
6 0846	Hero product fitment/shelf (300 x 80 x 230mm)	1m & 1/2m stand	1

Other Merchandising

Code	Description	Pack Qty
TWMERCH	500EL merchandiser (cardboard floor standing)	1
0778	Perspex logo carrier (slatwall type)	1
0779	Perspex logo carrier (pegboard type)	1
TWHEADER	Card header insert (use with items 0778 & 0779)	1
0811	Roll banner (internal use)	1
0810	Vinyl banner (internal/external use)	1

Discontinued Items/Codes

Code	Description	Box Qty.	Code	Description	Box Qty.	Code	Description	Box Qty.
Hand Tackers			Narrow Crown Staplers			16G Hardened Finish Nails (Continued)		
RZ140PT1	Z-140-P ABS Tacker		C9725VHH	25mm Narrow Crown Stapler		S03800A4-CG	16G/30mm •	2500
0315	Z1-53 Tacker Merchandiser		C9030VHH	30mm Narrow Crown Stapler		S04500A4-CG	16G/35mm •	2500
Z140PKIT-KK	Z-140-P Tacker Kit •		C9040LHH	40mm Narrow Crown Stapler •		S051C0A4-CG	16G/45mm •	2500
Compact Electrics			Heavy Duty & Wide Crown Staplers			Packaging Staples		
0864	Pro-4 53 Electric Tacker		F1440LHH	40mm Heavy Duty Stapler •		0458 (S9B10)	SECO B/10mm Staples Galv.	5000
0929	Pro-4 53 Electric Tacker (Euro)		F1440L	40mm Heavy Duty Stapler •		0459 (S9B12)	SECO B/12mm Staples Galv. •	5000
0943	Pro 140EL Nailer/Stapler Kit		G1450MHH	50mm Heavy Duty Stapler •		0460 (S9B16)	SECO B/16mm Staples Galv.	5000
0866	Pro 140EL Electric Stapler/Nailer •		Air Nailing- Nailers and Pinners			S9SS08	SECO B/8mm Staples Stainless Steel •	5000
0328	Hobby 53EL Electric Stapler/Nailer		A6425KHH	25mm Headless Pinner •		S9SS12	SECO B/12mm Staples Stainless Steel •	5000
Medium Duty Electrics			Air Nailing- Coil Nailers			S9SS16	SECO B/16mm Staples Stainless Steel •	5000
0324	Master Nailer 181EL Pro Boxed •		FCN57XHH	Professional Air Coil Nailer (2.1/2.3) •		0464	110/16mm Bedding Plier Staples	5000
0325	Master Nailer 181EL Pro 110v (inc. 2000 nails) •		FCN65GHH	Professional Coil Nailer (2.1/2.5)		Jumbo Coil Nails (Wire Collated Flat Top)		
1031	Master Nailer 181EL Pro Nailer Kit		GCN65XHH	Air Coil Nailer 2.5-3.1, 45-65mm		1142	2.8/50mm Galv. Plain 8 Micron •	7200
0326	Master Nailer 191EL Pro Nailer Boxed		GCN70XHH	Professional Air Coil Nailer (2.3/2.9) •		Coil Nails (Wire Collated Flat Top)		
0323	71EL Pro Electric Nailer		HCN83XHH	83mm Coil Nailer •		0812	2.1/30mm Bright Ring •	16000
Inclined Electric Nailers			Air Nailing- Strip Nailer			0272	2.1/30mm Galv. Ring	16000
0927	Master Nailer 400EL Pro 110v		JDH90FHH	90mm 34° Angled Strip Nailer 50-90mm		W2132BPL-CG	2.1/32mm Bright Plain •	16000
0664	Master Nailer 500EL Pro		KDH90XHH	90mm 34° Angled Strip Nailer 50-90mm •		0813	2.1/35mm Bright Ring	16000
0748	Master Nailer 500EL Pro (Euro)		JSN00LHH	100mm 22° Angled Strip Nailer 50-100mm •		0814	2.1/40mm Bright Ring	16000
0850	Replacement Nose Pieces for Master Nailer 500EL Pro (Pk 5)		Upholstery Staples			0275	2.1/40mm Galv. Ring	16000
Cordless Stapling/Nailing			0455	73/8mm Staples	5000	0815	2.1/45mm Bright Ring	16000
0852	Master Nailer Ranger 40 18G Brad Nailer Tradesmans Pack (Euro) •		S7310-DN	73/10mm Staples •	5000	0276	2.1/45mm Galv. Ring	16000
0863	Master Nailer Ranger 40 16G Finish Nailer Tradesmans Pack (Euro) •		0376	1400/6mm Staples	10000	0816	2.1/50mm Bright Ring	16000
0859	Master Nailer Ranger 40 Duo - Entry unit		1400AS08	1400/8mm Staples •	10000	0278	2.3/45mm Bright Ring	16000
0754	Master Nailer Ranger 40 Duo - Bare unit		Narrow Crown Staples			0426	2.5/60mm Galv. Ring	9000
0755	Master Nailer Ranger 40 Duo - Entry unit		0314	90/32mm Narrow Crown DP Staple	5000	Coil Nails (Wire Collated Conical Top)		
0756	Master Nailer Ranger 40 Duo - Pro Pack		S9032	90/32mm Divergent Point •	5000	0408	2.1/27mm Galv. Ring Blunt Point	16000
0757	Master Nailer Ranger 40 Duo - Pro Pack (Euro)		Heavy Duty Staples Bright			0280	2.1/32mm Galv. Smooth •	16000
0758	Master Nailer Ranger 40 Duo - Trademans Pack		1127	14/32mm Bright Staples	10000	0409	2.1/32mm Bright Ring	16000
0761/0776	1 Hour Charger for Master Nailer Ranger 40 Duo (UK & Euro)		1110	14/35mm Bright Staples	10000	0410	2.1/32mm Galv. Ring	16000
0762	5 Hour Charger for Master Nailer Ranger 40 Duo		1111	14/38mm Bright Staples	10000	0411	2.1/32mm Galv. Ring Blunt Point	16000
0759	1.7Ah NiCad Battery for Master Nailer Ranger 40 Duo, 18G & 16G Nailers •		1112	14/45mm Bright Staples	10000	0412	2.1/38mm Bright Ring	16000
0760	1.4Ah NiCad Battery for Master Nailer Ranger 40 Duo, 18G & 16G Nailers •		1129	14/50mm Bright Staples	10000	0413	2.1/38mm Galv. Ring	16000
0851	Replacement Nose Piece for Master Nailer Ranger 40 Duo (Pk 1) •		Wide Crown Staples			0414	2.1/38mm Galv. Ring Blunt Point	16000
0970	Replacement Nose Piece for Master Nailer Ranger 40 Nailer (Pk 1) •		S17250Z1	17/25mm Staples	10000	0415	2.1/45mm Bright Ring	16000
Staples for Hand/Electric Tackers			S17320Z1	17/32mm Staples	10000	0416	2.1/45mm Bright Smooth	16000
0339	53/16mm	2000	23G 'A64' Headless Pins			Strip Nails (Paper Collated 34°)		
S53162M1	53/16mm •	2000	0001	A65/12mm Staples	10000	0496	2.8/50mm Galv. Ring •	5000
0975	53 Staple Value Pack	8000	0002	A65/17mm Staples	10000	0497	2.8/50mm Galv. Plain	
0976	140 Staple Value Pack	8000	0004	A65/25mm Staples	10000	0498	2.8/50mm Bright Ring	
0868	91/15mm	5000	21G Mini Tip' Mini Brads			0499	2.8/50mm Extra Galv. Ring	5000
0869	91/18mm DP	5000	0388	MB15mm Staples	10000	0500	2.8/65mm Galv. Ring	
0870	91/20mm	5000	0389	MB20mm Staples	10000	0501	2.8/65mm Galv. Plain	
0871	91/22mm DP	5000	0390	MB25mm Staples	10000	0503	2.8/65mm Extra Galv. Ring	
0872	91/25mm	5000	0391	MB30mm Staples	10000	0504	3.1/75mm Galv. Ring	
0873	91/30mm	5000	Headless Brads			0505	3.1/75mm Galv. Plain •	2500
0874	91/35mm	5000	S16HL3B4	16mm (18G) Brads •	10000	0506	3.1/75mm Bright Ring •	2500
0875	91/40mm	5000	S19HL3B4	19mm (18G) Brads •	10000	0509	3.1/90mm Galv. Plain	
Air Stapling Upholstery Tackers			16G Hardened Finish Nails			0949	3.1/75mm Bright Plain •	2500
A5316PHH	53 Staple Lightweight Air Stapler		0291	16G/20mm	2500	0950	3.1/90mm Bright Plain	
A7116QII	Premium Air Stapler 71 Type 4-16mm		0292	16G/25mm	2500	0507	3.1/75mm Extra Galv. Ring •	2500
A8014PHH	Polymer Air Stapler 80 Type 4-14mm		0441	16G/25mm •	5000	0508	3.1/90mm Galv. Ring	2500
A7116PHH	Polymer Air Stapler 71 Type 4-16mm		0442	16G/30mm •	2500	0510	3.1/90mm Bright Ring •	2500
A7116VHH	Air Stapler 71 Type 4-16mm		0443	16G/35mm •	2500	0511	3.1/90mm Extra Galv. Ring •	2500
A7116QHH	71 Upholstery Stapler		0444	16G/40mm •	2500	Torx Head Collated Screws		
A7116NCB	Extra Long Nose 71 Stapler		0445	16G/45mm •	2500	PCS435TH-CX	4/35mm Torx Head	1000
A8014QHH	Premium 80 Upholstery Stapler		0446	16G/50mm •	2500	PCS445TH-CX	4/45mm Torx Head	1000
A8014QII	Air Stapler 80 Type 4-14mm		Hot Melt Glue			0467	5kg Hot Melt Woodworking Glue White	
AMB25VCB	Air Mini Bradder					0473	5kg Hot Melt Premium Glue Clear	
						0474	5kg Hot Melt Glue Slugs (Medium Time) Tan	
						0475	5kg Hot Melt Glue Slugs (Long Time) Tan	
						0468	Mini Multipurpose Hot Melt Glue Sticks Clear	

KEY • While stocks last