



This clamp provides a fast and convenient method of securing bundles from .19" (4.8mm) up to .69" (17.5mm) diameter. It is available with adhesive backing or screw applied with one #6 (M3) screw.

Part Number: ARC.68-S6-Q
Product Family: *Clincher*TM Adjustable Releasable Clamp
Product Line: Screw Mounts

Product Line: Screw/Rivet Applied

RoHS Compliancy Status: Compliant

Part Description: Adjustable and releasable clamp

Product Type: Wire Mounting Clamp

Material: Polypropylene

Color: White

UL Recognized: E136577

Length (In.): 1.00

Length (mm): 25.4

Width (In.): 1.00

Width (mm): 25.4

Bundle Diameter Range (In.): .19-.69

Bundle Diameter Range (mm): 4.8-17.5

Environment: Indoors

Flammability Rating: UL94 HB

Max. Bundle Diameter (In.): .68

Max. Bundle Diameter (mm): 17.3

Metric Screw Size: M3

