

ILD LFR45D038



Ideal for new builds - Only a 45mm cut-out (for MR11 12V GU4 or MR11 240V GU10 lamps). Great for tight spaces - 38.5mm super-low profile. Aesthetic - Ultra-thin 1mm blend-in bezel with a premium finish. Easy wiring - with a Fast-Fit, loop-in/loop-out, junction box for tool free assembly. Easy to install and remove - Durable steel assembly. Extended lamp life - Open design allows airflow to extend lamp life compared to traditional designs. 45mm Cut-Out, 64mm Diameter, IP65. This downlight is fire rated to 30, 60 and 90 minutes in compliance with BS476 Part 21:1987, Air Tightness compliant with Part C and Part L and Resistance to Sound compliant with Part E. See installation guide for full details.

Details

Barcode:	5055788254560
Category:	Downlights
Range Name:	Evofire mini
Product Body Finish:	Satin Nickel
Market Segment:	Commercial indoor, Residential indoor
Finish:	Satin Nickel
Warranty (Years):	3
CE RoHS:	Yes

Physical Data

Product Depth (mm):	38.5
Product Weight (g):	10
Material:	Steel, Glass
Overall diameter (mm):	64
Construction:	Pressed Steel, Glass
Cut Out Diameter (mm):	45
Luminaire Fixing:	Recess mounted
Placement / Application:	Indoor, General Lighting

Electrical Data

Light Data

Fire Rating (mins):	30, 60, 90
----------------------------	------------

Environment

CE RoHS:	Yes
-----------------	-----

IP Rating (Back/Recessed side):	IP20
IP Rating (Ingress Protection):	IP65

Packaging

Package Weight (g):	13
Package Length (mm):	70
Package Width (mm):	70
Package Depth (mm):	65
Qty per euro pallet:	1632