

ILD LFR45D039



Ideal for new builds - Only a 45mm cut-out (for MR11 12V GU4 or MR11 240V GU10 lamps). Great for tight spaces - 38.5mm super-low profile. Aesthetic - Ultra-thin 1mm blend-in bezel with a premium finish. Easy wiring - with a Fast-Fit, loop-in/loop-out, junction box for tool free assembly. Easy to install and remove - Durable steel assembly. Extended lamp life - Open design allows airflow to extend lamp life compared to traditional designs. 45mm Cut-Out, 64mm Diameter, IP65. This downlight is fire rated to 30, 60 and 90 minutes in compliance with BS476 Part 21:1987, Air Tightness compliant with Part C and Part L and Resistance to Sound compliant with Part E. See installation guide for full details.

## Details

<b>Barcode:</b>	5055788254577
<b>Category:</b>	Downlights
<b>Range Name:</b>	Evofire mini
<b>Product Body Finish:</b>	Polished Chrome
<b>Market Segment:</b>	Commercial indoor, Residential indoor
<b>Finish:</b>	Polished Chrome
<b>Warranty (Years):</b>	3
<b>CE RoHS:</b>	Yes

## Physical Data

<b>Product Depth (mm):</b>	38.5
<b>Product Weight (g):</b>	10
<b>Material:</b>	Steel, Glass
<b>Overall diameter (mm):</b>	64
<b>Construction:</b>	Pressed Steel, Glass
<b>Cut Out Diameter (mm):</b>	45
<b>Luminaire Fixing:</b>	Recess mounted
<b>Placement / Application:</b>	Indoor, General Lighting

## Electrical Data

### Light Data

<b>Fire Rating (mins):</b>	30, 60, 90
----------------------------	------------

## Environment

<b>CE RoHS:</b>	Yes
-----------------	-----

<b>IP Rating (Back/Recessed side):</b>	IP20
<b>IP Rating (Ingress Protection):</b>	IP65

## **Packaging**

<b>Package Weight (g):</b>	13
<b>Package Length (mm):</b>	70
<b>Package Width (mm):</b>	70
<b>Package Depth (mm):</b>	65
<b>Qty per euro pallet:</b>	1632