



TECHNICAL INFORMATION

Watts:	18
Lumens:	1080
Beam Angle:	120°
Color Temperature:	3IN1
Shape:	Round
Dimmable:	No
Input Power:	AC:175-265V, 50/60Hz
Long Life:	20,000 Hours
Unit Color:	White
Body Type:	Plastic
Dimension:	Ø310x55mm
PF:	>0.5
CRI:	>80
Operation Temperature:	-20°C to +45°C
LED Chip Type:	SMD
On/Off Cycles:	>15000

FEATURES

- 3IN1 Domelights designed to switch between three colours using toggle switch
- 3-in-1 Colour changing lights offer unparalleled flexibility and ease when compared with single coloured lights
- High quality power driver and LED Chip
- Excellent heat dissipation
- Easy to install and low maintenance
- Suitable for living rooms, bedrooms, utilities, corridors etc

COLOR CHANGING SWITCH | LED LIGHTING

<p>V-TAC's Decorative Lighting range is abundant with elegant and classy luminaries and fittings that provide customers with the ability to spruce up any location with limitless combinations of designs. Our lighting fixtures come with extended multi-year warranty, as well as unmatched support and quality.</p>

SKU: 7605 - 1407 940

[View more details](#)



PACKAGING

Gross Weight (Kgs): 0.396
 Unit CBM: 0.0059535
 Dimension: Ø310x55mm

MASTER BOX PACKAGING

Box Qty: 10
 Qty Per Pallet: 150
 Length (Box) mm: 60
 Width (Box) mm: 315

LISTING DETAILS

Commodity Code: 9405104090
 Ean Code: 3800157652209